



Juniper SFP-GE10KT15R13 Compatible SFP Module - 1000BASE-BX-D - 10 GbE Gigabit Ethernet BiDi Fiber (SMF) (SFPGE10KT5R3)

Product ID: SFPGE10KT5R3



The SFPGE10KT5R3 is a Juniper SFPP-10GE-LR compatible fiber transceiver module that has been designed, programmed and tested to work with Juniper brand switches and routers. It delivers dependable 1 GbE connectivity over fiber cable, for 1000Base-BX10-D compliant networks, with a maximum distance of up to 40 km (24.8 mi).

Technical Specifications:

- Wavelength: 1310nmTx/1550nmRx
- Maximum Data Transfer Rate: 1000 Mbps (1 Gbps)
- Type: Single Mode Fiber
- Connection Type: LC Connector
- Maximum Transfer Distance: 10 km (6.2 mi)
- MTBF: 3,713,222 hours
- **Power Consumption:** < 1.3W
- Digital Diagnostics Monitoring (DDM): Yes

www.startech.com 1 800 265 1844



Data Sheet

This SFP fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

StarTech.com SFPs

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

www.startech.com 1 800 265 1844



Certifications, Reports and Compatibility







Features

- 100% JUNIPER SFP-GE10KT15R13 COMPATIBLE: 1 Gigabit Ethernet BiDi Fiber Single Strand SFP designed, programmed and tested to work with compatible Juniper switches and routers to deliver dependable 1GbE connectivity
- INCREASE BANDWIDTH ON EXISTING INFRASTRUCTURE: This 10 Gigabit Ethernet bi-directional WDM SFP+ transceiver module sends and receives over a single strand of fiber optic cable instead of two
- TECHNICAL SPECS: 1000BASE-BX-D | 1Gbps | 10G Bi-Directional Downstream | Single Mode (SMF) | LC Connector | 1310nmTx/1550nmRx | Digital Diagnostic Monitoring (DDM) | Distances up to 10km (6.2mi)
- LIFETIME WARRANTY: Backed by a lifetime warranty on the life of the module itself, not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- PROGRAMMED & TESTED FOR COMPATIBILITY: Compatible with Juniper routers and switches. MSA Compliant with DDM that reports the transceiver's status to most SNMP network management tools



Hard-to-find made easy*

Data Sheet

	Warranty	3 Years
Hardware	Compatible Brand	Juniper
Performance	DDM	Yes
	Maximum Data Transfer Rate	1.00 Gbps
	MTBF	3,713,222 hours
	Wavelength	1310nmTx/1550nmRx
Connector(s)	Connector A	1 - SFP Slot Plug
	Connector B	1 - Fiber Optic LC Duplex Female
Physical Characteristics	Product Height	0.5 in [1.2 cm]
	Product Length	2.6 in [65 mm]
	Product Width	0.6 in [14 mm]
	Weight of Product	2.5 oz [72 g]
Packaging Information	Package Height	0.6 in [15 mm]
	Package Length	9.1 in [230 mm]
	Package Width	8.1 in [207 mm]
	Shipping (Package) Weight	2.8 oz [80 g]
What's in the Box	Included in Package	1 - SFP Transceiver
	Fiber Operating Mode	Full-Duplex
	Max Transfer Distance	10 km (6.2 mi)

Product appearance and specifications are subject to change without notice.

www.startech.com 1 800 265 1844