


Citrix 455883-B21 Compatible QSFP+ Module - 40GBASE-SR4 - Multi Mode Fiber (MMF) - 40GE Gigabit Ethernet QSFP+ - MPO 100 m - 850nm - DDM  
Product ID: 3013936-E2-ST



The 3013936-E2-ST is a Citrix 3013936-E2 compatible fiber transceiver module that has been designed, programmed and tested to work with Citrix brand switches and routers. It delivers dependable 40 GbE connectivity over fiber cable, for 40GBase-SR4 compliant networks, with a maximum distance of up to 100 m (328 ft).

:

850nm  
40 Gbps  
Multi Mode  
MPO  
100 m (328 ft)  
244,610,582 hours  
< 0.7W

This QSFP+ fiber module is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions.

All StarTech.com SFP & SFP+ transceiver modules are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of SFP modules and direct-attach SFP cables, providing the convenience and reliability you need to ensure dependable network performance.

## Certifications, Reports and Compatibility



## Applications

## Features

- 100% Citrix 455883-B21 COMPATIBLE: Designed, programmed and tested to work with compatible Citrix switches and routers to deliver dependable 40GbE connectivity

- **TECHNICAL SPECS:** 40GBASE-SR4 40 Gbps Multi Mode MPO Connector 850nm Digital Diagnostic Monitoring (DDM) Distances up to 100 m (328 ft)
- **TESTED FOR OEM HOST COMPATIBILITY:** Hot-swappable in Citrix routers and switches; DDM support reports the transceiver's status to most SNMP network management tools
- **LIFETIME WARRANTY:** Backed by a lifetime warranty on the life of the module itself - not the life of your switch. Our modules won't void your OEM warranty and supported by our Tech Advisors 5/24
- **WORKS WITH MSA COMPLIANT SWITCHES:** Also works with switch models from Ubiquiti, D-Link, Netgear, Supermicro, TP-Link and more that accept uncoded modules

<b>Hardware</b>	Warranty	Lifetime
	Compatible Brand	Citrix
<b>Performance</b>	Maximum Data Transfer Rate	40.00Gbps
	Max Transfer Distance	100 m (328 ft)
	Type	Multi Mode
	Wavelength	850nm
	Compatible Networks	40 Gbps
	MTBF	244,610,582 hours
	Power Consumption (In Watts)	< 0.7W
<b>Physical Characteristics</b>	Product Length	4.5 in [1.2 cm]
	Product Width	3.5 in [90 mm]
	Product Height	0.1 in [3.1 mm]
	Weight of Product	1.8 oz [50 g]
<b>Packaging Information</b>	Package Length	4.8 in [1.2 cm]
	Package Width	0.7 in [18.6 mm]
	Package Height	0.3 in [8.5 mm]
	Shipping (Package) Weight	1.3 oz [37.4 g]
<b>What's in the Box</b>	Included in Package	QSFP+ Transceiver

*\*Product appearance and specifications are subject to change without notice.*