



msi

GRAPHICS CARD

GEFORCE® GTX 1650 4GT LP



SPECIFICATION


Model Name	GeForce® GTX 1650 4GT LP
Graphics Processing Unit	NVIDIA® GeForce® GTX 1650
Interface	PCI Express x16 3.0
Cores	896 Units
Core Clocks	Boost: 1665 MHz
Memory Speed	8 Gbps
Memory	4GB GDDR5
Memory Bus	128-bit
Output	HDMI 2.0b x 1 / DL-DVI-D x 1
HDCP Support	2.2
Power consumption	75 W
Recommended PSU	300 W
Card Dimension(mm)	168 x 105 x 37 mm (w/ normal bracket) 168 x 69 x 37 mm (w/ low profile bracket)
Weight (Card / Package)	292 g / 605 g
Afterburner OC	Y
DirectX Version Support	12 API
OpenGL Version Support	4.5
Maximum Displays	2
G-SYNC® technology	Y
Digital Maximum Resolution	7680x4320

CONNECTIONS



1. HDMI
2. DVI-D

FEATURE



LOW PROFILE DESIGN

Low Profile design saves space to allow building a slim/small form factor system.



DUAL FAN THERMAL DESIGN

Dual fans covers more area of heatsink to take heat away more efficiently.



MSI Afterburner

The ultimate overclocking software with advanced control options and real-time hardware monitor.



NVIDIA® G-SYNC®

Gives you more of what you want in a gaming experience. Incredibly smooth, tear-free gameplay at refresh rates up to 240 Hz.