

2 Port HDMI KVM Switch - 4K 60Hz - Compact Dual Port UHD/Ultra HD USB Desktop KVM Switch w/Integrated 4ft Cables & Audio - Bus Powered & Remote Switching - MacBook ThinkPad

Product ID: SV211HDUA4K



The SV211HDUA4K 2-Port 4K60Hz HDMI Cable KVM Switch with Audio and Remote Switching Control gives you control of two HDMI, USB equipped computers with a single monitor, keyboard, mouse and audio peripheral set.

The Dual HDMI KVM switch supports resolutions up to 4K at 60Hz and can drive one large HDMI display with ease, maximizing viewing space. With support for separate 3.5 mm stereo audio, the KVM switch delivers full audio compatibility across connected computers.

While supporting most PC operating systems, this HDMI KVM switch is OS independent which means it works with Mac computers (an adapter may be required) and any other laptops, notebooks, and tablets.

The switch features a remote push-button on a 1.5 meter (4ft) integrated cable that can be placed in an easily accessible location, as well as keyboard hot-keys, and PC or Mac compatible software for switching between systems.

StarTech.com offers a wide selection of high-quality KVM switches and KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice and monitors.

The SV211HDUA4K is backed by a 2-year StarTech.com warranty and free lifetime multilingual technical support.

Certifications, Reports and Compatibility



Applications

Features

- Operate and access two HDMI computers from one workstation at 4K 60Hz resolutions
- Integrate into your set up quickly and easily with built-in 4 ft. KVM cables (including remote switch) and a space-saving design
- Switch PCs via push-button, hot-keys or switching software
- Switching software supports Windows, Windows Server & macOS platforms
- USB Powered - No external power adapter required
- Independent audio/mic switching for uninterrupted audio Analog (3.5mm) and HDMI audio supported

Hardware	Warranty	2 Years
	Audio	Yes
	KVM Ports	2
	PC Interface	USB
	PC Video Type	HDMI
	Number of Monitors Supported	1
	Rack-Mountable	No
	Cables Included	Yes
	Daisy-Chain	No
Performance	On-Screen Display	No
	IP Control	No
	Hot-Key Selection	Yes
	Maximum Data Transfer Rate	480Mbps (USB 2.0)
	Maximum Digital Resolutions	3840 x 2160 (Ultra HD 4K) @ 60hz
	Wide Screen Supported	Yes
	Audio Specifications	Two Channel Audio Input and Output
	Auto Scan	10, 20, 30, 40, 50, and 60 seconds
	Port Selection Support	Push Button, Hotkeys, and Software
	MTBF	1,012,884 hours
Connector(s)	Console Interface(s)	USB Type-A (4 pin) USB 2.0

	Console Interface(s)	HDMI
	Console Interface(s)	3.5 mm Mini-Jack (3 Position)
	Host Connectors	USB Type-A (4 pin) USB 2.0
	Host Connectors	HDMI
	Host Connectors	3.5 mm Mini-Jack (3 Position)
Software	OS Compatibility	Windows 2000, XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012, 2016, 2019 Mac OS 10.6 to 10.9
Special Notes / Requirements	Note	In order to access the software and hotkeys of the KVMs, a compatible OS must be installed on the connected host, however the KVM and push button switching function is OS independent
Indicators	LED Indicators	Orange
Power	Power Source	Bus Powered
Environmental	Operating Temperature	0 ~ 40C
	Storage Temperature	-20 ~ 60C
	Humidity	0 ~ 90% RH, Non-Condensing
Physical Characteristics	Product Length	4.3 ft [1.3 m]
	Product Width	3.8 in [97 mm]
	Product Height	1.0 in [25 mm]
	Weight of Product	15.2 oz [431 g]
Packaging Information	Package Length	6.3 in [1.6 cm]
	Package Width	9.8 in [2.5 cm]
	Package Height	2.5 in [63 mm]
	Shipping (Package) Weight	18.4 oz [522 g]
What's in the Box	Included in Package	KVM Switch
	Included in Package	Quick-Start Guide

****Product appearance and specifications are subject to change without notice.***

