

Tripp Lite1111 W. 35th Street
Chicago, IL 60609 USA

Telephone: 773.869.1234 www.tripplite.com

Dual-Display Monitor Arm with Desk Clamp and Grommet - Height Adjustable, 17" to 27" Monitors

MODEL NUMBER: DDR1727DC











Mounts 2 monitors to your workspace using either clamp or grommet and allows one-touch vertical adjustment via easy-grip knob.

Features

Low-Profile Monitor Desk Mount Makes It Easy to Adjust the Height of Your Monitors Adjusting the height of desktop flat-panel displays at home or the office often requires a lot of effort - loosening fasteners, moving the monitor up and down, tightening knobs to secure the monitor in place. With the Tripp Lite DDR1727DC, all it takes is a simple turn of the easy-grip knob on the back of the vertical support for fast one-touch adjustment from 9.4 to 18.5 inches. The monitor arm is compatible with flat-panel screens ranging from 17 to 27 inches.

Choose Clamp or Grommet Mounting to Match Your Preference This monitor mount includes a clamp for attaching it to the edge of a desk or table and a grommet for secure mounting through the desktop. The clamp supports surfaces ranging from 0.4 to 1 inch thick. Grommet mounting works with surfaces from 0.4 to 1.6 inches thick. Maximum weight capacity is 15.4 lbs (6.9 kgs) per screen. Cables are efficiently routed through the rear of the arm to reduce clutter and keep cords organized.

Swivel, Tilt and Rotate the Screen to Find the Perfect and Most Comfortable Viewing AngleThis monitor-arm desk mount adjusts independently to optimize viewing angles and improve ergonomics. To minimize screen glare, reduce eye fatigue and increase viewing comfort, the mount features -10° to +10° tilt, 10° swivel and 180° rotation for position your screens in portrait or landscape orientation. Easy screen adjustment lets you quickly find just the right angle without interrupting your workday. The slim design makes this dual-monitor mount ideal for sit-stand workstations.

VESA-Compliant Mounting Ensures Display CompatibilityVESA (Video Electronics Standards Association) promotes uniformity in the video electronics industry by developing standards for TVs and monitors. For hassle-free display compatibility, this mount supports the following VESA mounting hole patterns: 75 x 75 and 100 x 100. Mounting hardware is included.

Sure to Stand Up to Frequent UseThe durable steel frame withstands the stress of repeated adjustments. Its scratch-resistant powder-coated finish tolerates frequent handling and blends easily into any home or office décor.

Highlights

- Low-profile monitor arm attaches to your desktop with either clamp or grommet mount - .4 to 1" for clamp & .4 to 1.6" for grommet
- One-touch adjustment lets you view 2 monitors at a comfortable height
- Offers -10° to +10° tilt, 10° swivel and 180° rotation to help you find the perfect angle
- Durable steel construction blends into any décor and supports up to 15.4 lbs (6.9 kgs) per screen
- Display cables attach to slim mount to reduce clutter and keep cords organized

Applications

- Adjust the height of your desk monitors with just a twist of a knob, instead of loosening and tightening multiple fasteners and handles
- Mount 2 monitors to your sitstand desk or workstation without taking up much valuable surface space
- Swivel, tilt and/or rotate your screen for the most comfortable viewing angle

Package Includes

- DDR1727DC Dual-Display Monitor Arm, 17" to 27" Monitors
- Mounting hardware
- Owner's manual



Specifications

OVERVIEW		
UPC Code	037332248909	
Device Compatibility	Monitor/HDTV	
PHYSICAL		
Color	Black	
Material of Construction	Steel	
VESA Pattern (mm)	100x100; 75x75	
Motion	Swivel; Tilt	
Mounting Location	Desk Clamp; Grommet	
Degrees of Motion	-10/+10 Tilt and Swivel; 360 Rotate	
Minimum Screen Size (in.)	17	
Maximum Screen Size (cm)	68.58	
Maximum Screen Size (in.)	27	
Minimum Screen Size (cm)	43.18	
Maximum Weight Capacity (lbs.)	15.4	
Maximum Weight Capacity (kg)	7	
Number of Displays	2	
Shipping Dimensions (hwd / in.)	29.30 x 5.70 x 3.50	
Shipping Weight (kg)	3.67	
Unit Dimensions (hwd / cm)	71.7 x 15.0 x 53.0	
Unit Dimensions (hwd / in.)	28.2 x 5.9 x 20.9	
Unit Weight (kg)	3.45	
Unit Weight (lbs.)	7.6	
FEATURES & SPECIFICATIONS		
Cord Management	Yes	
Tools Necessary	Yes	
Security Lock	No	
STANDARDS & COMPLIANCE		
Approvals	RoHS3, REACH	
WARRANTY		



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Product Warranty Period (Worldwide)	5-year limited warranty
-------------------------------------	-------------------------

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies