



Essential features. Essential value.



DELL 23 MONITOR : E2318H



Essential features

Productivity drivers for everyday office demands.



Eco-conscious design

Save energy with power-efficient features.



Superb usability

Create a workspace that fits your exact needs.



Highly reliable

Dell monitors — the number 1 monitor brand worldwide for four consecutive years.*

Dell 23 Monitor



DELL 23 MONITOR : E2318H



ESSENTIAL FEATURES

Maximize workspace efficiency with a monitor designed to meet your business needs.

- **Screen performance:** View your applications, spreadsheets and more on 23 inches of 1920 x 1080 Full HD clarity.
- **Work comfortably:** Optimize eye comfort and reduce harmful blue light emissions with ComfortView and a flicker-free screen.
- **Brilliant at every angle:** See consistent colors across a wide 178°/178° viewing angle.

SUPERB USABILITY

Work the way you like.

- **Convenient controls:** Easy access buttons for power, brightness, contrast and customizable preset models on the monitor's front panel.
- **Versatility included:** Get the flexibility to configure your monitor with various mounts and stands for evolving office requirements.
- **Tilt at will:** Work comfortably by tilting the monitor 5° forward or 21° backward.
- **Plug and view:** Compatible with most legacy and current PCs via VGA and DisplayPort connectivity.

ECO-CONSCIOUS DESIGN

- **Reduced energy footprint:** Our eco-conscious design meets latest regulatory and environmental standards such as ENERGY STAR, EPEAT® Gold³, TCO Certified Displays, CEL and CECP.

SUPERB RELIABILITY

Comes with Dell's high reliability promise.

- From the #1 monitor brand worldwide for four consecutive years.*
- Minimize downtime with Dell's Advanced Exchange Service!¹

FOR MORE INFORMATION
VISIT DELL.COM/MONITORS

Thank you
for making
Dell Monitors

#1
worldwide*

Features & Technical Specifications



DELL 23 MONITOR : E2318H

Display

Model number	E2318H
Viewable image size (diagonal)	58.42 cm (23.0 Inches)
Active display area	
Horizontal	509.18 mm (20.05 inches)
Vertical	286.42 mm (11.28 inches)
Maximum resolution	1920 x 1080 at 60Hz
Aspect ratio	16:9
Pixel pitch	0.265 mm x 0.265 mm
Pixels per inch (PPI)	96
Brightness (typical)	250 cd/m ²
Color gamut (typical)	85% (CIE 1976), 72% (CIE 1931)
Color depth	16.7 million colors
Contrast ratio (typical)	1000: 1
Viewing angle (typical) (vertical/horizontal)	178° x 178°
Response time (typical)	5 ms (gray to gray - fast mode) 8 ms (gray to gray - normal mode)
Panel technology	In-plane switching, antiglare with 3H hardness
Backlight	LED
Dell Display Manager	Yes
Optional soundbar	AC511

Connectivity

Connectors	1 x DisplayPort (ver 1.2), 1 x VGA
-------------------	------------------------------------

Design features

Stand	Tilt (-5° to 21°)
Security	Security lock slot (cable lock sold separately), Anti-theft stand lock slot (to panel)
VESA mounting support	100 mm

Power

AC input voltage/frequency/current	100 to 240 VAC / 50 or 60 Hz ± 3Hz / 1.0 A (typical)
Power consumption (typical)	20W
Power consumption (ENERGY STAR®)	54 kWh
Power consumption (standby/sleep mode)	< 0.3W

Dimensions (with stand)

Height	415.0 mm (16.34 inches)
Width	544.8 mm (21.45 inches)
Depth	180.0 mm (7.09 inches)

Weight

Weight (panel only)	3.17 kg (6.99 lb)
Weight (with stand)	3.89 kg (8.58 lb)
Shipping weight	5.47 kg (12.06 lb)

Standard service plan	3 Years Advanced Exchange Service ¹ & Limited Hardware Warranty ²
------------------------------	---

Environmental compliance	ENERGY STAR®, EPEAT® Gold ³ , TCO Certified Displays, RoHS Compliant
---------------------------------	---

What's in the box?

Components

- Monitor
- Stand riser
- Stand base
- VESA screw cover

Cables

- 1 x DisplayPort cable
- Power cable

Documentation

- Quick Setup Guide
- Drivers and documentation media
- Safety and regulatory information

Adjustability and connectivity



DELL 23 MONITOR : E2318H

Easily tilt the panel to your preferred viewing position.



Tilt

Connectivity



- A AC power
- B DisplayPort in
- C VGA
- D Dell soundbar mounting slots

* Dell monitors are #1 worldwide for 4 consecutive years! Source: IDC Worldwide PC Monitor Tracker (4Q16)

- 1 Advanced Exchange Service: Replacement part/unit dispatched, if needed, following completion of phone/online diagnosis. Fee charged for failure to return defective unit. Availability varies. Other conditions apply.
- 2 For a copy of the Limited Hardware Warranty, write Dell USA LP, Attn: Warranties, One Dell Way, Round Rock, TX 78682 or see Dell.com/warranty.
- 3 EPEAT Gold registered in the U.S. EPEAT registration varies by country. See www.epeat.net for registration status by country.

