

Lenovo L24q-30 65FBGCC1US

Product

Lenovo L24q-30

Region

NA,LA

Color

Raven Black

Panel

In-Plane Switching

Display Size

23.8"

View Area

526.85x296.35 mm

Resolution

2560x1440

Aspect Ratio

16:9

Pixel Pitch

0.2058x0.2058 mm

Dot / Pixel Per Inch

123.4 dpi

Brightness

300 nits

Contrast Ratio

1000:1

Pixel Response Time

4 ms (extreme mode) / 6 ms/14 ms (typical/off mode)

Color Gamut

99% sRGB

View Angle (H / V)

178 / 178

Stand

Tilt Stand

Side Bezel Width

2 / 21.4 mm

Dimensions with Stand (HxWxD)

402.7x539.8x190 mm

Power Consumption (Typical / Maximum)

20W / 31W

Power Adapter

Integrated

Weight (Including Stand)

7.72 lb / 3.5 kg

Warranty

1-year

ENERGY STAR

ENERGY STAR 8.0

TCO

TCO 8.0

EPEAT

Silver

Low Blue Light / Eye Comfort

Eye Comfort

Presets / User Settings

20

On Screen Display

OSD, 8 Languages

USB Port

None

Speaker

None

Camera

None

Multiple Input

HDMI, DP

Monitor Cable

HDMI

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Operating System

Support Windows 7, Windows 10

Ann Date (mm/yy)

11/19



WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo L24q-30



DISPLAY

Panel Size

23.8-inch

Screen Dimensions

526.85 mm x 296.35 mm

Panel Type

3-side NearEdgeless
In-Plane Switching

Backlight

WLED

Aspect Ratio

16:9

Resolution

2560 x 1440

Pixel Pitch

0.2058 x 0.2058 mm

Dot/Pixel Per Inch (DPI/PPI)

123.4

Viewing Angle (H x V @ CR 10:1)

178° / 178°

Response Time

4ms (extreme mode)

Refresh Rate

75 Hz

Brightness (typical)

240 cd/m²

Brightness (peak)

300 cd/m²

Contrast Ratio (typical)

1000:1

MECHANICAL

Dynamic Contrast Ratio (typical)

3M:1

Color Gamut

> 99% sRGB

Color Support (typical)

16.7 Million

Anti-glare

Yes

CONNECTIVITY

Video Signal

1 x HDMI 1.4
1 x DP 1.2

Audio Signal

1 x Audio Out (3.5 mm)

SPECIAL FEATURES

Sync Technology

AMD FreeSync™

POWER

Power Consumption (typical/max)

20W / 31W

Power Consumption Sleep/Off Mode

< 0.5W

Power Consumption Switch-off Mode

< 0.3W

Voltage Required

AC 100 to 240 V (50/60 Hz)

MECHANICAL

Tilt Angle (front/back)

-5° / 22°

VESA Mount Capability

Yes (100 x 100 mm)

Kensington™ Lock Slot

Yes

Cable Management

Yes

Bezel Color

Raven Black

Bezel Width (side)

2 mm

Bezel Width (top/bottom)

2 / 21.4 mm

DIMENSION

Size Packed (D x H x W, mm/inch)

405 x 122 x 639 mm /
15.94 x 4.80 x 25.16 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)

190 x 402.7 x 539.8 mm /
7.48 x 15.85 x 21.25 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position)

190 x 402.7 x 539.8 mm /
7.48 x 15.85 x 21.25 inches

Weight Packed (kg/lb)

5.25 kg / 11.57 lbs.

Weight Unpacked (kg/lb)

3.50 kg / 7.72 lbs.

WHAT'S IN THE BOX

Monitor with stand

1 x Power cable (1.8 m)

1 x HDMI cable (1.8 m)

Quick setup guide

CERTIFICATION

ENERGY STAR® Rating

8.0

CCC

Yes

TCO

8.0

EPEAT™

Silver

RoHS (EU 2002/95/EC)

Yes

Windows Certification

Window 7, Windows 10

China Energy Efficiency Standard

Tier 1

TÜV Eye Comfort

Yes



Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2019 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Lenovo L24q-30

Lenovo

