



MEDICAL KEYBOARD

Designed for Medical
Applications

FEATURES

- 96 Keys
- Cleanable, Sealed Keyboard
- Withstands Most Hospital Grade Cleaners
- Wrapped in Silicone Rubber
- IP68 Rated
- VESA Mounting Holes
- Scissor Switch Technology
- Low Profile
- Light Weight
- Optional: Backlight
- 10 Million Actuations Per Key

SPECIFICATIONS

- Storage Temperature: -40C to +70C
- Operating Temperature: 0C to +70C
- Supply Voltage: 5V + 5%/-10 Through USB Port
- Current Consumption: Max 100mA
- Dimensions: 11.10 x 5.30 x 0.59 in (281.94 x 134.53 x 15.00 mm)
- Warranty: 1 Year

INTERFACE

- USB
- Wireless
- Bluetooth

CLEAN KEY INSTRUCTIONS

1. Fn + Shift (Clean On / Off)
2. "Clean" LED Will Illuminate, Indicating Cleaning Mode
3. To Turn Off, Repeat Step 1
4. "Clean" LED Will Turn Off, Indicating Typing Mode

TG3 PART NUMBER	DESCRIPTION
KBA-CK96-BNUN-US	Black, USB, No Backlight
KBA-CK96-WNUN-US	White, USB, No Backlight
KBA-CK96-BNUW-US	Black, USB, White Backlight
KBA-CK96-WNUG-US	White, USB, Green Backlight
KBA-CK96-BNBN-US	Black, Bluetooth, No Backlight
KBA-CK96-WNBN-US	White, Bluetooth, No Backlight