

ideacentre A340-22AST F0EQ006KUS

Product

ideacentre A340-22AST

Region

NA

Country/Region

USA

Machine Type

F0EQ

Processor

AMD A9-9425 (2C, 3.1 / 3.7GHz, 1MB L2)

Graphics

Integrated AMD Radeon R5 Graphics

Chipset

AMD SoC Platform

Memory

1x 8GB DIMM DDR4-2666

Storage

128GB SSD M.2 2242 PCIe NVMe + 1TB HDD 5400rpm
2.5"

Optical

None

Media Reader

3-in-1

Display

21.5" FHD (1920x1080) WVA 250nits

Touchscreen

10-point Multi-touch

Camera

720p

Speaker

3Wx2

Ethernet

Integrated 100/1000M

Microphone

Mono

Stand

AIO Stand

WLAN + Bluetooth

11ac, 1x1 + BT4.0

Color

Business black

Keyboard

USB Calliope Keyboard, Black, English

Mouse

USB Calliope Mouse, Black

Power Supply

65W Adapter Black

Operating System

Windows 10 Home 64, English

Bundled Software

None

Base Warranty

1-year, Mail-in

Bundled Service

None

EAN / UPC

194778331081

End of Support

2021-02-14

Announce Date

2020-01-15

Notes:**California Electronic Waste Recycling Fee**


In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

PSREF <https://psref.lenovo.com>
Visit psref website for the latest version of Product Specifications Reference.
© Lenovo, 2020. All rights reserved.



AMD

Lenovo

ideacentre A340-22AST Platform Specifications

Product Specifications Reference (PSREF)

Processor	AMD® A4, A6, A9, A10 or A12 series APUs						Power adapter	65 watts PSU, 100V-240V
	APU	Cores	Frequency (Base/Max)	Cache	Memory Type	Integrated Graphics	Limited warranty	<i>Some: 1-year, mail-in service</i> <i>Some: 1-year or 2-year, depot service</i>
	A4-9125	2	2.3 GHz / 2.6 GHz	1 MB	DDR4-2133	Radeon™ R3	Preload	Preloaded operating system <i>Some: Windows® 10 Home 64</i> Preinstalled software includes but not limited to the following: <ul style="list-style-type: none">• Tangram• Lenovo® Application Explorer• Microsoft Office Trial• PowerDVD/Power2Go• McAfee® LiveSafe™ trial
	A6-9225	2	2.6 GHz / 3.1 GHz	1 MB		Radeon R4		
A9-9425	2	3.1 GHz / 3.7 GHz	1 MB	Radeon R5				
Memory	8GB max / 2666MHz DDR4, one SO-DIMM socket * System automatically clocks down for the processors with lower memory controller							
Storage	<i>Some: SATA 6.0Gb/s, 2.5" wide, 5400 rpm</i> <i>Some: M.2 (2280) SSD / PCIe NVMe, PCIe 3.0 x 4</i> <i>(e.g. 256GB SSD M.2 PCIe NVMe)</i> <i>Some: M.2 (2242) SSD / PCIe NVMe, PCIe 3.0 x 2</i> <i>(e.g. 128GB SSD M.2 PCIe NVMe)</i>							
Optane Memory	None							
SATA controller	Serial ATA, SATA 6.0Gb/s support							
Optical (opt)	SATA connector, DVD±RW, 9.0mm high, tray-in							
Media reader	3-in-1 reader (SD, SDHC, SDXC)							
Graphics	AMD Radeon R3, R5 or R7 Graphics in processor, uses main memory, DirectX 12, one VGA, one HDMI							
Display	21.5" (546.1mm) FHD (1920x1080) color, WVA, LED backlight, anti-glare, borderless, 16:9 aspect ratio, 250 nits							
Multi-touch (opt)	Multi-touch (10-point), Advanced In-Cell Touch (AIT) technology							
Camera	720p HD, autofocus							
Light sensor	None							
Controls	Power button, optical drive eject button, camera cover slider							
Chipset	AMD SoC (System on Chip) platform							
Ports*	<i>Rear:</i> Two USB 2.0, one USB 3.1 Gen1, power connector, Ethernet (RJ-45), HDMI-out <i>Left:</i> One USB 3.1 Gen1, headphone / microphone combo jack (3.5mm), media card reader <i>Right:</i> None <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i>							
Audio support	HD Audio, stereo speakers with Dolby® Audio™ certification, 3W x 2, monaural microphone							
WLAN	802.11ac wireless, Wi-Fi + Bluetooth 4.0 combo adapter, 1x1, M.2 card							
Bluetooth™	Bluetooth 4.0 wireless, integrated in Wi-Fi + Bluetooth combo adapter							
Ethernet	Gigabit Ethernet connection							
Remote control	None							
Security	Power-on password, administrator password							
Security chip	None							
Keyboard (opt)	<i>Some: Lenovo Calliope Keyboard (USB connector), black or white</i> <i>Some: Lenovo Calliope Wireless Keyboard, black or white</i>							
Mouse (opt)	<i>Some: Lenovo Calliope Mouse (USB connector), black or white</i> <i>Some: Lenovo Calliope Wireless Mouse, black or white</i>							
Mechanical	● Business black or foggy white color							
		Dimensions (WxDxH)		Max weight (lb / kg)		Adjustments		
	With stand	19.31 X 7.28 X 16.49 (inch); 490.5x 185 x 418.88 (mm)		11.64 / 5.28		Tilt: 25° back, -5° forward		

Lenovo™

ideacentre A340-22AST



AMD



AMD



AMD



AMD



AMD



AMD