




ThinkVision P24q

A BUSINESS MONITOR THAT FITS EVERY WORKSTYLE



Lenovo

EVERYDAY COMPUTING MADE EASY

Designed to fit into any workspace, the ThinkVision P24q-20 is packed with productivity features that boost efficiency. When collaborating, or in a multiscreen setup, this 23.8-inch monitor enhances your viewing experience thanks to its QHD resolution, In-Plane Switching (IPS), and 3-side NearEdgeless bezels. Multiple color gamuts—sRGB, BT.709, and DCI-P3—and factory calibration ensure outstanding visual quality and impressive color accuracy. Now, say goodbye to tired, strained eyes as the ThinkVision P24q-20 is TÜV Rheinland Eye Comfort certified, ensuring you work without fatigue.



Vivid Display From Any Direction

Sporting a 3-side NearEdgeless IPS panel, the monitor's QHD resolution packs 1.77 times the pixels than Full HD, giving you more screen real estate and allowing you to see and do more. Carry out everyday tasks with clarity and precision. 99% sRGB, 99% BT.709, and 84% DCI-P3 color ranges, and factory color calibration (avg. Delta E<2) offer vibrant and striking image quality, ensuring color consistency throughout.



Impactful Productivity

The ThinkVision P24q-20 is engineered to improve efficiency—this is a monitor synonymous with flexibility, functionality, collaboration, and multitasking. Show off your work by daisy-chaining effectively to create a multi-monitor setup. Connect with computers and peripherals seamlessly with an array of USB ports (upstream and downstream) on offer.



Space-saving Design for Clutter-free Desk

The tilt, lift, pivot, and swivel functionality allows you to customize the ThinkVision P24q-20 the way you want it. A higher lift range ensures minimal neck and back strain. With its cable management, minimized square base, and integrated phone holder you get an organized and uncluttered desk space. With TÜV Rheinland eye comfort certification, the monitor assures minimal eye fatigue.

*Up to 80W power delivery to compatible devices by USB Type-C

ThinkVision P24q-20

DISPLAY

Panel Size

23.8-inch

Screen Dimensions

526.85 mm x 296.35 mm

Panel Type

3-side NearEdgeless
In-Plane Switching

Backlight

WLED

Aspect Ratio

16:9

Resolution

2560 x 1440

Pixel Pitch

0.2058 x 0.2058 mm

Dot/Pixel Per Inch (DPI/PPI)

123

Viewing Angle (H x V @ CR 10:1)

178° / 178°

Response Time

4ms (extreme mode)
6ms (normal mode)

Refresh Rate

60 Hz

Brightness (typical)

300 cd/m²

Contrast Ratio (typical)

1000:1

Dynamic Contrast Ratio (typical)

3M:1

Color Gamut

99% sRGB,
99% BT.709,
84 % DCI-P3

Color Support (typical)

16.7 Million

Anti-glare

Yes

CONNECTIVITY

Video Signal

1 x HDMI 1.4
1 x DP 1.2
1 x DP 1.2 (out)

Audio Signal

1 x Audio Out (3.5 mm)

USB Hub

Yes

USB Upstream

1 x USB3.1 Gen1 Type-B

USB Downstream

4 x USB3.1 Gen1 (1 x BC1.2)

SPECIAL FEATURES

Factory Calibration

Yes (Avg. Delta E<2)

POWER

Power Consumption (typical/max)

20W / 61W

Power Consumption Sleep/Off Mode

≤ 0.5W

Power Consumption Switch-off Mode

≤ 0.3W

ENERGY STAR Power Consumption

(P_{on}/E_{TEC})

16.04W / 51.61kWh

Power Supply

Internal

Voltage Required

AC 100 to 240 V (47-63 Hz)

MECHANICAL

Tilt Angle (front/back)

-5° / 35°

Swivel Angle (left/right)

+45° / -45°

Lift (Max range)

150 mm

Pivot

-90° / 90°

VESA Mount Capability

Yes (100 X 100 mm)

Kensington Lock Slot

Yes

Cable Management

Yes

Bezel Color

Raven Black

Bezel Width (side)

2.0 mm

Bezel Width (top/bottom)

2.0 / 21.4 mm

DIMENSION

Size Packed (D x H x W, mm/inch)

620 x 149 x 423 mm /
24.4 x 5.9 x 16.7 inches

Size Unpacked w/ Stand

(D x H x W, mm/inch) (lowest position)

205 x 420 x 539.8 mm /
8.07 x 16.5 x 21.3 inches

Size Unpacked w/ Stand

(D x H x W, mm/inch) (highest position)

205 x 570 x 539.8 mm /
8.07 x 22.4 x 21.3 inches

Size Unpacked w/o Stand

(head only) (D x H x W, mm/inch)

44.6 x 325.7 x 539.8 mm /
1.8 x 12.8 x 21.3 inches

Min. Distance from Table to Panel

(lowest pixel at bottom of screen, mm)

117.9 mm

Max. Distance from Table to Panel

(highest pixel at top of screen, mm)

415 mm

Weight Packed (kg/lbs.)

8.1 kg / 17.86 lbs.

Weight Unpacked (kg/lbs.)

6.18 kg / 13.6 lbs.

Weight (monitor head only) (kg/lbs.)

3.85 kg / 7.89 lbs.

Full Container Load (40' STD / 20' STD)

1395 / 645 units

WHAT'S IN THE BOX

MONITOR WITH STAND

1 X POWER CABLE (1.8 M)

1 X DP CABLE (1.8 M)

1 X USB TYPE-A TO TYPE-B CABLE (1.8 M)

FACTORY CALIBRATION REPORT

QUICK SETUP GUIDE

CERTIFICATION

ENERGY STAR Rating

8.0

CCC

Yes

TCO

8.0

TCO Edge

2.0

EPEAT

Silver

RoHS (EU 2002/95/EC)

Yes

Windows Certification

Windows 7, Windows 10

China Energy Efficiency Standard

Tier 1

TÜV Rheinland Eye Comfort

Yes



Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: ~ 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2020 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Lenovo