

# IdeaPad 5 15ARE05 81YQ0008US

**Product**

IdeaPad 5 15ARE05

**Region**

NA

**Country/Region**

USA

**Machine Type**

81YQ

**Processor**

AMD Ryzen 5 4500U (6C / 6T, 2.3 / 4.0GHz, 3MB L2 / 8MB L3)

**Graphics**

Integrated AMD Radeon Graphics

**Chipset**

AMD SoC Platform

**Memory**

8GB Soldered DDR4-3200

**Storage**

512GB SSD M.2 2242 PCIe NVMe 3.0x2

**Display**

15.6" FHD (1920x1080) TN 250nits Anti-glare

**Touchscreen**

None

**Optical**

None

**Media Reader**

4-in-1 Card Reader

**Ethernet**

None

**WLAN + Bluetooth**

11ax, 2x2 + BT5.1

**Case Material**

Aluminum (Top) + PC / ABS (Bottom)

**Camera**

720p

**Microphone**

2x, Array

**Color**

Platinum Grey

**Keyboard**

Backlit, English (US)

**Fingerprint Reader**

Touch Style

**TPM**

FW TPM 2.0

**Battery**

Integrated 57Wh

**Power Adapter**

65W Round Tip

**Operating System**

Windows 10 Home 64, English

**Bundled Software**

Office Trial

**Base Warranty**

1-year, Depot

**Bundled Service**

None

**EAN / UPC / JAN**

194778022347

**End of Support**

2026-04-30

**Announce Date**

2020-03-30

**Notes:****California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

**L** [WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



AMD

Lenovo™

# IdeaPad 5 15ARE05 Platform Specifications

Product Specifications Reference (PSREF)



Processor	<p>AMD Ryzen™ Mobile Processors with Radeon™ Graphics</p> <table border="1"> <thead> <tr> <th>Processor Number</th> <th># of Cores</th> <th># of Threads</th> <th>Base Frequency</th> <th>Max Turbo Frequency</th> <th>Cache</th> <th>Memory Types</th> <th>Processor Graphics</th> </tr> </thead> <tbody> <tr> <td>Ryzen 3 4300U</td> <td>4</td> <td>4</td> <td>2.7 GHz</td> <td>3.7 GHz</td> <td>2MB/L2 4MB/L3</td> <td rowspan="4">DDR4-3200</td> <td rowspan="4">AMD Radeon Graphics</td> </tr> <tr> <td>Ryzen 5 4500U</td> <td rowspan="2">6</td> <td>6</td> <td>2.3 GHz</td> <td>4.0 GHz</td> <td rowspan="2">3MB/L2 8MB/L3</td> </tr> <tr> <td>Ryzen 5 4600U</td> <td>12</td> <td>2.1 GHz</td> <td>4.0 GHz</td> </tr> <tr> <td>Ryzen 7 4700U</td> <td rowspan="2">8</td> <td>8</td> <td>2.0 GHz</td> <td>4.1 GHz</td> <td rowspan="2">4MB/L2 8MB/L3</td> </tr> <tr> <td>Ryzen 7 4800U</td> <td>16</td> <td>1.8 GHz</td> <td>4.2 GHz</td> </tr> </tbody> </table>	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics	Ryzen 3 4300U	4	4	2.7 GHz	3.7 GHz	2MB/L2 4MB/L3	DDR4-3200	AMD Radeon Graphics	Ryzen 5 4500U	6	6	2.3 GHz	4.0 GHz	3MB/L2 8MB/L3	Ryzen 5 4600U	12	2.1 GHz	4.0 GHz	Ryzen 7 4700U	8	8	2.0 GHz	4.1 GHz	4MB/L2 8MB/L3	Ryzen 7 4800U	16	1.8 GHz	4.2 GHz	<p>Media reader Ports</p> <p>4-in-1 media reader (MMC, SD, SDHC, SDXC) Two USB 3.2 Gen 1 (one Always on) one USB 3.2 Type-C Gen 1 (with the function of Power Delivery and DisplayPort), HDMI 1.4b, 4-in-1 media reader (MMC, SD, SDHC, SDXC), AC power adapter jack, headphone / microphone combo jack <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i></p> <p>Camera</p> <p>HD720p, 1.0MP resolution, with privacy shutter, fixed focus, bump camera, with dual array microphone</p> <p>Audio support</p> <p>HD Audio, Dolby Audio™, stereo speakers, 2W x 2, dual array microphone, headphone / microphone combo jack</p> <p>Keyboard Touchpad</p> <p>6-row, multimedia Fn keys, numeric keypad, optional LED backlight Buttonless Mylar surface multi-touch touchpad</p> <p>Security</p> <p>Power-on password, hard-disk password, supervisor password Security chip Firmware TPM 2.0 integrated in chipset Fingerprint reader <i>Optional</i>: Touch style fingerprint reader on power button</p> <p>Battery</p> <p>Integrated Li-ion 45Wh, 57Wh or 70Wh battery,</p> <table border="1"> <thead> <tr> <th>Battery</th> <th>Support Rapid charge (charge up to 80% in 1hr)</th> </tr> </thead> <tbody> <tr> <td>45Wh</td> <td>with 65W or 95W AC dapter</td> </tr> <tr> <td>57Wh</td> <td>with 65W or 95W AC dapter</td> </tr> <tr> <td>70Wh</td> <td>with 95W AC adapter</td> </tr> </tbody> </table> <p>Max battery life</p> <p><i>MobileMark® 2014</i>: 11.5 hr (45Wh), 14 hr (57Wh) or 17 hr (70Wh) <i>* Battery life varies significantly with settings, usage, &amp; other factors</i></p> <p>AC adapter</p> <p>65W round tip or 95W USB-C AC adapter</p> <p>Preload (<i>optional</i>) <i>Preloaded operating system</i></p> <ul style="list-style-type: none"> <li>Windows® 10 Home 64</li> <li>Windows 10 Home in S mode</li> <li>Windows 10 Pro 64</li> </ul> <p><i>Preloaded applications (only some listed)</i></p> <ul style="list-style-type: none"> <li>Microsoft Office Trial (with 30-day license)</li> <li>Microsoft Office Home and Student 2019</li> <li>Microsoft Office Home and Business 2019</li> <li>Microsoft Office Professional 2019</li> <li>Microsoft Office Personal 2019</li> </ul> <p>Limited warranty</p> <p><i>One of the following, configurable by model:</i></p> <ul style="list-style-type: none"> <li>1-year depot repair service</li> <li>1-year depot with 2-year system board repair service</li> <li>2-year/1-yr battery depot repair service</li> </ul> <p>Environment</p> <p>ENERGY STAR® 8.0; ErP lot3; RoHS-compliant</p>	Battery	Support Rapid charge (charge up to 80% in 1hr)	45Wh	with 65W or 95W AC dapter	57Wh	with 65W or 95W AC dapter	70Wh	with 95W AC adapter
Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics																																							
Ryzen 3 4300U	4	4	2.7 GHz	3.7 GHz	2MB/L2 4MB/L3	DDR4-3200	AMD Radeon Graphics																																							
Ryzen 5 4500U	6	6	2.3 GHz	4.0 GHz	3MB/L2 8MB/L3																																									
Ryzen 5 4600U		12	2.1 GHz	4.0 GHz																																										
Ryzen 7 4700U	8	8	2.0 GHz	4.1 GHz	4MB/L2 8MB/L3																																									
Ryzen 7 4800U		16	1.8 GHz	4.2 GHz																																										
Battery	Support Rapid charge (charge up to 80% in 1hr)																																													
45Wh	with 65W or 95W AC dapter																																													
57Wh	with 65W or 95W AC dapter																																													
70Wh	with 95W AC adapter																																													
Graphics	<p>AMD Radeon Graphics in processor; supports external digital monitor via HDMI or USB-C; supports three independent displays; Max resolution: 3840x2160@30Hz (HDMI); 3840x2160@30Hz (USB-C)</p>																																													
Chipset	AMD SoC (System on Chip) platform																																													
Memory	4GB, 8GB or 16GB / 3200MHz DDR4, soldered to systemboard, no socket																																													
Display	<p><i>One of the following, configurable by model:</i></p> <table border="1"> <thead> <tr> <th>Size</th> <th>Resolution</th> <th>Type</th> <th>Surface</th> <th>Brightness</th> <th>Aspect Ratio</th> <th>Color Gamut</th> </tr> </thead> <tbody> <tr> <td>15.6"</td> <td>FHD (1920x1080)</td> <td>TN</td> <td>Anti-glare</td> <td>250 nits</td> <td>16:9</td> <td>45%</td> </tr> <tr> <td>15.6"</td> <td>FHD (1920x1080)</td> <td>IPS</td> <td>Anti-glare</td> <td>300 nits</td> <td>16:9</td> <td>45%</td> </tr> <tr> <td>15.6"</td> <td>FHD (1920x1080)</td> <td>IPS</td> <td>Anti-glare</td> <td>300 nits</td> <td>16:9</td> <td>100%</td> </tr> </tbody> </table>	Size	Resolution	Type	Surface	Brightness	Aspect Ratio	Color Gamut	15.6"	FHD (1920x1080)	TN	Anti-glare	250 nits	16:9	45%	15.6"	FHD (1920x1080)	IPS	Anti-glare	300 nits	16:9	45%	15.6"	FHD (1920x1080)	IPS	Anti-glare	300 nits	16:9	100%																	
Size	Resolution	Type	Surface	Brightness	Aspect Ratio	Color Gamut																																								
15.6"	FHD (1920x1080)	TN	Anti-glare	250 nits	16:9	45%																																								
15.6"	FHD (1920x1080)	IPS	Anti-glare	300 nits	16:9	45%																																								
15.6"	FHD (1920x1080)	IPS	Anti-glare	300 nits	16:9	100%																																								
Multi-touch ( <i>opt</i> )	On-cell touch, support 10-finger gesture																																													
Storage	<p><i>Up to 2 drives (one HDD and one M.2 SSD):</i></p> <ul style="list-style-type: none"> <li>HDD / SATA 6.0Gb/s, 2.5" wide, 7mm high</li> <li>M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 2</li> <li>M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4</li> </ul>																																													
Optical ( <i>optional</i> )	External DVD burner, 9.5mm high																																													
Ethernet	None																																													
WLAN + Bluetooth™	<p><i>One of the following, configurable by model:</i></p> <ul style="list-style-type: none"> <li>802.11ac 2x2 Wi-Fi + Bluetooth 5.1, M.2 Card</li> <li>802.11ax 2x2 Wi-Fi + Bluetooth 5.1, M.2 Card</li> </ul>																																													
Dimensions	<p><i>Aluminum bottom model:</i> 14.04" x 9.18" x 0.67"; 356.67mm x 233.13mm x 16.9mm</p> <p><i>Plastic bottom model:</i> 14.04" x 9.18" x 0.7"; 356.67mm x 233.13mm x 17.9mm</p>																																													
Weight	Starting at 3.66 lb / 1.66 kg																																													
Case color	Graphite grey, light teal or platinum grey																																													
Case material	<p><i>Display cover:</i> Aluminum</p> <p><i>Bottom:</i> PC/ABS plastic or Aluminum</p>																																													

Note: The specifications above may not be available in all regions.

Lenovo  
March 2020

# IdeaPad 5 15ARE05



AMD



AMD



AMD



AMD



AMD



AMD