DELL

DELL ULTRASHARP 27 4K USB-C MONITOR | U2720Q

# True, superior color.

VESA CERTIFIED
DisplayHDR™ 400

4K

EXCEPTIONAL VISUALS

Experience true color and captivating details on this 27" 4K monitor with a wide color coverage, including 95% DCI-P3.

THE POWER OF USB-C

Single cable USB-C delivers up to 90W of power while transmitting data and video signals.

CRAFTED FOR PRODUCTIVITY

Work efficiently with improved Dell Display Manager, a fully adjustable stand and virtually borderless InfinityEdge.

TRUSTED RELIABILITY

World's number 1 monitor company.[1] Backed by renowned Dell reliability.

True, superior color.

EXCEPTIONAL VISUALS

Exceptional color: Get true color reproduction with a wide color coverage including 99% sRGB, 99% Rec. 709 and 95% DCI-P3. With approximately 25% larger color coverage than sRGB, DCI-P3 is becoming a color standard when creating and viewing content.

Visually stunning: Experience outstanding color gradient and precision in more shades on this VESA DisplayHDR™ 400 monitor with a color depth 1.07 billion colors and high contrast ratio of 1300:1.

See more: Capture every detail with 4K UHD (3840x2160) resolution and a high pixel density of 163ppi. That's 4 times more details than Full HD.

Accurate color, out of the box: Your monitor is factory calibrated at 99% sRGB to an accuracy of Delta-E < 2 for accurate colors right from the start.

THE POWER OF USB-C

USB-C charging: Get up to 90W of power delivery — the highest power delivery in a 27" 4K USB-C monitor[2] — plus uninterrupted charging with the Always On Power Delivery feature for continuous power charging to your system, even when the monitor is turned off.

Get to work faster: Conveniently placed, quick access USB-C and USB 3.0 ports let you easily charge and connect to a variety of devices all while reducing cable clutter.

IMPROVED DELL DISPLAY MANAGER

Productive at every level: Dell Display Manager's (DDM)[3] Easy Arrange feature lets you quickly tile and view your applications side by side across one or more connected screens for multitasking efficiency. And with the improved DDM, you'll get even more preset layouts.

The key to convenience: Shortcut keys can save you even more time, letting you easily configure your display management settings so you can get to work faster.

More ways to manage: Asset management reports allow IT managers to quickly capture and track monitor information as well as configure multiple monitors at once through a single setup.

CRAFTED FOR PRODUCTIVITY

More room to work: Make the most of your limited desk space with the compact base.

Virtually borderless: Work with an uninterrupted view across multiple monitors with InfinityEdge. And, with a Dell dual monitor set up, you can increase your productivity by up to 21%.[4]

Flexibility for all-day comfort: With the ability to tilt, swivel, pivot and adjust the height of your monitor to fit your needs, you can stay comfortable all day.

Energy efficient and Eco-conscious: Designed with the environment in mind, this energy efficient monitor meets the latest regulatory and environmental standards such as ENERGY STAR® and EPEAT® and is packed in Styrofoam-free packaging.

THANK YOU FOR MAKING DELL MONITORS #1 WORLDWIDE[1]

Peace of mind: Dell Premium Panel Exchange allows a free monitor replacement during the Limited Hardware Warranty[5] period even if only one bright pixel is found.

Minimize downtime: Your monitor comes with a 3-year Advanced Exchange Service[6] so that if a replacement becomes necessary, it will be shipped to you the next business day during your 3-year Limited Hardware Warranty.

Get a higher level of support: Upgrade to 24 X 7, in-region technical phone support from qualified engineers with Dell ProSupport option.[7]

Monitor	Dell UltraSharp 27 4K USB-C Monitor – U2720Q
Diagonal Image Size	68.47 cm (27 inches)
Active Display Area	
Horizontal	596.74 mm (23.49 inches)
Vertical	335.66 mm (13.21 inches)
Maximum Preset Resolution	3840 x 2160 at 60Hz
Aspect Ratio	16:9
Pixel Pitch	0.1554 mm x 0.1554 mm
Pixels Per Inch (PPI)	163
Brightness	350 cd/m² (typical)
Color Gamut	99% sRGB, 99% Rec 709, 95% DCI-P3
Calibration Accuracy	Delta-E < 2 (average)
Color Depth	1.07 billion colors
Contrast Ratio	1300: 1 (typical)
Viewing Angle	178° vertical / 178° horizontal
Response Time	5ms (gray to gray) fast mode; 8ms (gray to gray) normal mode
Panel Technology	In-Plane Switching Technology
Backlight Technology	LED
Display Screen Coating	Anti-glare treatment of the front polarizer (3H) hard coating
ComfortView with Flicker-free Screen	Yes
Dell Display Manager	Yes with Dell Easy Arrange and other key features
Remote Asset Management	Yes, via Dell Command	Monitor

Connectivity

Connectors	1 x DP 1.4 (HDCP 1.4/ HDCP 1.2) 1 x HDMI 2.0 (HDCP 1.4/ HDCP 1.2) 1 x USB Type-C (Alternate Mode with DisplayPort 1.4, USB 3.1 upstream port, Power Delivery up to 90W[8]) 2 x USB 3.0 Downstream ports 1 x USB 3.0 with B.C 1.2 charging adaptability of 2 A (Max) 1 x Analog 2.0 Audio Line out (3.5 mm Jack) 1 x USB Type-C Downstream charging port with charging capability up to 3 A (Max)

Design features

Adjustability	Height-adjustable (130 mm), Tilt (-5° to 21°), Swivel (-45° to 45°), Pivot (-90° to 90°)
Security	Security lock slot (security lock not included), anti-theft stand lock slot (to lock stand to monitor using screw)
VESA Mounting Support	VESA mounting holes (100 mm x 100 mm — behind attached VESA cover)

Power

AC Input voltage/frequency/current	100 VAC to 240 VAC / 50 Hz or 60 Hz + 3 Hz / 2.5 A (typical)
Power Consumption (Normal Operation)	33 W (typical), 200 W (maximum)[9]
Power Consumption Stand by/Sleep	Less than 0.3 W

Dimensions (with stand)

Height (Compressed ~ Extended)	395.2 mm ~ 525.2 mm (15.56 inches ~ 20.68 inches)
Width	611.3 mm (24.07 inches)
Depth	185.0 mm (7.28 inches)

Weight

Weight (panel only)	4.4 kg (9.70 lb)
Weight (with stand)	6.6 kg (14.55 lb)
Shipping Weight	9.6 kg (21.16 lb)

Standard Service plan	3 Years Advanced Exchange Service[6] & Limited Hardware Warranty[5], Premium Panel Exchange
Optional Service Plan	Dell ProSupport[7]
Environmental Compliance	ENERGY STAR® certified monitor, EPEAT® registered where applicable[10], RoHS Compliant, TCO Certified displays, BFR/PVC Free (Halogen-free) (excluding external cables), Meets NFPA 99 leakage current requirements, Arsenic-Free glass and Mercury-Free for the panel only

What's in the box?

Components
- Monitor with stand

Cables
- Power Cable
- DP Cable (DP to DP)
- USB Type-C Cable (C to C)
- USB Type-C Cable (C to A)

Documentation
- Quick Setup Guide
- Factory Calibration Report
- Safety and regulatory information

Connectivity and Accessories

DELL ULTRASHARP 27 4K USB-C MONITOR | U2720Q

Purposeful design, built for ergonomic comfort.

Cable management slot

21°   5°
130 mm

Tilt and height adjustable

90°   90°

Pivot

45°   45°

Swivel

Connectivity

1	AC Power	**4**	DisplayPort	**7**	USB Downstream (x2)
2	Security-lock slot	**5**	USB-C/DisplayPort	**8**	Stand Lock
3	HDMI Port	**6**	Audio Line-out[11]		

9 USB Downstream Port (supports BC 1.2)
10 USB-C Downstream Port (supports 3 A)

RECOMMENDED ACCESSORIES

DELL DUAL MONITOR ARM | MDA20

Enjoy toolless installation with Quick Release and the flexibility to pivot, tilt, swivel and adjust the height of each monitor independently. Features a small footprint and neat cable management.

DELL PRO STEREO SOUNDBAR | AE515M

Optimize conference calls and multimedia streaming with exceptional audio clarity. Minimize background noise with the dual mic array and echo-cancelling feature.

DELL PREMIER WIRELESS KEYBOARD AND MOUSE | KM717

Enjoy a uniquely designed, arc-shaped mouse that fits into virtually any workspace and boost productivity with a keyboard that features multi-OS support and popular shortcut keys.

VESA CERTIFIED
DisplayHDR™ 400

ENERGY STAR

epeat

TCO CERTIFIED

v.2 12/2019