

# Lenovo V14 ARE 82DQ000KUS

## Product

Lenovo V14 ARE

## Region

NA

## Country/Region

USA

## Machine Type

82DQ

## TopSeller

TopSeller

## Processor

AMD Ryzen 5 4500U (6C / 6T, 2.3 / 4.0GHz, 3MB L2 / 8MB L3)

## Graphics

Integrated AMD Radeon Graphics

## Chipset

AMD SoC Platform

## Memory

4GB Soldered DDR4-2666

## Storage

1TB HDD 5400rpm 2.5"

## Display

14" FHD (1920x1080) TN 220nits Anti-glare

## Touchscreen

None

## Optical

None

## Media Reader

4-in-1 Card Reader

## Ethernet

None

## WLAN + Bluetooth

11ac, 2x2 + BT5.0

## Case Material

PC / ABS

## Camera

0.3MP

## Microphone

Mono

## Color

Iron Grey, IMR

## Keyboard

Non-backlit, English

## Fingerprint Reader

None

## TPM

FW TPM 2.0

## Battery

Integrated 35Wh

## Power Adapter

65W Round Tip

## Operating System

Windows 10 Pro 64, English

## Bundled Software

Office Trial

## Base Warranty

1-year, Depot

## Bundled Service

None

## EAN / UPC / JAN

194778594639

## End of Support

2026-03-28

## Announce Date

2020-02-28

## Recommended Services

### Best

3Y Premium Care with Onsite upgrade from 1Y Depot/CCI  
(5WS0U55751)

### Better

3Y Onsite upgrade from 1Y Depot/CCI delivery  
(5WS0Q81865)

### Good

3Y Depot/CCI upgrade from 1Y Depot/CCI delivery  
(5WS0Q81869)

## Notes:

### California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:  
<https://www.calrecycle.ca.gov/Electronics/Consumer>



[WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



# Lenovo V14 ARE Platform Specifications

Product Specifications Reference (PSREF)

Processor	AMD Ryzen™ Mobile Processors with Radeon™ Graphics															
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics								
	Ryzen 5 4500U	6	6	2.3 GHz	4.0 GHz	3MB L2 / 8MB L3	DDR4-2666	AMD Radeon Graphics								
	Ryzen 7 4700U	8	8	2.0 GHz	4.1 GHz	4MB L2 / 8MB L3										
Graphics	AMD Radeon Graphics in processor; supports external digital monitor via HDMI; supports dual independent display; Max resolution: 3840x2160@30Hz (HDMI)															
Chipset Memory	AMD SoC (System on Chip) platform 8GB max / 2666MHz DDR4, 4GB memory soldered to systemboard, one DDR4 SO-DIMM socket															
Display	<p><i>One of the following, configurable by model:</i></p> <ul style="list-style-type: none"> <li>• 14.0" (356mm) HD (1366x768), anti-glare, LED backlight, 220 nits, 16:9 aspect ratio</li> <li>• 14.0" (356mm) FHD (1920x1080), anti-glare, LED backlight, 220 nits, 16:9 aspect ratio</li> </ul>															
Multi-touch	None															
Storage	Up to 2 drives (one HDD and one M.2 SSD): <ul style="list-style-type: none"> <li>• HDD / SATA 6.0Gb/s, 2.5" wide, 7mm high</li> <li>• M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 2</li> <li>• M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4</li> </ul>															
Optical	None															
Ethernet	None															
WLAN Bluetooth™	802.11ac 2x2 Wi-Fi + Bluetooth 5.0, M.2 Card Bluetooth 5.0 wireless, integrated in Wi-Fi + Bluetooth combo adapter															
Dimensions	WxDxH: 12.88" x 9.49" x 0.78"; 327.1mm x 241mm x 19.9mm															
Weight	Starting at 3.53 lb / 1.6 kg															
Case color	Iron Grey, IMR or Texture															
Case material	PC/ABS plastic															
<p>Note: The specifications above may not be available in all regions.</p>																
Lenovo April 2020																
Media reader Ports 4-in-1 reader (MMC, SD, SDHC, SDXC) One USB 2.0, two USB 3.1 Gen 1, HDMI 1.4b, 4-in-1 reader (MMC, SD, SDHC, SDXC), headphone / microphone combo jack, AC power adapter jack <small>* Depending on many factors, actual data transfer speed may be lower than theoretical speed.</small>																
Camera Audio support 0.3MP, fixed focus, with monaural microphone HD Audio, Dolby Audio™, stereo speakers, 1.5W x 2, monaural microphone, headphone / microphone combo jack																
Keyboard Touchpad 6-row, spill-resistant, multimedia Fn keys Buttonless Mylar surface multi-touch touchpad																
Security Security chip Firmware TPM 2.0 integrated in chipset																
Fingerprint reader None																
Battery Max battery life Integrated Li-Ion 30Wh or 35Wh battery <small>MobileMark® 2014: 5 hr (30Wh) or 6 hr (35Wh)</small> <small>* Battery life varies significantly with settings, usage, &amp; other factors.</small>																
AC adapter 65W round tip AC adapter																
Preload (opt) <small>Preloaded operating system</small> <ul style="list-style-type: none"> <li>• Windows® 10 Home 64</li> <li>• Windows 10 Pro 64</li> </ul> <small>Preloaded applications (only some listed)</small> <ul style="list-style-type: none"> <li>• Microsoft Office Trial (with 30-day license)</li> <li>• Microsoft Office Home and Student 2019</li> <li>• Microsoft Office Home and Business 2019</li> <li>• Microsoft Office Professional 2019</li> </ul>																
Limited warranty <small>One of the following, configurable by model:</small> <ul style="list-style-type: none"> <li>• 1-year depot repair service</li> <li>• 2-year/1-yr battery depot repair service</li> </ul>																
Environment ENERGY STAR® 8.0; ErP lot3; RoHS-compliant																

# Lenovo V14 ARE

Lenovo

