

## PRO 16T 10M


### All-in-One, One for All.

Space saving and elegant corporate partners for use in the office, at the POS terminal in a shop window that meets the business requirements such as hotel receptions, 24-hour convenience stores, etc.



### Selling Points


- Windows 10 Home / Professional 64-bit Support
- Intel® 10th gen Comet Lake U processor with DDR4 memory
- Dual LAN design provides the second LAN backup and a safer network environment
- Dual COM ports and one printer port for barcode scanner, credit card reader, printer, cash machine
- USB 3.2 Gen1 Type A x 4
- TPM Module: Secure Your Confidential Data (Optional)
- HDD Caddy to expand storage capacity (Optional)
- LED Display and Anti-Glare Touchscreen
- VESA Wall mounting (Optional)



### I/O & Accessory Overview



- |                              |                                    |
|------------------------------|------------------------------------|
| 1. 1x Card Reader            | 6. 2x RJ-45 LAN                    |
| 2. 2x USB 3.1 Gen 1 Type A   | 7. 1x VGA Port                     |
| 3. 1x Line-out/Microphone-in | 8. 2x Serial Port (COM Port)       |
| 4. 2x USB 3.1 Gen 1 Type A   | 9. 1x Parallel Port (Printer Port) |
| 5. 2x USB 2.0 Type A         | 10. 2.5" HDD Caddy                 |



# PRO 16T 10M

<b>Product Name</b>		PRO 16T 10M
<b>Part Number</b>		-
<b>EAN</b>		-
<b>System OS</b>		Windows 10 Support
<b>Processor</b>	Type CPU Frequency / Cache Size CPU FSB/ HT bus / CPU TDP	Intel® Celeron® 5205U 1.90 GHz / 2M Cache 2 / 2 / 15 Watt  Intel® Pentium® Gold 6405U 2.40 GHz / 2M Cache 2 / 4 / 15 Watt
<b>Chipset</b>		Intel® SoC
<b>Touch Panel / Technology</b>		Single-Touch (PRO 16T 10M)
<b>Monitor</b>	Size	344.232mm (H) x 193.536mm(V) ; 39.6cm ,(15.6")
	Resolution	1366 x 768 HD
	Brightness	250cd/m2
	Response	5 ms
	Glare/ Non-Glare	Anti-Glare
	Contrast Ratio	500:1
	Color	16,7 M
	Pixel Pitch	0.252mm (H) x 0.252mm (V)
	Viewing Angle	170° Horizontal, 160° Vertical
<b>VGA</b>	Graphic VRAM	Integrate Intel® UHD Graphics Integrate : Support Intel® Dynamic Video Memory Technology (DVMT) Technology
<b>Memory</b>	Type Configuration Maximum	DDR4 4GB DDR4 SO-DIMM x 2 slots Expandable to 32GB
<b>Storage</b>	Total number of storage Optical Drive	1x M.2 SSD (PCIe), 1x 2.5" HDD, 1x 2.5" HDD Caddy (Optional) -
<b>Audio</b>	Internal Microphone Audio Chipset Speaker	Yes Realtek ALC233 1.5W x 2
<b>Audio Jack</b>	Line-in/ Headphone out	1x Line-out/Microphone-in combo
<b>Communication</b>	Wireless LAN LAN (RJ45) Bluetooth	INTEL 9462AC WIFI (Optional) 2x 10/100/1000 5 (Optional)
<b>I/O</b>	USB (front/ side/ rear q'ty) Card Reader HDMI-in / HDMI-out VGA-in / VGA-out COM Port	6 (0/ USB 3.2 Gen1 Type A x 2 / USB 3.2 Gen1 Type A x 2, USB2.0 x2) 3 in 1 (SD3.0, SD4.0, MMC) - / - - / 1 2
<b>Others I/O</b>		1x Printer Port
<b>Expansion</b>		M.2 2230 (1xWiFi)
<b>TV Tuner</b>		-
<b>Webcam</b>		1.0M
<b>Mechanical and Environmental</b>	Operating, Storage Temperature Operating, Storage Humidity Regulatory Compliance	0- 35° C, -20 – 60° C 0% ~ 85% : 0% ~ 90% EMC compliance: FCC(Class B), CE, VCCI, BSMI, RCM(C-Tick) Safety compliance: UL(CUL), CB/CE
<b>Noise</b>		27dBA
<b>Lock</b>		Kensington Lock
<b>Wake-on-LAN</b>		YES
<b>KB / Mouse</b>		USB KB/Mouse (Optional)
<b>Wall Mount</b>		VESA standard (STD 100*100mm) (Optional)
<b>Power</b>	AC Adaptor	65W
<b>Durability</b>	Project Capacitive Touch (MTBF)	35M times / -
<b>Dimension (W x D x H)</b> <b>Dimension with carton (W x D x H)</b>		399.5 x 69.2 x 313.9 mm (15.73 x 2.72 x 12.36 inch) 528 x 183 x 393 (20.79 x 7.2 x 15.47 inch)
<b>Weight</b> <b>Warranty</b>	Net / Gross Weight	3.94 kg / 5.78 kg; 8.69 lbs / 12.74 lbs Depends on region
<b>Accessories</b>		-