


Key Features

- HDMI and VGA inputs
- VESA mountable
- 50M:1 dynamic contrast ratio
- ViewMode technology
- 16:9 aspect ratio



Product Description

The ViewSonic® VA1903h is a 19" (18.5" viewable) widescreen monitor that delivers value and performance for both home offices and small businesses. Equipped with HDMI inputs, a fast 5ms response time, and a 50M:1 Dynamic Contrast Ratio, the VA1903h is great for a variety of applications ranging from viewing office documents to surfing the web. Featuring a hairline surface finish, this monitor looks great on any desktop. ViewSonic's exclusive ViewMode™ feature provides intuitive presets for optimised screen performance in different applications. In addition, Flicker-Free technology and a Blue Light Filter help to eliminate eyestrain from extended viewing periods for improved productivity. An energy-saving Eco-mode reduces cost of ownership, making the VA1903h a great choice for both government and education.



Visit Us www.viewsonic.com

DISPLAY		POWER		DIMENSIONS (IMPERIAL) (WXHxD)	
Display Size (in.):	19	Eco Mode (Conserve):	9.5W	Packaging (in.):	19.8 x 13.7 x 4.1
Viewable Area (in.):	18.5	Eco Mode (optimized):	12.5W	Physical (in.):	17.2 x 13.5 x 6.7
Panel Type:	TN Technology	Consumption (typical):	15.3W	Physical Without Stand (in.):	17.2 x 10.7 x 1.9
Resolution:	1366 x 768	Consumption (max):	17W	DIMENSIONS (METRIC) (WXHxD)	
Resolution Type:	WXGA	Voltage:	AC 100-240V	Packaging (mm):	502 x 349 x 105
Static Contrast Ratio:	600:1 (typ)	Stand-by:	0.5W	Physical (mm):	438 x 344 x 170
Dynamic Contrast Ratio:	50M:1	Power Supply:	Internal Power Supply	Physical Without Stand (mm):	438 x 271 x 48
Light Source:	LED	ADDITIONAL HARDWARE		GENERAL	
Brightness:	200 cd/m ² (typ)	Kensington Lock Slot:	1	Regulations:	cTUVus, FCC-B, ICES003, CEC, IQC-ST, MK-CoC, Mexico Energy RoHS, WEEE, BIS
Colors:	16.7M	CONTROLS		PACKAGE CONTENTS:	VA1903H x1, 3-pin Plug (IEC C13 / CEE22) x1, VGA Cable (Male-Male) x1, Quick Start Guide x1
Color Space Support:	8 bit (6 bit + FRC)	Physical Controls:	Auto, Left, Right, Menu, Power	Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Aspect Ratio:	16:9	On Screen Display:	Auto Image Adjust, Contrast/Brightness, Input Select, Audio Adjust, Color Adjust, Information, Manual Image Adjust, Setup Menu, Memory Recall	Warranty:	*Warranty offered may differ from market to market
Response Time (Typical Tr+Tf):	5ms	OPERATING CONDITIONS			
Viewing Angles:	90° horizontal, 65° vertical	Temperature:	32°F to 104°F (0°C to 40°C)		
Backlight Life (Hours):	30000 Hrs (Min)	Humidity (non-condensing):	20% to 90%		
Curvature:	Flat	WALL MOUNT			
Refresh Rate (Hz):	60	VESA Compatible:	75 x 75 mm		
Blue Light Filter:	Yes	INPUT SIGNAL			
Flicker-Free:	Yes	Frequency Horizontal:	RGB Analog: 24 ~ 82KHz, HDMI (v1.4): 15 ~ 82KHz		
Color Gamut:	NTSC: 72% size (Typ) sRGB: 102% size (Typ)	Frequency Vertical:	RGB Analog: 50 ~ 75Hz, HDMI (v1.4): 50 ~ 75Hz		
Pixel Size:	0.3 mm (H) x 0.3 mm (V)	VIDEO INPUT			
Surface Treatment:	Anti-Glare, Hard Coating (3H)	Digital Sync:	TMDS - HDMI (v1.4)		
COMPATIBILITY		Analog Sync:	Separate - RGB Analog		
PC Resolution (max):	1366x768	ERGONOMICS			
Mac® Resolution (max):	1366x768	Tilt (Forward/Back):	-3° / 18°		
PC Operating System:	Windows 10/11 certified; macOS tested	WEIGHT (IMPERIAL)			
Mac® Resolution (min):	1366x768	Net (lbs):	4.6		
CONNECTOR		Net Without Stand (lbs):	4		
VGA:	1	Gross (lbs):	6.6		
3.5mm Audio Out:	1	WEIGHT (METRIC)			
HDMI 1.4:	1	Net (kg):	2.1		
Power in:	3-pin Socket (IEC C14 / CEE22)	Net Without Stand (kg):	1.8		
		Gross (kg):	3		