

# ThinkPad T14 Gen 1 (Intel) 20S0002VUS

**Product**

ThinkPad T14 Gen 1 (Intel)

**Region**

NA

**Country/Region**

USA

**Machine Type**

20S0

**TopSeller**

TopSeller

**Processor**

Intel Core i7-10610U (4C / 8T, 1.1 / 4.7GHz, 12MB)

**Graphics**

Integrated Intel UHD Graphics

**Chipset**

Intel SoC Platform

**Memory**

16GB Soldered DDR4-2666

**Storage**

512GB SSD M.2 2280 PCIe NVMe Opal2

**Display**

14" FHD (1920x1080) IPS 300nits Anti-glare

**Touchscreen**

10-point Multi-touch

**Media Reader**

MicroSD Reader

**Ethernet**

100/1000M

**Optical**

None

**WLAN + Bluetooth**

Intel AX201 11ax, 2x2 + BT5.0

**WWAN**

None

**SIM Card**

None

**Smart Card Reader**

None

**Monitor Cable**

None

**Case Material**

PPS / 50% GF (Top) + PA / 50% GF (Bottom)

**Bundled Accessories**

None

**Camera**

720p + IR with ThinkShutter

**Microphone**

2x, Array

**Color**

Black

**Keyboard**

Backlit, English

**Fingerprint Reader**

Touch Style, Match-on-Chip

**NFC**

None

**TPM**

Discrete TPM 2.0

**Battery**

Integrated 50Wh

**Power Adapter**

65W USB-C

**System Management**

Intel vPro

**Operating System**

Windows 10 Pro 64, English

**Bundled Software**

None

**Base Warranty**

3-year, Depot

**Bundled Service**

None

**EAN / UPC / JAN**

195042002027

**End of Support**

2026-06-05

**Announce Date**

2020-05-05

**Recommended Services****Best**

3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + Sealed Battery) (5PS0N73216)

**Better**

3Y Lenovo Support (Premier Support + Keep Your Drive + Sealed Battery) (5PS0N73159)

**Good**

3Y Premier Support Upgrade from 3Y Depot/CCI (5WS0T36152)

**Notes:**

**Battery life** is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

[WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



# ThinkPad T14 Gen 1 (Intel) Platform Specifications

Product Specifications Reference (PSREF)



Processor	10th Generation Intel® Core™ i5 / i7 Processor								Dimensions WxDxH: 12.95" x 8.94" x 0.70"; 329mm x 227mm x 17.9mm	Weight	Models				
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics			HD	FHD	FHD Touch	FHD Low Power	UHD
Graphics	i5-10210U	4	8	1.6 GHz	4.2 GHz	6MB	DDR4-2666	Intel UHD Graphics	Black	Case material Display cover: PPS / 50% GF; Bottom: PA / 50% GF	Smart card reader Optional: Smart card reader				
	i5-10310U			1.6 GHz	4.4 GHz	6MB					Media reader MicroSD card reader				
	i7-10510U			1.8 GHz	4.9 GHz	8MB					Ports Two USB 3.1 Gen 1 (one Always On), one USB 3.1 Type-C Gen 1 (with the function of Power Delivery and DisplayPort), one USB 3.1 Type-C Gen 2 / Thunderbolt 3 (with the function of PD and DP), HDMI 1.4b, Ethernet (RJ-45), nano-SIM card slot (WWAN models), headphone / microphone combo jack, optional smart card reader, microSD card reader, side docking connector, security keyhole * Depending on many factors, actual data transfer speed may be lower than theoretical speed				
	i7-10610U			1.8 GHz	4.9 GHz	8MB					Monitor cable (optional) • Lenovo HDMI to VGA Monitor Adapter • Lenovo USB-C to VGA Adapter • Lenovo USB-C to DisplayPort Adapter				
	i7-10710U	6	12	1.1 GHz	4.7 GHz	12MB					Camera (optional) • HD720p camera with ThinkShutter camera privacy, fixed focus • IR camera and HD720p camera with ThinkShutter camera privacy, fixed focus				
	i7-10810U	1.1 GHz	4.9 GHz	12MB	Audio support HD Audio, Realtek® ALC3287 codec / Dolby® Audio speaker system, 2W x 2 / optional dual array far-field microphone, headphone / microphone combo jack										
Chipset	Intel SoC (System on Chip) platform								Keyboard 6-row, spill-resistant, multimedia Fn keys with Unified Communications controls, optional LED backlight	UltraNav™ TrackPoint® pointing device and buttonless Mylar surface multi-touch touchpad	Security Security chip • Power-on password, hard disk password, supervisor password, security keyhole • Firmware TPM 2.0 integrated in chipset • Discrete TPM 2.0 TCG Certified				
Memory	40GB or 48GB max / 2666MHz DDR4, dual-channel capable, 8GB or 16GB memory soldered to systemboard, one DDR4 SO-DIMM socket * Installed memory is actually 3200MHz but run at 2666MHz due to Intel limitation														
Display	Size	Resolution	Type	Surface	Touch	Brightness	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	System Mgt (opt) Intel vPro Technology Fingerprint reader Optional: Touch style match on chip fingerprint reader on the palm rest NFC (optional) Near Field Communication				
	14.0"	HD (1366x768)	TN	Anti-glare	-	220 nits	16:9	400:1	45%	90°					
	14.0"	FHD (1920x1080)	IPS	Anti-glare	-	250 nits	16:9	700:1	45%	170°					
	14.0"	FHD (1920x1080)	IPS	Anti-glare	Multi-touch	300 nits	16:9	700:1	45%	170°					
	14.0"	FHD (1920x1080) Low Power	IPS	Anti-glare	-	400 nits	16:9	800:1	72%	170°					
	14.0"	FHD (1920x1080) ThinkPad Privacy Guard	IPS	Anti-glare	Multi-touch	500 nits	16:9	1000:1	72%	178°					
	14.0"	UHD (3840x2160) HDR400, Dolby Vision™	IPS	Glossy	-	500 nits	16:9	1500:1	100%	178°					
Multi-touch (opt)	On-cell touch, supports 10-finger gesture														
Storage	<ul style="list-style-type: none"> <li>• M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4</li> <li>• M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 2</li> <li>• Intel Optane™ Memory H10 with Solid State Storage, M.2 2280, PCIe NVMe 3.0 x 4</li> </ul>														
Optical	None														
Ethernet	<i>Non-vPro model:</i> Intel Ethernet Connection I219-V (Jacksonville) <i>vPro model:</i> Intel Ethernet Connection I219-LM (Jacksonville)														
WLAN + Bluetooth™	Intel Wi-Fi 6 AX201, Wi-Fi 2x2 802.11ax + Bluetooth 5.0 * Intel AX201 card supports BT5.1 but is limited to BT5.0 by Windows OS														
WWAN (optional)	<ul style="list-style-type: none"> <li>• Wireless WAN upgradable</li> <li>• Integrated Mobile Broadband 4G LTE-A, Fibocom L850-GL, M.2 card</li> <li>• Integrated Mobile Broadband 4G LTE-A, Fibocom L860-GL, MIMO 2x2, M.2 card</li> <li>* For non-WWAN model, it means the model is NOT WWAN upgradable</li> </ul>														
SIM card (opt)	Gemalto eSIM Card														
Battery	Integrated Li-Polymer 50Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter														
Max battery life	<i>MobileMark® 2014:</i> 16.5 hr <i>MobileMark 2018:</i> 10.5 hr * Battery life varies significantly with settings, usage, & other factors														
AC adapter	<ul style="list-style-type: none"> <li>• 45W USB-C AC adapter</li> <li>• 65W USB-C AC adapter</li> <li>• 65W USB-C slim AC adapter</li> </ul>														
Operating system	Optional: Windows® 10 Home 64 or Windows 10 Pro 64														
Limited warranty (optional)	<ul style="list-style-type: none"> <li>• 1-year depot repair service</li> <li>• 1-year depot with 2-year system board repair service</li> <li>• 1-year limited onsite service</li> <li>• 1-year + 2-year depot repair service</li> <li>• 1-year + 2-year onsite repair service</li> <li>• 3-year/1-yr battery depot repair service</li> <li>• 3-year/1-yr battery limited onsite service</li> </ul>														
Mil-Spec test	MIL-STD-810G military testing														
Environment	EPEAT™ Gold; ENERGY STAR® 8.0; RoHS-compliant														

Note: The specifications above may not be available in all regions.

Lenovo  
May 2020

# ThinkPad T14 Gen 1 (Intel)

