

ThinkPad T14 Gen 1 (Intel) 20S0002RUS

Product

ThinkPad T14 Gen 1 (Intel)

Region

NA

Country/Region

USA

Machine Type

20S0

TopSeller

TopSeller

Processor

Intel Core i7-10610U (4C / 8T, 1.1 / 4.7GHz, 12MB)

Graphics

Integrated Intel UHD Graphics

Chipset

Intel SoC Platform

Memory

8GB Soldered DDR4-2666

Storage

256GB SSD M.2 2280 PCIe NVMe Opal2

Display

14" FHD (1920x1080) IPS 250nits Anti-glare

Touchscreen

None

Media Reader

MicroSD Reader

Ethernet

100/1000M

Optical

None

WLAN + Bluetooth

Intel AX201 11ax, 2x2 + BT5.0

WWAN

None

SIM Card

None

Smart Card Reader

None

Monitor Cable

None

Case Material

PPS / 50% GF (Top) + PA / 50% GF (Bottom)

Bundled Accessories

None

Camera

720p with ThinkShutter

Microphone

2x, Array

Color

Black

Keyboard

Backlit, English

Fingerprint Reader

Touch Style, Match-on-Chip

NFC

None

TPM

Discrete TPM 2.0

Battery

Integrated 50Wh

Power Adapter

65W USB-C

System Management

Intel vPro

Operating System

Windows 10 Pro 64, English

Bundled Software

None

Base Warranty

3-year, Depot

Bundled Service

None

EAN / UPC / JAN

195042012866

End of Support

2026-06-05

Announce Date

2020-05-05

Recommended Services**Best**

3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + Sealed Battery) (5PS0N73216)

Better

3Y Lenovo Support (Premier Support + Keep Your Drive + Sealed Battery) (5PS0N73159)

Good

3Y Premier Support Upgrade from 3Y Depot/CCI (5WS0T36152)

Notes:

Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

ThinkPad T14 Gen 1 (Intel) Platform Specifications

Product Specifications Reference (PSREF)



Processor	10th Generation Intel® Core™ i5 / i7 Processor								Dimensions WxDxH: 12.95" x 8.94" x 0.70"; 329mm x 227mm x 17.9mm	Weight	Models					
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics			HD	FHD	FHD Touch	FHD Low Power	UHD	
Graphics	i5-10210U	4	8	1.6 GHz	4.2 GHz	6MB	DDR4-2666	Intel UHD Graphics	Black	Case material Display cover: PPS / 50% GF; Bottom: PA / 50% GF	Smart card reader Optional: Smart card reader					
	i5-10310U			1.6 GHz	4.4 GHz	6MB					Media reader MicroSD card reader					
	i7-10510U			1.8 GHz	4.9 GHz	8MB					Ports Two USB 3.1 Gen 1 (one Always On), one USB 3.1 Type-C Gen 1 (with the function of Power Delivery and DisplayPort), one USB 3.1 Type-C Gen 2 / Thunderbolt 3 (with the function of PD and DP), HDMI 1.4b, Ethernet (RJ-45), nano-SIM card slot (WWAN models), headphone / microphone combo jack, optional smart card reader, microSD card reader, side docking connector, security keyhole * Depending on many factors, actual data transfer speed may be lower than theoretical speed					
	i7-10610U			1.8 GHz	4.9 GHz	8MB					Monitor cable (optional) • Lenovo HDMI to VGA Monitor Adapter • Lenovo USB-C to VGA Adapter • Lenovo USB-C to DisplayPort Adapter					
	i7-10710U	6	12	1.1 GHz	4.7 GHz	12MB					Camera (optional) • HD720p camera with ThinkShutter camera privacy, fixed focus • IR camera and HD720p camera with ThinkShutter camera privacy, fixed focus					
	i7-10810U	1.1 GHz	4.9 GHz	12MB	Audio support HD Audio, Realtek® ALC3287 codec / Dolby® Audio speaker system, 2W x 2 / optional dual array far-field microphone, headphone / microphone combo jack											
Chipset	Intel SoC (System on Chip) platform								Keyboard	6-row, spill-resistant, multimedia Fn keys with Unified Communications controls, optional LED backlight						
Memory	40GB or 48GB max / 2666MHz DDR4, dual-channel capable, 8GB or 16GB memory soldered to systemboard, one DDR4 SO-DIMM socket * Installed memory is actually 3200MHz but run at 2666MHz due to Intel limitation									UltraNav™	TrackPoint® pointing device and buttonless Mylar surface multi-touch touchpad					
Display	Size	Resolution	Type	Surface	Touch	Brightness	Aspect Ratio	Contrast Ratio	Color Gamut		Viewing Angle	Security	Power-on password, hard disk password, supervisor password, security keyhole • Firmware TPM 2.0 integrated in chipset • Discrete TPM 2.0 TCG Certified			
	14.0"	HD (1366x768)	TN	Anti-glare	-	220 nits	16:9	400:1	45%	90°	Security chip		Intel vPro Technology			
	14.0"	FHD (1920x1080)	IPS	Anti-glare	-	250 nits	16:9	700:1	45%	170°		Fingerprint reader	Optional: Touch style match on chip fingerprint reader on the palm rest			
	14.0"	FHD (1920x1080)	IPS	Anti-glare	Multi-touch	300 nits	16:9	700:1	45%	170°	NFC (optional)		Near Field Communication			
	14.0"	FHD (1920x1080) Low Power	IPS	Anti-glare	-	400 nits	16:9	800:1	72%	170°		Battery	Integrated Li-Polymer 50Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter MobileMark® 2014: 16.5 hr MobileMark 2018: 10.5 hr * Battery life varies significantly with settings, usage, & other factors			
	14.0"	FHD (1920x1080) ThinkPad Privacy Guard	IPS	Anti-glare	Multi-touch	500 nits	16:9	1000:1	72%	178°	AC adapter		• 45W USB-C AC adapter • 65W USB-C AC adapter • 65W USB-C slim AC adapter			
	14.0"	UHD (3840x2160) HDR400, Dolby Vision™	IPS	Glossy	-	500 nits	16:9	1500:1	100%	178°		Operating system	Optional: Windows® 10 Home 64 or Windows 10 Pro 64			
Multi-touch (opt)	On-cell touch, supports 10-finger gesture								Limited warranty (optional)	• 1-year depot repair service • 1-year depot with 2-year system board repair service • 1-year limited onsite service • 1-year + 2-year depot repair service • 1-year + 2-year onsite repair service • 3-year/1-yr battery depot repair service • 3-year/1-yr battery limited onsite service						
Storage	<ul style="list-style-type: none"> • M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4 • M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 2 • Intel Optane™ Memory H10 with Solid State Storage, M.2 2280, PCIe NVMe 3.0 x 4 									Mil-Spec test	MIL-STD-810G military testing					
Optical	None								Environment		EPEAT™ Gold; ENERGY STAR® 8.0; RoHS-compliant					
Ethernet	Non-vPro model: Intel Ethernet Connection I219-V (Jacksonville) vPro model: Intel Ethernet Connection I219-LM (Jacksonville)															
WLAN + Bluetooth™	Intel Wi-Fi 6 AX201, Wi-Fi 2x2 802.11ax + Bluetooth 5.0 * Intel AX201 card supports BT5.1 but is limited to BT5.0 by Windows OS															
WWAN (optional)	<ul style="list-style-type: none"> • Wireless WAN upgradable • Integrated Mobile Broadband 4G LTE-A, Fibocom L850-GL, M.2 card • Integrated Mobile Broadband 4G LTE-A, Fibocom L860-GL, MIMO 2x2, M.2 card * For non-WWAN model, it means the model is NOT WWAN upgradable 															
SIM card (opt)	Gemalto eSIM Card															

Note: The specifications above may not be available in all regions.

Lenovo
May 2020

ThinkPad T14 Gen 1 (Intel)

