

ThinkVision T24i-20 61F7MAR1US

Product

ThinkVision T24i-20

Machine Type

61F7

Region

NA, LA

Display Size

23.8"

View Area

527.04x296.46 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

1920 X 1080

Pixel Pitch

0.2745x0.2745 mm

Dot / Pixel Per Inch

93 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (off mode)

Refresh Rate

60 Hz

Brightness

250 nits

Contrast Ratio

1000:1

Color Gamut

72% NTSC

Multiple Input

HDMI, DP, VGA

USB Port

4 x USB 3.2 Gen1 (1 x BC1.2)

Camera

None

Speaker

None

Power Consumption (Typical / Maximum)

14W / 55W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

559.3x539.8x205 mm

Weight (Including Stand)

13.01lb / 5.9kg

Monitor Cable

DP, USB Type-A to B

ENERGY STAR

Yes

TCO

TCO 8.0

EPEAT

Silver

Low Blue Light / Eye Comfort

Eye Comfort

Base Warranty

3-year

Operating System

Support Windows 7, Windows 10

Presets / User Settings

24/20

On Screen Display

OSD, 8 Languages

Sync Technology

None

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Announce Date

2020-04-24



WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



ThinkVision T24i-20

Lenovo

DISPLAY

Panel Size
23.8-inch

Screen Dimensions
527.04 mm x 296.46 mm

Panel Type
3-side NearEdgeless
In-Plane Switching

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920 x 1080

Pixel Pitch
0.2745 x 0.2745 mm

Dot/Pixel Per Inch (DPI/PPI)
93

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
4ms (extreme mode)

Refresh Rate
60 Hz

Brightness (typical)
250 cd/m²

Brightness (peak)
250 cd/m²

Contrast Ratio (typical)
1000:1

Dynamic Contrast Ratio (typical)
3M:1

Color Gamut
72% NTSC (CIE 1931)

Color Support (typical)
16.7 Million

Anti-glare
Yes

CONNECTIVITY

Video Signal
1 x HDMI 1.4
1 x DP 1.2
1 x VGA

Audio Signal
1 x Audio Out (3.5 mm)

USB Hub
Yes

USB Upstream
1 x USB 3.2 Gen1

USB Downstream
4 x USB 3.2 Gen1 (1 x BC 1.2)

MULTI-MEDIA

Optional Soundbar Support
Yes (PN OA36190)

POWER

Power Consumption (typ./max.)
14W / 55W

Power Consumption Sleep/Off Mode
< 0.5W

Power Consumption Switch-off Mode
< 0.3W

ENERGY STAR Power Consumption (P_{on}/E_{TEC})
12.35W / 38.83kWh

Power Supply
Internal

Voltage Required
AC 100 to 240 V (50-60 Hz)

MECHANICAL

Tilt Angle (front/back)
-5° / 35°

Swivel Angle (left/right)
+45° / -45°

Lift (max. range)
150 mm

Pivot
-90° / 90°

VESA Mount Capability
Yes (100 x 100 mm)

Kensington Lock Slot
Yes

Tiny Bracket Support
Yes (sold separately)

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (side)
2.0 mm

Bezel Width (top/bottom)
2.0 mm / 22.2 mm

DIMENSION

Size Packed (D x H x W, mm/inch)
422.0 x 187.0 x 622.0 mm
16.61 x 7.36 x 24.49 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)
205.0 x 409.3 x 539.8 mm
8.07 x 16.11 x 21.25 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position)
205.0 x 559.3 x 539.8 mm
8.07 x 22.02 x 21.25 inches

Size Unpacked w/o Stand (head only) (D x H x W, mm/inch)
46.8 x 326.5 x 539.8 mm
1.84 x 12.85 x 21.25 inches

Min. Distance from Table to Panel (lowest pixel at bottom of screen, mm)
106.62 mm

Max. Distance from Table to Panel (highest pixel at top of screen, mm)
557.0 mm

Weight Packed (kg/lbs.)
8.17 kg/18.01 lbs

Weight Unpacked (kg/lbs.)
5.90 kg/13.01 lbs.

Weight (monitor head only) (kg/lbs.)
3.30 kg/7.28 lbs.

Full Container Load (40' STD/20' STD)
1140/540 units

WHAT'S IN THE BOX

Monitor with stand
1 x Power cable (1.8 m)
1 x DP cable (1.8 m)
1 x USB Type-A to B cable (1.8 m)
Quick setup guide

CERTIFICATION

ENERGY STAR Rating
8.0

CCC
Yes

TCO
8.0

TCO Edge
2.0

EPEAT
Silver

RoHS (EU 2002/95/EC)
Yes

Windows Certification
Windows 7, Windows 10

China Energy Efficiency Standard
Tier 1

TÜV Rheinland Eye Comfort
Yes



Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2020 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

ThinkVision T24i-20

Lenovo

