

ThinkVision P32p-20 62A2GAR2US

Product

ThinkVision P32p-20

Machine Type

62A2

Region

NA, LA

Display Size

31.5"

View Area

697.31x392.23 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

3840x2160

Pixel Pitch

0.1816x0.1816 mm

Dot / Pixel Per Inch

140 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (off mode)

Refresh Rate

60 Hz

Brightness

350 nits

Contrast Ratio

1000:1

Color Gamut

99% sRGB, 99% BT.709, 90% DCI-P3

Multiple Input

USB Type-C, HDMI, DP

USB Port

3 x USB 3.2 Gen1 (1 x BC 1.2)

Camera

None

Speaker

None

Power Consumption (Typical / Maximum)

36W / 186W

Power Adapter

Integrated

Stand

Tilt, Swivel, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

604.4x714.6x235 mm

Weight (Including Stand)

22.51lb / 10.21kg

Monitor Cable

USB Type-C to Type-C, USB Type-A to Type-B, DP

ENERGY STAR

Yes

TCO

TCO 8.0

EPEAT

Gold

Low Blue Light / Eye Comfort / Eyesafe Display

Eye Comfort

Base Warranty

3-year

Operating System

Support Windows 7, Windows 10

Presets / User Settings

13 / 16

On Screen Display

OSD, 8 Languages

Sync Technology

None

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Announce Date

2020-6-30

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

ThinkVision P32p-20

DISPLAY

Panel Size
31.5-inch

Screen Dimensions
697.31 mm x 392.23 mm

Panel Type
3-side NearEdgeless
In-Plane Switching

Backlight
WLED

Aspect Ratio
16:9

Resolution
3840 x 2160

Pixel Pitch
0.1816 x 0.1816 mm

Dot/Pixel Per Inch (DPI/PPI)
140

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
4ms (extreme mode)
6ms (normal mode)

Refresh Rate
60 Hz

Brightness (typical)
350 cd/m²

Contrast Ratio (typical)
1000:1

Dynamic Contrast Ratio (typical)
3M:1

Color Gamut
99% sRGB
99% BT.709
90% DCI-P3

Color Support (typical)
1.07 Billion

Color Depth
10-bit

Processor LUT
14-bit

Anti-glare
Yes

CONNECTIVITY

Video Signal
1 x USB Type-C Gen1
(DP1.2 Alt Mode)
1 x HDMI 2.0
1 x DP 1.2

Audio Signal
1 x Audio Out (3.5 mm)

USB Hub
Yes

Ethernet
Yes (10M/100M/1000M)

USB Upstream
2 x USB 3.2 Gen1 (1 by USB
Type-C, 1 by USB Type-B)

USB Downstream
3 x USB 3.2 Gen1 (1 x BC1.2)

MULTI-MEDIA

Optional Soundbar Support
Yes (PN:0A36190)

SPECIAL FEATURES

Factory Calibration
Yes (Avg. Delta E<2)

KVM Switch
Yes

POWER

Power Consumption (typ./max.)
36W / 186W

Power Consumption Sleep/Off Mode
< 0.5W

Power Consumption Switch-off Mode
< 0.3W

ENERGY STAR Power Consumption (P_{on}/E_{TEC})
27W / 84kWh

Power Supply
Internal

USB Type-C Power Delivery (W)
up to 90 W

Voltage Required
AC 100 to 240 V (50-60 Hz)

MECHANICAL

Tilt Angle (front/back)
-5° / 35°

Swivel Angle (left/right)
+45° / -45°

Lift (max. range)
135 mm

Pivot
-90° / 90°

VESA Mount Capability
Yes (100 x 100 mm)

ThinkCentre M Series Tiny support
Yes, by Tiny/Nano monitor clamp II (PN: 4XH0Z42451) & Tiny VESA mount II (PN: 4XFON03161)*

ThinkCentre M Series Nano support
Yes, by Tiny/Nano monitor clamp II (PN: 4XH0Z42451) & Nano VESA mount (PN: 4XFOV81630)*

Kensington Lock Slot
Yes

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (side)
2.0 mm

Bezel Width (top/bottom)
2.0 / 24.1 mm

DIMENSION

Size Packed (D x H x W, mm/inch)
528 x 190 x 845 mm
20.79 x 7.48 x 32.27 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)
235.0 x 469.4 x 714.6 mm
9.25 x 18.48 x 28.13 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position)
235.0 x 604.4 x 714.6 mm
9.25 x 23.79 x 28.13 inches

Size Unpacked w/o Stand (head only) (D x H x W, mm/inch)
714.6 x 426.0 x 51.0 mm
28.13 x 16.77 x 2.01 inches

Weight Packed (kg/lbs.)
13.30 kg/29.32 lbs.

Weight Unpacked (kg/lbs.)
10.21 kg/22.51 lbs.

Weight (monitor head only) (kg/lbs.)
6.96 kg/15.34 lbs.

WHAT'S IN THE BOX

Monitor with stand
1 x Power cable (1.8 m)
1 x DP cable (1.8 m) (for US and Canada only)
1 x USB Type-C to Type-C cable (1.8 m)
1 x USB Type-A to Type-B cable (1.8 m)
Factory calibration report
Quick setup guide

CERTIFICATION

ENERGY STAR
Yes

CCC
Yes

TCO
8.0

TCO Edge
2.0

EPEAT
Gold

RoHS (EU 2002/95/EC)
Yes

Windows Certification
Windows 7, Windows 10

China Energy Efficiency Standard
Tier 1

TÜV Rheinland Eye Comfort
Yes



Lenovo

*Accessories sold separately

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2020 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

ThinkVision P32p-20

