

ThinkVision T23i-20 61F6MAR2US

Product

ThinkVision T23i-20

Machine Type

61F6

Region

NA, LA

Display Size

23"

View Area

509.19x286.42 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.2652x0.2652 mm

Dot / Pixel Per Inch

95.78 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (off mode)

Refresh Rate

60 Hz

Brightness

250 nits

Contrast Ratio

1000:1

Color Gamut

75% NTSC

Multiple Input

HDMI, DP, VGA

USB Port

4 x USB 3.2 Gen1 (1 x BC1.2)

Camera

None

Speaker

None

Power Consumption (Typical / Maximum)

14.5W / 52W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

554.34x521.8x200 mm

Weight (Including Stand)

12.32lb / 5.59kg

Monitor Cable

DP

ENERGY STAR

Yes

TCO

TCO 8.0

EPEAT

Silver

Low Blue Light / Eye Comfort

Eye Comfort

Base Warranty

3-year

Operating System

Support Windows 7, Windows 10

Presets / User Settings

20

On Screen Display

OSD, 8 Languages

Sync Technology

None

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Announce Date

2020-04-15

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

ThinkVision T23i-20

DISPLAY

Panel Size
23-inch

Screen Dimensions
509.19 mm × 286.42 mm

Panel Type
3-side NearEdgeless
In-Plane Switching

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920 x 1080

Pixel Pitch
0.2652 × 0.2652 mm

Dot/Pixel Per Inch (DPI/PPI)
95.78

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
4ms (extreme mode)
6ms (normal mode)

Refresh Rate
60 Hz

Brightness (typical)
250 cd/m²

Contrast Ratio (typical)
1000:1

Dynamic Contrast Ratio (typical)
3M:1

Color Gamut
75% NTSC (CIE 1931)

Color Support (typical)
16.7 Million

Anti-glare
Yes

CONNECTIVITY

Video Signal
1 x HDMI 1.4
1 x DP 1.2
1 x VGA

Audio Signal
1 x Audio Out (3.5 mm)

USB Hub
Yes

USB Upstream
1 x USB 3.2 Gen 1
Type-B

USB Downstream
4 x USB 3.2 Gen 1
(1 x BC1.2)

POWER

Power Consumption (typ./max.)
14.5W / 52W

Power Consumption Sleep/Off Mode
< 0.5 W

Power Consumption Switch-off Mode
< 0.3 W

Energystar Power Consumption (P_{on}/E_{TEC})
10.52W / 33.73kWh

Power Supply
Internal

Voltage Required
AC 100 to 240 V (47-63 Hz)

MECHANICAL

Tilt Angle (front/back)
-5° / 35°

Swivel Angle (left/right)
+45° / -45°

Lift (max. range)
150 mm

Pivot
-90° / 90°

VESA Mount Capability
Yes (100 x 100 mm)

Tiny Bracket Support
Yes (sold separately)

Nano Bracket Support
Yes (sold separately)

Kensington Lock Slot
Yes

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (side)
2.0 mm

Bezel Width (top/bottom)
2.0 / 22.0 mm

DIMENSION

Size Packed (D x H x W, mm/inch)
175 x 387 x 599 mm
6.89 x 15.24 x 23.58 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)
200 x 404.34 x 521.8 mm
7.87 x 15.92 x 20.54 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position)
200 x 554.34 x 521.8 mm
7.87 x 21.82 x 20.54 inches

Size Unpacked w/o Stand (head only) (D x H x W, mm/inch)
44.82 x 316.31 x 521.8 mm
1.76 x 12.45 x 20.54 inches

Min. Distance from Table to Panel (lowest pixel at bottom of screen, mm)
111.62 mm

Max. Distance from Table to Panel (highest pixel at bottom of screen, mm)
398.04 mm

Weight Packed (kg/lbs.)
7.5 kg / 16.53 lbs.

Weight Unpacked (kg/lbs.)
5.59 kg / 12.32 lbs.

Weight (monitor head only) (kg/lbs.)
3.32 kg / 7.32 lbs.

Full Container Load (40' STD / 20' STD)
1260 / 600 units

WHAT'S IN THE BOX

Monitor with stand
1 x Power cable (1.8 m)
1 x DP cable (1.8 m)
Quick setup guide

CERTIFICATION

ENERGY STAR Rating
8.0

CCC
Yes

TCO
8.0

TCO Edge
2.0

EPEAT
Silver

RoHS (EU 2002/95/EC)
Yes

Windows Certification
Windows 7, Windows 10

China Energy Efficiency Standard
Tier 1

TÜV Rheinland Eye Comfort
Yes



Lenovo

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2020 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

ThinkVision T23i-20

