


ASUS ZenBook 13/14

Timeless beauty, effortless portability



Timeless beauty, effortless portability

The beautiful new ZenBook 13 and 14 are more portable than ever. It's thinner, lighter, and incredibly compact, yet includes HDMI, Thunderbolt™ 3 USB-C®, USB Type-A and microSD card reader for unrivaled versatility. Built to deliver powerful performance, ZenBook 13 and 14 are your perfect choice for an effortless on-the-go lifestyle.



Powered by Intel® Core™ i7 Processor.

Learn more at: <https://www.asus.com/Laptops/ZenBook-Series-Home/>

starting at \$ xxxxxxxx

* Specification may vary by model.

Travel light, travel smart

The compact, thin and ultralight all-metal design of ZenBook 13 and 14 make it the ideal traveling companion. It's also the world's thinnest 13-inch and 14-inch laptops to feature a full set of I/O ports — including HDMI and USB Type-A — so you can enjoy versatile connectivity wherever you are.



No charger? No problem!

With ZenBook 13 and 14's amazing 22-hour battery life, traveling without a charger isn't a big deal. When you do need to top up, its fast-charge feature can restore the battery to a 60% charge level in just 40 minutes, so you'll be ready to go in no time.

Connect fast — anywhere

ZenBook 13 and 14 redefine what's possible in an ultrathin laptop to give you a full complement of I/O ports, including full-size HDMI and USB Type-A ports. The power of Thunderbolt™ 3 is also at your disposal, with two Thunderbolt™ 3 USB-C® ports that support fast charging, 4K UHD external displays and up to 40Gbps data transfers. For easy transfers of data from your mobile devices, there's also a microSD card reader.

Bright, clear, power-efficient display

ZenBook 13 and 14 have a bright and clear four-sided NanoEdge display, with slim bezels that create an 90% screen-to-body ratio for a more immersive viewing experience. The low-power 1-watt display delivers an incredible 450 nits of brightness, while maximizing battery life.



ASUS ZenBook 13/14 (UX325/UX425)

- Windows 10 Pro
- Up to Intel® Core™ i7-1065G7 processor
- Up to Intel® Iris™ Plus Graphics
- Up to LPDDR4x 32GB RAM (3200MHz)
- Ultra-fast up to 2TB PCIe 3.0 x4 SSD
- 13.3" or 14" FHD 1W, anti-glare screen
- 13.3" or 14" FHD, anti-glare screen
- IPS-level wide-view technology
- 4-sided NanoEdge display with up to 90% screen-to-body ratio
- Intel Wi-Fi 6 with Gig+ (802.11ax), Bluetooth® 5.0
- Interface : 2 x Thunderbolt™ 3 USB-C®, 1 x USB 3.2 Gen1 Type-A, 1 x HDMI 2.0, 1 x microSD card
- Certified by Harman/Kardon
- Exclusive colors: pine Grey, lilac mist
- Military-grade quality: MIL-STD 810G standard
- Incredible 22 hours of battery life with 67Whs battery
- Full-size backlit keyboard with 1.4mm key travel distance
- 13.3" 1.07kg, 1.39cm
- 14" 1.13kg, 1.39cm

| ASUS ZenBook 13/14 | UX325JA | UX425JA |
|------------------------------|---|--------------------------------|
| Operating System | Windows 10 Pro (ASUS recommends Windows 10 Pro for business) Windows 10 Home | |
| CPU | Intel® Core™ i7-1065G7 processor Intel® Core™ i5-1035G1 processor Intel® Core™ i3-1005G1 processor | |
| On Board Memory | 8GB / 16GB / 32GB LPDDR4x 3200MHz | |
| Memory Max. | LPDDR4 32GB | |
| Storage | 1TB / 2TB PCIe 3.0 x4 256GB / 512GB / 1TB PCIe 3.0 x2 Intel® Optane™ Memory H10 with Solid State Storage (32GB Optane™ + 512GB SSD / 32GB Optane™ + 1TB SSD) | |
| EMMC / ISSD | Support Intel Optane & Teton glacier (32GB / 512GB & 32GB / 1TB) | |
| Display | 13.3" or 14" FHD 1W, anti-glare screen 13.3" or 14" FHD, anti-glare screen IPS-level wide-view technology 4-sided NanoEdge display with up to 90% screen-to-body ratio | |
| Touch Panel | NA | |
| External Video Display Modes | HDMI | |
| Discrete GPU | NA | |
| Integrated GPU | Intel® Iris™ Plus Graphics / Intel® UHD Graphics | |
| Video Memory | NA | |
| Video Camera | 3D IR Camera | |
| Fingerprint Sensor | NA | |
| Wireless | Intel Wi-Fi 6 with Gig+ performance (802.11ax) + Bluetooth® 5.0 | |
| LAN | NA | |
| Card Reader | MicroSD card reader | |
| Interface | 2 x Thunderbolt™ 3 USB-C® 1 x USB 3.2 Gen1 Type-A 1 x HDMI 2.0 1 x MicroSD reader | |
| Audio | Certified by Harman/Kardon | |
| Weight (kg) | Approx. 1.07kg | Approx. 1.13kg |
| Dimension (cm) | 30.4(W) x 20.3(D) x 1.39(H) cm | 31.9(W) x 20.8(D) x 1.39(H) cm |
| AC Adapter | 65W AC Adapter Output : 20V DC, 65W; Input : 100~240V AC, 50/60Hz universal | |
| Battery | 67Wh 4-cell lithium-polymer battery | |
| Replaceable Battery | No | |
| Keyboard Type | Full-size backlit keyboard | |
| Warranty | 2 years | |
| Price | | |