



msi


ALL IN ONE PC
PRO 24X 10M
PRO 24X 10M-061US



SPECIFICATION


Manufacturer Part #	PRO24X10M061
OS	Windows 10 Home
CPU	Intel® Core™ i3-10110U Processor 2 Cores 2.1-4.1 GHz 4M Cache
Chipset	SoC
Motherboard	Proprietary
VGA	Intel® HD Graphics 620
Memory (GB)	4GB DDR4 2666MHz (1 x 4GB)
LAN	10/100/1000
Wireless Communication	Intel® Dual Band Wireless-AC 9462 1x1 802.11ac (433 Mbps)
Audio	2 x 2.5W Speakers
Video Port	1 HDMI-out
I/O	Side: 2x USB 3.1 Gen 1 Type A (1 with Super Charger) Rear: 2 x rear USB 3.1 Gen 1 Type A 2 x USB 2.0 1 x HDMI-out
USB	Side: 2x USB 3.1 Gen 1 Type A (1 with Super Charger) Rear: 2 x rear USB 3.1 Gen 1 Type A 2 x USB 2.0
HDD/SSD	256GB PCIe NVME SSD
Peripherals	USB Keyboard & Mouse
Power Supply	65W
Dimensions	21.2" x 6.69" x 15.75"
Weight	9.79 lbs
Warranty	1 Year

FEATURE



Silent PRO Cooling

Server Grade Thermal Module handles the cooling of different components within the system.



Dual LAN

The best way to back up your file/ secure data and prevent the hacker (with MSI exclusive BIOS).



HDD Rapid Upgrade

Easy maintenance and easy upgrade design with a switchable 2.5" storage inside.



Anti-Flicker Technology

With MSI Anti-Flicker technology, a stable output current for the monitor is provided to protect your eyes.



Anti-Glare Display

An anti-glare display makes viewing the display more pleasant and reduces eyestrain for users.



VESA Mountable

VESA mountable design makes the PC completely invisible on your desk.

CONNECTIONS



- | | |
|--------------------------------|-------------------------------|
| 1. 2x USB 3.2 Gen 1 Type-A | 6. 1xHDMI-out |
| 2. 1x Mic-in/ 1x Headphone-out | 7. 2x USB 3.2 Gen 1 Type A |
| 3. 1x DC-in | 8. 2x USB 2.0 Type A |
| 4. 1x Kensington Lock | 9. 1x switchable 2.5" Storage |
| 5. 2x RJ45 LAN | |