

# 8K HDMI Cable (M/M) - 8K 60 Hz, Dynamic HDR, 4:4:4, HDCP 2.2, Black, 3 ft.

# MODEL NUMBER: P568-003-8K6



8K HDMI cable connects your HDMI compatible source and display devices to transmit enhanced 8K video with Dynamic HDR.

## Features

**HDMI Cable Helps Your Gaming, Home Theater or Digital Signage Setup Get 8K-Ready**This HDMI cable (M/M) allows your compatible hardware to deliver up to 8K resolutions while securely connecting source and display devices compatible with HDMI audio/video signals. Backward compatible with all your existing HDMI devices, including Blu-ray players, game consoles and 4K televisions, the P568-003-8K6 is ideal for future-proofing your high-definition or UHD A/V application in anticipation of an 8K upgrade.

**Enjoy the Clarity of 4K/8K Video with Multi-Channel Audio, HDR and 4:4:4 Color**The P568-003-8K6 supports 8K video resolutions and 7.1-channel surround sound, including Dolby Atmos. It's compatible with 8K/60Hz video resolutions with Dynamic HDR (High Dynamic Range), which maintains premium contrast and color in each scene or even each frame. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This cable also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

Take Advantage of the Most Advanced HDMI Features for Premier Picture QualityThis 8K 60Hzready cable allows your compatible hardware to deliver up-to-date features, such as eARC (enhanced Audio Return Channel), which passes full-resolution surround sound signals to your speakers without compressing them. QMS (Quick Media Switching) switches from one frame rate to another without the delay of a blank screen between them. ALLM (Auto Low Latency Mode), VRR (Variable Refresh Rate) and QFT (Quick Frame Transport) reduce latency, refresh rate and lag for a more vivid gaming experience.

**Invest in Quality Construction for Reliable Performance**You're expecting this 8K cable to last a long time, which is why it has been constructed with high-quality materials, such as a rugged PVC jacket. Contacts and connectors are gold-plated to resist corrosion. Double shielding reduces line noise (EMI/RFI) that can disrupt signals traveling through the HDMI cord.

# **Specifications**

OVERVIEW

# Highlights

- Supports UHD resolutions up to 8K @ 60 Hz (4:4:4) for heightened video quality
- Supports Dynamic HDR for richer contrast and expanded color accuracy per frame
- Supports eARC for fullresolution object-based surround sound with no compression
- Plug-and-play operation with no software required for easy, immediate installation

## Applications

- Watch 8K video from a compatible Blu-ray player, game console, laptop or tablet on a compatible television, monitor or projector
- Connect a Windows laptop to a conference table's A/V box to give a video presentation on a large screen
- Play online or PC video games that display optimal graphics
- Send 8K video content to digital signs or point-of-sale displays

## **System Requirements**

Both source and display devices must be compatible with 8K standards to watch 8K video

## **Package Includes**

P568-003-8K6 HDMI Cable, 8K @ 60 Hz, M/M, Black, 3 ft. (0.9 m)



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

UPC Code	037332254795	
Product Type	Passive	
Technology	HDMI	
VIDEO		
Max Supported Video Resolution	7680 x 4320 @ 60Hz	
Max Supported Color Depth	48-bit Deep Color	
HDR Support	Yes	
3D Video Supported	Yes	
Chroma Sub Sampling	4:4:4	
EDID Support	Yes	
Signal Transmission	Bidirectional	
Bandwidth	48 Gbps	
AUDIO		
	eARC	
Audio Specification	earc	
USER INTERFACE, ALERTS & COI	NTROLS	
LED Indicators	0	
PHYSICAL		
Material of Construction	PVC	
Color	Black	
Cable Jacket Color	Black	
Connector Color	Black	
Cable Jacket Material	PVC	
Cable Jacket Rating	VW-1	
Cable Outer Diameter (OD)	7.3mm	
Wire Gauge (AWG)	28	
Cable Length (ft.)	3	
Cable Length (m)	0.91	
Cable Length (in.)	36	
Ferrite Core	No	
Minimum Bend Radius	36.5mm	
ENVIRONMENTAL		
Operating Temperature Range	14 to 122 F (-10 to 50 C)	



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Storage Temperature Range	5 to 140 F (-15 to 60 C)	
Operating Humidity Range	0% to 90% RH, Non-Condensing	
Storage Humidity Range	0% to 90% RH, Non-Condensing	
COMMUNICATIONS		
EDID Compatible	Yes	
Consumer Electronics Control (CEC) Supported	Yes	
CONNECTIONS		
Side A - Connector 1	HDMI (MALE)	
Side B - Connector 1	HDMI (MALE)	
Connector Plating	Gold	
Contact Plating	Gold	
Connector Style	Straight	
Latching or Gripping Connector	No	
FEATURES & SPECIFICATIONS		
HDCP Specification	1.4; 2.2	
Driver Required	No	
Fully Molded Connector Ends	No	
Ohms	No	
EMI/RFI Line Noise Protection	No	
Integral Strain Relief	No	
Impedance-Matched Twisted-Pair Construction	No	
DIN Mountable	No	
Integrated/Removable Cable	No	
MST Support	No	
Scaler Function	No	
IP67 Rated	No	
IP68 Rated	No	
Antibacterial	No	
Armored Cable	No	
Ethernet Support	Yes	
IP20 Rated	No	
STANDARDS & COMPLIANCE		



Certification & Compliance	CE (Europe); RoHS; REACH; IEC/EN 62040	
WARRANTY		
Product Warranty Period (Worldwide)	Lifetime limited warranty	

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies