


eDatasheet
HP P24v G4 Monitor (9TT78A6)



An everyday, affordable business monitor that's easy on you.

Tackle your daily to-do list and multi-task across multiple windows on the on the large-screen HP P24v G4 Monitor that adjusts to your comfort needs and delivers Full HD picture quality with clear 178° sightlines.



Crisp image clarity for all your content.

Get lifelike color, sharp details, and a great view of everything you do, wherever you sit or stand, on a 23.8" diagonal Full HD IPS monitor with 178° viewing angles.

Modern connectivity.

Conveniently and quickly connect to your devices and additional monitors through the HDMI and VGA ports, no dongles required.

Limitless views.

See more of your actual screen and less of its borders with the 3-sided micro-edge design that also makes dual-monitor[1] setups a virtually seamless dream with no bezel interruptions.

Featuring

Make conscientious buying choices.

Choose a monitor that's TCO and ENERGY STAR® certified to help meet your environmental buying requirements.

Personalize your comfort settings.

See your screen in a whole new light with HP Low Blue Light, which shifts the color spectrum for more comfortable viewing. Tilt the screen up to 5° forward or 20° back to find your best viewing position.

We have your back.

Rest assured that your IT investment has a long lifecycle and is supported with our three-year standard limited warranty. To extend your protection, select an optional HP Care Pack service. [2]

Specifications

Display size (diagonal)	23.8"
Panel technology	IPS
Aspect ratio	16:9 ^[1]
Native resolution	FHD (1920 x 1080) ^[1]
Resolutions supported	1024 x 768; 1280 x 1024; 1280 x 720; 1280 x 800; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 640 x 480; 720 x 400; 800 x 600
Pixel pitch	0.274 mm
Brightness	250 nits ^[1]
Contrast ratio	1000:1 static ^[1]
Response time (typical)	5ms GtG ^[1]
Minimum dimensions (W x D x H)	53.96 x 4.76 x 32.5 cm
Minimum dimensions (W x D x H)	21.24 x 1.87 x 12.8 in
Dimensions With Stand (W x D x H)	53.96 x 18.61 x 40.5 cm
Weight	3.46 kg
Weight	7.62 lb
Display features	Anti-glare; Low blue light mode
Display Input Type	1 VGA; 1 HDMI 1.4 (with HDCP support)
Onscreen controls	Exit; Information; Management; Power control; Input control; Menu control; Brightness+; Image; Color
Display scan frequency (horizontal)	30-80 KHz
Display scan frequency (vertical)	50-60 Hz
Power	Input voltage 100 to 240 VAC
Power consumption	26 W (maximum), 23.5 W (typical), 0.5 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% RH
Certifications and compliances	Australian-New Zealand MEPS; BIS; BSMI; CB; CCC; CE; CECP; CEL; C-Tick; cTUVus; EAC; ENERGY STAR®; E-standby; EUP Lot-5; EUP Lot-6; FCC; ISO 9241-307; KC/KCC; NOM NYCE; PSB; SEPA; TCO Certified; TUV Bauart; VCCI; Vietnam MEPS; WEEE; ISC; Low blue light; UkrSEPRO; South Africa MEPS; Ukraine Energy label; California Energy Commission (CEC); WW application; ICE; Mexico MEPS; TGM; Japan PC Green Label
Physical security	Security lock-ready ^[2]
UPC number	194850305900
What's in the box	Monitor; AC power cord; HDMI cable; Documentation; Warranty card; Product notice

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Each monitor sold separately.

[2] HP Care Packs sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit www.hp.com/go/cpc. HP Services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.

Technical Specifications Footnotes

[1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[2] Lock sold separately.

© Copyright 2020 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

ENERGY STAR is a registered trademark of the U.S. Environmental Protection Agency.

