

# ThinkPad T15 Gen 1 20S6004PUS

**Product**

ThinkPad T15 Gen 1

**Region**

NA

**Country/Region**

USA

**Machine Type**

20S6

**TopSeller**

TopSeller

**Processor**

Intel Core i5-10310U (4C / 8T, 1.7 / 4.4GHz, 6MB)

**Graphics**

Integrated Intel UHD Graphics

**Chipset**

Intel SoC Platform

**Memory**

8GB Soldered DDR4-2666

**Storage**

256GB SSD M.2 2280 PCIe NVMe Opal2

**Display**

15.6" FHD (1920x1080) WVA 250nits Anti-glare

**Touchscreen**

None

**Media Reader**

MicroSD Reader

**Ethernet**

100/1000M

**Optical**

None

**WLAN + Bluetooth**

Intel AX201 11ax, 2x2 + BT5.0

**WWAN**

WWAN Upgradable

**SIM Card**

None

**Smart Card Reader**

None

**Monitor Cable**

None

**Bundled Accessories**

None

**Case Material**

PPS / 50% GF (Top), PA / 50% GF (Bottom), Anti-microbial

**Camera**

720p with ThinkShutter

**Microphone**

2x, Array

**Color**

Black

**Keyboard**

Backlit, English

**Fingerprint Reader**

Touch Style, Match-on-Chip

**NFC**

None

**TPM**

Discrete TPM 2.0

**Battery**

Integrated 57Wh

**Power Adapter**

65W USB-C

**System Management**

Intel vPro

**Operating System**

Windows 10 Pro 64, English

**Bundled Software**

None

**Base Warranty**

3-year, Depot

**Bundled Service**

None

**EAN / UPC / JAN**

195235581902

**End of Support**

2026-12-05

**Announce Date**

2020-07-28

**Recommended Services****Best**

3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + Sealed Battery) (5PS0N73216)

**Better**

3Y Lenovo Support (Premier Support + Keep Your Drive + Sealed Battery) (5PS0N73159)

**Good**

3Y Premier Support Upgrade from 3Y Depot/CCI (5WS0T36152)

**Notes:**

**Battery life** is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

[WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

# ThinkPad T15 Gen 1 Platform Specifications

Product Specifications Reference (PSREF)



<p>Processor 10th Generation Intel® Core™ i5 / i7 Processor</p> <table border="1"> <thead> <tr> <th>Processor Number</th> <th># of Cores</th> <th># of Threads</th> <th>Base Frequency</th> <th>Max Turbo Frequency</th> <th>Cache</th> <th>Memory Types</th> <th>Processor Graphics</th> </tr> </thead> <tbody> <tr> <td>i5-10210U</td> <td rowspan="4">4</td> <td rowspan="4">8</td> <td>1.6 GHz</td> <td>4.2 GHz</td> <td>6MB</td> <td rowspan="4">DDR4-2666</td> <td rowspan="4">Intel UHD Graphics</td> </tr> <tr> <td>i5-10310U</td> <td>1.7 GHz</td> <td>4.4 GHz</td> <td>6MB</td> </tr> <tr> <td>i7-10510U</td> <td>1.8 GHz</td> <td>4.9 GHz</td> <td>8MB</td> </tr> <tr> <td>i7-10610U</td> <td>1.8 GHz</td> <td>4.9 GHz</td> <td>8MB</td> </tr> </tbody> </table>	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics	i5-10210U	4	8	1.6 GHz	4.2 GHz	6MB	DDR4-2666	Intel UHD Graphics	i5-10310U	1.7 GHz	4.4 GHz	6MB	i7-10510U	1.8 GHz	4.9 GHz	8MB	i7-10610U	1.8 GHz	4.9 GHz	8MB	<p>Dimensions <i>WxDxH:</i> 14.40" x 9.76" x 0.75"; 365.8mm x 248mm x 19.1mm</p> <p>Weight <i>FHD model:</i> 3.99 lb / 1.81 kg; <i>UHD model:</i> 3.84 lb / 1.74 kg</p> <p>Case color Black</p> <p>Case material <i>Display cover:</i> PPS / 50% GF <i>Keyboard cover:</i> PC / ABS / Talc15 + Magnesium alloy <i>Bottom:</i> PA / 50% GF with optional ISO 22196 compliant anti-microbial surface treatment (not including keyboard, display, and display bezel)</p>												
Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics																																		
i5-10210U	4	8	1.6 GHz	4.2 GHz	6MB	DDR4-2666	Intel UHD Graphics																																		
i5-10310U			1.7 GHz	4.4 GHz	6MB																																				
i7-10510U			1.8 GHz	4.9 GHz	8MB																																				
i7-10610U			1.8 GHz	4.9 GHz	8MB																																				
<p>Graphics Intel UHD Graphics in processor only or Intel UHD Graphics in processor and NVIDIA® GeForce® MX330, 2GB GDDR5 memory; supports up to 3 independent displays via native display and two external monitors; supports external monitors via HDMI (up to 4096x2160@24Hz), USB-C (up to 4096x2304@60Hz) or Thunderbolt (up to 4096x2304@60Hz)</p>	<p>Smart card reader <i>Optional:</i> Smart card reader</p> <p>Media reader MicroSD card reader</p> <p>Ports Two USB 3.2 Gen 1 (one Always On), one USB 3.2 Type-C Gen 1 (with the function of Power Delivery and DisplayPort), one USB 3.2 Type-C Gen 2 / Thunderbolt 3 (with the function of PD and DP), HDMI 1.4b, Ethernet (RJ-45), nano-SIM card slot (WWAN models), headphone / microphone combo jack, optional smart card reader, microSD card reader, side docking connector, security keyhole <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i></p>																																								
<p>Chipset Intel SoC (System on Chip) platform</p> <p>Memory 40GB or 48GB max / 2666MHz DDR4, dual-channel capable, 8GB or 16GB memory soldered to systemboard, one DDR4 SO-DIMM socket <i>* Installed memory is actually 3200MHz but run at 2666MHz due to Intel limitation</i></p>	<p>Monitor cable <i>(optional)</i></p> <ul style="list-style-type: none"> <li>• Lenovo HDMI to VGA Monitor Adapter</li> <li>• Lenovo USB-C to VGA Adapter</li> <li>• Lenovo USB-C to DisplayPort Adapter</li> </ul> <p>Bundled Accy None</p>																																								
<p>Display</p> <table border="1"> <thead> <tr> <th>Size</th> <th>Resolution</th> <th>Type</th> <th>Surface</th> <th>Touch</th> <th>Brightness</th> <th>Aspect Ratio</th> <th>Contrast Ratio</th> <th>Color Gamut</th> <th>Viewing Angle</th> </tr> </thead> <tbody> <tr> <td>15.6"</td> <td>FHD (1920x1080)</td> <td>WVA</td> <td>Anti-glare</td> <td>-</td> <td>250 nits</td> <td>16:9</td> <td>800:1</td> <td>45%</td> <td>170°</td> </tr> <tr> <td>15.6"</td> <td>FHD (1920x1080)</td> <td>WVA</td> <td>Anti-glare</td> <td>Multi-touch</td> <td>300 nits</td> <td>16:9</td> <td>800:1</td> <td>45%</td> <td>170°</td> </tr> <tr> <td>15.6"</td> <td>UHD (3840x2160) HDR400, Dolby Vision™</td> <td>WVA</td> <td>Anti-glare</td> <td>-</td> <td>500 nits</td> <td>16:9</td> <td>1400:1</td> <td>100%</td> <td>170°</td> </tr> </tbody> </table>	Size	Resolution	Type	Surface	Touch	Brightness	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	15.6"	FHD (1920x1080)	WVA	Anti-glare	-	250 nits	16:9	800:1	45%	170°	15.6"	FHD (1920x1080)	WVA	Anti-glare	Multi-touch	300 nits	16:9	800:1	45%	170°	15.6"	UHD (3840x2160) HDR400, Dolby Vision™	WVA	Anti-glare	-	500 nits	16:9	1400:1	100%	170°	<p>Camera <i>(optional)</i></p> <ul style="list-style-type: none"> <li>• HD720p camera with ThinkShutter camera privacy, fixed focus</li> <li>• IR camera and HD720p camera with ThinkShutter camera privacy, fixed focus</li> </ul> <p>Audio support HD Audio, Realtek® ALC3287 codec / Dolby® Audio speaker system, 2W x 2 / optional dual array far-field microphone, headphone / microphone combo jack</p>
Size	Resolution	Type	Surface	Touch	Brightness	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle																																
15.6"	FHD (1920x1080)	WVA	Anti-glare	-	250 nits	16:9	800:1	45%	170°																																
15.6"	FHD (1920x1080)	WVA	Anti-glare	Multi-touch	300 nits	16:9	800:1	45%	170°																																
15.6"	UHD (3840x2160) HDR400, Dolby Vision™	WVA	Anti-glare	-	500 nits	16:9	1400:1	100%	170°																																
<p>Multi-touch <i>(opt)</i> On-cell touch, supports 10-finger gesture</p>	<p>Keyboard 6-row, spill-resistant, multimedia Fn keys with Unified Communications controls, numeric keypad, optional LED backlight</p> <p>UltraNav™ TrackPoint® pointing device and buttonless Mylar surface multi-touch touchpad</p>																																								
<p>Storage</p> <ul style="list-style-type: none"> <li>• M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4</li> <li>• M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 2</li> <li>• Intel Optane™ Memory H10 with Solid State Storage, M.2 2280, PCIe NVMe 3.0 x 4</li> </ul>	<p>Security Power-on password, hard disk password, supervisor password, security keyhole</p> <p>Security chip</p> <ul style="list-style-type: none"> <li>• Firmware TPM 2.0 integrated in chipset</li> <li>• Discrete TPM 2.0 TCG Certified</li> </ul> <p>System Mgt <i>(opt)</i> Intel vPro Technology</p> <p>Fingerprint reader <i>Optional:</i> Touch style match on chip fingerprint reader on the palm rest</p> <p>NFC <i>(optional)</i> Near Field Communication</p>																																								
<p>Optical None</p>	<p>Battery Integrated Li-Polymer 57Wh battery, supports Rapid Charge (charge up to 80% in 1hr) with 65W AC adapter</p> <p>Max battery life <i>MobileMark® 2014:</i> 15.26 hr <i>MobileMark 2018:</i> 10.81 hr <i>* Battery life varies significantly with hardware configurations, settings, usage, &amp; other factors</i></p>																																								
<p>Ethernet <i>Non-vPro model:</i> Intel Ethernet Connection I219-V (Jacksonville) <i>vPro model:</i> Intel Ethernet Connection I219-LM (Jacksonville)</p>	<p>AC adapter</p> <ul style="list-style-type: none"> <li>• 45W USB-C AC adapter</li> <li>• 65W USB-C AC adapter</li> <li>• 65W USB-C slim AC adapter</li> </ul>																																								
<p>WLAN + Bluetooth™ Intel Wi-Fi 6 AX201, Wi-Fi 2x2 802.11ax + Bluetooth 5.0 <i>* Intel AX201 card supports BT5.1 but is limited to BT5.0 by Windows OS</i></p>	<p>Operating system <i>Optional:</i> Windows® 10 Home 64 or Windows 10 Pro 64</p>																																								
<p>WWAN <i>(optional)</i></p> <ul style="list-style-type: none"> <li>• Wireless WAN upgradable</li> <li>• Integrated Mobile Broadband 4G LTE-A, Fibocom L850-GL, M.2 card</li> <li>• Integrated Mobile Broadband 4G LTE-A, Fibocom L860-GL, MIMO 2x2, M.2 card</li> <li><i>* For non-WWAN model, it means the model is NOT WWAN upgradable</i></li> </ul>	<p>Limited warranty</p> <ul style="list-style-type: none"> <li>• 1-year depot repair service</li> <li>• 1-year depot with 2-year system board repair service</li> <li>• 1-year limited onsite service</li> <li>• 1-year + 2-year depot repair service</li> <li>• 1-year + 2-year limited onsite service</li> <li>• 3-year/1-yr battery depot repair service</li> <li>• 3-year/1-yr battery limited onsite service</li> </ul>																																								
<p>SIM card <i>(opt)</i> Gemalto eSIM</p>	<p>Mil-Spec test MIL-STD-810G military testing</p>																																								
	<p>Environment EPEAT™ Gold; ENERGY STAR® 8.0; TCO Certified; RoHS-compliant</p>																																								

Note: The specifications above may not be available in all regions and might change by regions.

Lenovo  
July 2020

# ThinkPad T15 Gen 1

