

# ThinkPad P15v Gen 1 20TQ001HUS

**Product**

ThinkPad P15v Gen 1

**Region**

NA

**Country/Region**

USA

**Machine Type**

20TQ

**TopSeller**

TopSeller

**Processor**

Intel Core i7-10850H (6C / 12T, 2.7 / 5.1GHz, 12MB)

**Graphics**

NVIDIA Quadro P620 4GB GDDR5

**Chipset**

Intel WM490

**Memory**

1x 32GB SO-DIMM DDR4-3200 Non-ECC

**Storage**

512GB SSD M.2 2280 PCIe NVMe Opal2

**Display**

15.6" FHD (1920x1080) IPS 250nits Anti-glare, 45% Gamut

**Touchscreen**

None

**Media Reader**

SD Reader

**Ethernet**

100/1000M

**Optical**

None

**WLAN + Bluetooth**

Intel AX201 11ax, 2x2 + BT5.1

**WWAN**

None

**SIM Card**

None

**Smart Card Reader**

None

**Monitor Cable**

None

**Case Material**

Display cover: PC / ABS Bottom: PC / ABS

**Bundled Accessories**

None

**Camera**

720p + IR with ThinkShutter

**Microphone**

2x, Array

**Color**

Black

**Keyboard**

Backlit, English

**Fingerprint Reader**

Touch Style, Match-on-Chip

**NFC**

None

**TPM**

Discrete TPM 2.0

**Battery**

Integrated 68Wh

**Power Adapter**

135W Slim Tip

**System Management**

Intel vPro

**Operating System**

Windows 10 Pro 64, English

**Bundled Software**

None

**Base Warranty**

3-year, Depot

**Bundled Service**

3Y Premier Support Upgrade from 3Y Depot/CCI (5WS0V07092)

**EAN / UPC / JAN**

195235022351

**End of Support**

2027-03-04

**Announce Date**

2020-08-04

**Notes:**

**Battery life** is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

[WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

# ThinkPad P15v Gen 1 Platform Specifications



Processor	Supports one 10th Xeon W, Core i7, or i5 processor as following:										
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics			
	Xeon W-10855M	6	12	2.8GHz	5.1GHz	12MB	DDR4-2933	Intel UHD Graphics			
	Core i7-10875H	8	16	2.3GHz	5.1GHz	16MB	DDR4-2933	Intel UHD Graphics			
	Core i7-10850H	6	12	2.7GHz	5.1GHz	12MB	DDR4-2933	Intel UHD Graphics			
	Core i7-10750H	6	12	2.6GHz	5.0GHz	12MB	DDR4-2933	Intel UHD Graphics			
Core i5-10300H	4	8	2.5GHz	4.5GHz	8MB	DDR4-2933	Intel UHD Graphics				
Chipset	Intel WM490 Chipset										
Memory Type	SO-DIMM, DDR4-3200 non-ECC or DDR4-2933 ECC. Operates at DDR4-2933. 8GB/16GB/32GB available for both ECC and non-ECC										
Memory Sockets	2 DIMM sockets										
Memory Protection	ECC on models with ECC DIMMs and Xeon processor										
Max Memory	64GB										
Graphics	Intel UHD Graphics in processor, also supports optional NVIDIA Quadro P620, 4GB GDDR5 memory										
Display	Size	Resolution	Type	Surface	Touch	Brightness	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	
	15.6"	FHD (1920x1080)	WVA	Anti-glare	-	250 nits	16:9	700:1	45% NTSC	170°	
	15.6"	FHD (1920x1080)	WVA	Anti-glare	multi-touch	300 nits	16:9	800:1	45% NTSC	170°	
	15.6"	UHD (3840x2160) Dolby Vision, HDR 400	WVA	Anti-glare	-	600 nits	16:9	1400:1	100% Adobe	178°	
Color Calibration	Factory Color Calibration on UHD panels										
Touchscreen	Touch enable on selected FHD models, supports 10-finger gesture										
Pen	None										
Storage	Up to two M.2 2280 SSD, PCIe NVMe, 256GB / 512GB / 1TB / 2TB each										
RAID	RAID 0 / 1 support										
Optical	None										
Ethernet	One onboard GbE port via integrated gigabit ethernet, Intel i219LM for vPro models or i219V for non-vPro models										
NFC	None										
WLAN + Bluetooth	Optional Intel Wi-Fi 6 AX201 on most models, Wi-Fi 2x2 802.11ax + Bluetooth 5.1. Bluetooth 5.1 requires the latest version of Windows 10 (version 2004 or above)										
WWAN	One of the following, configurable by model: • No WWAN card and non upgradable • Integrated Mobile Broadband Upgradable, No WWAN Card, WWAN Antenna Only • Integrated Mobile Broadband 4G LTE-A, Fibocom L850-GL, MIMO 2x2, M.2 card										
SIM card	Optional Nano-SIM card slot										
Dimensions	Width: 366.5 mm (14.43 in). Depth: 250 mm (9.84 in). Thickness: 24.2 mm (0.95 in)										
Weight	Starting at 2.07 kg (4.57 lb, UHD)										
Case color	Black										
Case material	Display cover: PC / ABS Bottom: PC / ABS										
Media reader	SD card reader										
Standard Ports	1x Thunderbolt (USB-C form, Thunderbolt 3, USB 3.2 Gen 2, PD, DP), 2x USB-A 3.2 Gen 1 (one Always-on), 1x HDMI 2.0, 1x headphone / microphone combo jack, 1x SD card reader, 1x security keyhole, 1x RJ-45										
Optional Ports	One optional smart card reader on left, one optional Nano-SIM card slot on rear										
Monitor support	Up to 3 displays with 2 external monitors plus system LCD screen. External monitors supported via Thunderbolt and HDMI. HDMI supports up to 4K@60Hz. Thunderbolt supports up to 5K@60Hz										
Monitor cable	Optional HDMI to VGA, USB-C to DP, or USB-C to VGA adapters										
Bundled Accy	None										
Camera	Supports one optional camera as following: • HD720p camera with ThinkShutter camera privacy, fixed focus • Hybrid IR camera with ThinkShutter camera privacy, fixed focus										
Audio chip	Realtek ALC3287 codec										
Speaker	Stereo speakers with Dolby Audio support										
Microphone	Optional dual array near-field microphone										
Keyboard	6-row, spill-resistant, numeric keypad, multimedia Fn keys with Unified Communications controls, optional LED backlight										
UltraNav	3-button TrackPoint pointing device and 2-button Mylar surface multi-touch touchpad										
Password	Power-on password, hard disk password, supervisor password										
Security chip	Discrete TPM 2.0, TCG Certified, may be disabled in some regions										
System mgmt	Optional Intel vPro Technology supported on vPro enable models										
Security locks	Security keyhole for optional Kensington lock										
Smart card reader	Optional										
Fingerprint reader	Touch style match on chip fingerprint reader on the palm rest										
Battery	Integrated Li-Polymer 68Wh battery. Supports Rapid Charge (charge up to 80% in 1hr) with 135W AC adapter										
Max battery life	MobileMark 2014: 10 hr. MobileMark 2018: 7.2 hr <i>* Battery life varies significantly with hardware configurations, settings, usage, &amp; other factors</i>										
Power Adapter	135W slim AC adapter										
Operating system	Supports one optional preloaded operating system as following: • Windows 10 Home 64 • Windows 10 Pro 64 • Windows 10 Pro 64 for Workstations • Ubuntu Linux LTS										
Base Warranty	Optional warranty plans as following: • 1-year depot repair service • 3-year depot repair service • 1-year + 2-year depot repair service • 1-year limited onsite service • 3-year limited onsite service • 1-year + 2-year limited onsite service • 1-year depot with 2-year system board repair service										
Mil-Spec test	MIL-STD-810G military testing										
Environment	EPEAT Gold. ENERGY STAR 8.0. RoHS-compliant										
ISV certifications	Please visit <a href="http://www.thinkworkstations.com/isv-certifications/">www.thinkworkstations.com/isv-certifications/</a>										

# ThinkPad P15v Gen 1

