

ThinkPad P1 Gen 3 20TH003KUS

Product

ThinkPad P1 Gen 3

Region

NA

Country/Region

USA

Machine Type

20TH

TopSeller

TopSeller

Processor

Intel Xeon W-10855M (6C / 12T, 2.8 / 5.1GHz, 12MB)

Graphics

NVIDIA Quadro T2000 Max-Q 4GB GDDR6

Chipset

Intel WM490

Memory

1x 32GB SO-DIMM DDR4-3200 Non-ECC

Storage

1TB SSD M.2 2280 PCIe NVMe Opal2

RAID Preset

No

Display

15.6" FHD (1920x1080) IPS 500nits Anti-glare, 72% Gamut, Dolby Vision, HDR

Touchscreen

None

Pen

None

Media Reader

SD Reader

Optical

None

Ethernet

100/1000M via Optional Adapter

WLAN + Bluetooth

Intel AX201 11ax, 2x2 + BT5.1

WWAN

None

SIM Card

None

Monitor Cable

None

Bundled Accessories

None

Case Material

Carbon Fiber (Black) + PC + PPS Hybrid

Camera

720p + IR with ThinkShutter

Color

Black

Microphone

2x, Array

Keyboard

Backlit, English

Fingerprint Reader

Touch Style, Match-on-Chip

Color Calibrator

Factory Color Calibration on UHD panels

NFC

None

TPM

Discrete TPM 2.0

Battery

Integrated 80Wh

Power Adapter

135W Slim Tip

System Management

Intel vPro

Operating System

Windows 10 Pro 64 for Workstations, English

Bundled Software

None

Base Warranty

3-year, Depot

Bundled Service

None

EAN / UPC / JAN

195235869383

End of Support

2027-02-21

Announce Date

2020-08-04

Recommended Services**Best**

3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection + Sealed Battery) (5PS0N73216)

Better

3Y Lenovo Support (Premier Support + Keep Your Drive + Sealed Battery) (5PS0N73159)

Good

3Y Premier Support Upgrade from 3Y Depot/CCI (5WS0V07092)

Notes:

Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences.

California Electronic Waste Recycling Fee

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to:

<https://www.calrecycle.ca.gov/Electronics/Consumer>

[WWW.LENOVO.COM](https://www.lenovo.com)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo™

ThinkPad P1 Gen 3 Platform Specifications



Processor	Supports one 10th Xeon W, Core i9, i7, or i5 processor as following:										
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics			
	Xeon W-10855M	6	12	2.8GHz	5.1GHz	12MB	DDR4-2933	Intel UHD Graphics			
	Core i9-10885H	8	16	2.4GHz	5.3GHz	16MB	DDR4-2933	Intel UHD Graphics			
	Core i7-10875H	8	16	2.3GHz	5.1GHz	16MB	DDR4-2933	Intel UHD Graphics			
	Core i7-10850H	6	12	2.7GHz	5.1GHz	12MB	DDR4-2933	Intel UHD Graphics			
Core i7-10750H	6	12	2.6GHz	5.0GHz	12MB	DDR4-2933	Intel UHD Graphics				
Chipset	Intel WM490 Chipset										
Memory Type	SO-DIMM. DDR4-3200 for non-ECC, DDR4-2933 for ECC. Both ECC and non-ECC memory operate at DDR4-2933. 8GB/16GB/32GB available for both ECC and non-ECC										
Memory Sockets	2 DIMM sockets										
Memory Protection	ECC on models with ECC DIMMs and Xeon processor										
Max Memory	64GB										
Graphics	Intel UHD Graphics in processor, also supports one of the following optional discrete graphics:										
	<ul style="list-style-type: none"> • NVIDIA Quadro T1000 with Max-Q Design, 4GB GDDR6 memory • NVIDIA Quadro T2000 with Max-Q Design, 4GB GDDR6 memory 										
Display	Size	Resolution	Type	Surface	Touch	Brightness	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	
	15.6"	FHD (1920x1080)	WVA	Anti-glare	-	300 nits	16:9	700:1	72% NTSC	170°	
	15.6"	FHD (1920x1080) Dolby Vision HDR	WVA	Anti-glare	-	500 nits	16:9	800:1	72% NTSC	170°	
	15.6"	UHD (3840x2160) Dolby Vision HDR	WVA	Anti-glare	-	600 nits	16:9	1400:1	100% Adobe	178°	
	15.6"	UHD (3840x2160) Dolby Vision, HDR 500 True Black	OLED	Anti-reflection / Anti-smudge	multi-touch	400 nits, 540 nits (peak)	16:9	100000:1	100% DCI-P3	170°	
Color Calibration	Factory Color Calibration on UHD panels										
Touchscreen	Touch enable on selected UHD OLED models, supports 10-finger gesture										
Pen	Optional Lenovo Pen Pro										
Storage	Up to two M.2 2280 SSD, PCIe NVMe, 256GB / 512GB / 1TB / 2TB each										
RAID	RAID 0 / 1 support										
Optical	None										
Ethernet	Optional Lenovo USB-C to Ethernet Adapter										
NFC	None										
WLAN + Bluetooth	Intel Wi-Fi 6 AX201 on most models, Wi-Fi 2x2 802.11ax + Bluetooth 5.1. Bluetooth 5.1 requires the latest version of Windows 10 (version 2004 or above)										
WWAN	One of the following, configurable by model: <ul style="list-style-type: none"> • No WWAN card and non upgradable • Integrated Mobile Broadband 4G LTE-A, Fibocom L860-GL, MIMO 2x2, M.2 card 										
SIM card	Optional Nano-SIM card slot										
Dimensions	Width: 361.8 mm (14.24 in). Depth: 245.7 mm (9.67 in).										
	Thickness for non-touch models: 18.4 mm (0.72 in) Thickness for touch models: 18.7 mm (0.74 in)										
Weight	Starting at 1.7 kg (3.75 lb, FHD non-touch) / 1.8 kg (3.97 lb, OLED touch)										
Case color	Woven Carbon Fiber Finish (standard on OLED models, optional on UHD WVA models) or black										
Case material	<i>Display cover:</i> Carbon Fiber (Black or woven pattern) + PC + PPS Hybrid <i>Bottom:</i> Aluminum + PC / ABS										
Media reader	SD card reader										
Standard Ports	2x Thunderbolt (USB-C form, Thunderbolt 3, USB 3.2 Gen 2, PD, DP), 2x USB-A 3.2 Gen 1 (one Always-on), 1x HDMI 2.0, 1x headphone / microphone combo jack, 1x SD card reader, 1x security keyhole										
Optional Ports	One optional Nano-SIM card slot on right										
Monitor support	Up to 4 displays with 3 external monitors plus system LCD screen. External monitors supported via 2x Thunderbolt and 1x HDMI. HDMI supports up to 4K@60Hz. Two Thunderbolt support up to 5K@60Hz each										
Monitor cable	Optional HDMI to VGA, USB-C to DP, or USB-C to VGA adapters										
Bundled Accy	None										
Camera	Supports one optional camera as following: <ul style="list-style-type: none"> • HD720p camera with ThinkShutter camera privacy, fixed focus • Hybrid IR camera with ThinkShutter camera privacy, fixed focus 										
Audio chip	Realtek ALC3286 codec										
Speaker	Stereo speakers, Dolby ATMOS Speaker System										
Microphone	Optional dual far-field microphone										
Keyboard	6-row, spill-resistant, LED backlight, multimedia Fn keys with Unified Communications controls.										
UltraNav	3-button TrackPoint pointing device and 2-button glass surface multi-touch touchpad										
Password	Power-on password, hard disk password, supervisor password										
Security chip	Discrete TPM 2.0, TCG Certified, may be disabled in some regions										
System mgmt	Optional Intel vPro Technology supported on vPro enable models										
Security locks	Security keyhole for optional Kensington lock										
Smart card reader	None										
Fingerprint reader	Touch style match on chip fingerprint reader on the palm rest										
Battery	Integrated Li-Polymer 80Wh battery. Supports Rapid Charge (charge up to 80% in 1hr) with 135W AC adapter										
Max battery life	MobileMark 2014: 15.9 hr. MobileMark 2018: 12 hr <i>* Battery life varies significantly with hardware configurations, settings, usage, & other factors</i>										
Power Adapter	One of the following: <ul style="list-style-type: none"> • 135W slim AC adapter • 170W slim AC adapter 										
Operating system	Supports one optional preloaded operating system as following: <ul style="list-style-type: none"> • Windows 10 Home 64 • Windows 10 Pro 64 • Windows 10 Pro 64 for Workstations • Windows 10 Government Edition 64 • Ubuntu Linux LTS (available later) • Fedora Linux (available later) 										
Base Warranty	Optional warranty plans as following: <ul style="list-style-type: none"> • Non-warranty (special bids only) • 1-year depot repair service • 3-year depot repair service • 1-year + 2-year depot repair service • 1-year limited onsite service • 3-year limited onsite service • 1-year + 2-year limited onsite service • 1-year depot with 2-year system board repair service 										
Mil-Spec test	MIL-STD-810G military testing										
Environment	EPEAT Gold. ENERGY STAR 8.0. RoHS-compliant										
ISV certifications	Please visit www.thinkworkstations.com/isv-certifications/										

ThinkPad P1 Gen 3

