

Lenovo V15 ADA 82C700BNUS

Product

Lenovo V15 ADA

Region

NA

Country/Region

USA

Machine Type

82C7

TopSeller

No

Processor

AMD Athlon Gold 3150U (2C / 4T, 2.4 / 3.3GHz, 1MB L2 / 4MB L3)

Graphics

Integrated AMD Radeon Graphics

Chipset

AMD SoC Platform

Memory

4GB Soldered DDR4-2400

Storage

500GB HDD 5400rpm 2.5"

Display

15.6" HD (1366x768) TN 220nits Anti-glare

Touchscreen

None

Optical

None

Media Reader

4-in-1 Card Reader

Ethernet

None

WLAN + Bluetooth

11ac, 2x2 + BT5.0

Case Material

PC / ABS

Camera

0.3MP

Microphone

Mono

Color

Iron Grey

Surface Treatment

Texture

Keyboard

Non-backlit, English

Fingerprint Reader

None

TPM

FW TPM 2.0

Battery

Integrated 30Wh

Power Adapter

65W Round Tip

Operating System

Windows 10 Home 64, English

Bundled Software

Office Trial

Base Warranty

1-year, Depot

Bundled Service

None

EAN / UPC / JAN

195235476246

End of Support

N/A

Announce Date

2020-06-16

Recommended Services**Best**

3Y Premium Care with Onsite upgrade from 1Y Depot/CCI (5WS0U55751)

Better

3Y Onsite upgrade from 1Y Depot/CCI delivery (5WS0Q81865)

Good

3Y Depot/CCI upgrade from 1Y Depot/CCI delivery (5WS0Q81869)

Notes:**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



Lenovo V15 ADA Platform Specifications

Product Specifications Reference (PSREF)

Processor	AMD Athlon™ series processor or AMD Ryzen™ 3 / 5 series processor							Dimensions	WxDxH: 14.26" x 9.9" x 0.78"; 362.2mm x 251.5mm x 19.9mm	
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Type	Processor Graphics	Weight	Starting at 4.08 lb / 1.85 kg
	3020e	2	2	1.2 GHz	2.6GHz	1MB L2 / 4MB L3	DDR4-2400	AMD Radeon™ Graphics	Case color	Iron grey, IMR or Texture
	Athlon Silver 3050U			2.3 GHz	3.2 GHz				Case material	PC/ABS plastic
	Athlon Gold 3150U			2.4 GHz	3.3 GHz				Media reader	4-in-1 reader (MMC, SD, SDHC, SDXC)
	Ryzen 3 3250U	4	4	2.6 GHz	3.5 GHz	2MB L2 / 4MB L3	AMD Radeon Vega 8 Graphics	Ports	One USB 2.0, two USB 3.1 Gen 1, HDMI 1.4b, 4-in-1 reader (MMC, SD, SDHC, SDXC), combo audio / microphone jack * Depending on many factors, actual data transfer speed may be lower than theoretical speed.	
	Ryzen 5 3500U			2.1 GHz	3.7 GHz			Camera	0.3MP, fixed focus, with monaural microphone	
Graphics	AMD Radeon Graphics or AMD Radeon Vega 8 Graphics in processor; supports external digital monitor via HDMI; supports two independent displays; Max resolution: 3840x2160@30Hz (HDMI)							Audio support	HD Audio, Dolby Audio™, stereo speakers, 1.5W x 2, monaural microphone, combo audio / microphone jack	
Chipset	AMD SoC (System on Chip) platform							Keyboard	6-row, spill-resistant, multimedia Fn keys, numeric keypad	
Memory	A4-3020E model: 8GB max / 2400MHz DDR4, one DDR4 SO-DIMM socket Other model: 12GB max / 2400MHz DDR4, 4GB memory soldered to systemboard, one DDR4 SO-DIMM socket							Touchpad	Buttonless Mylar surface multi-touch touchpad	
Display	One of the following, configurable by model: • 15.6" (396mm) HD (1366x768), anti-glare, LED backlight, 220 nits, 16:9 aspect ratio • 15.6" (396mm) FHD (1920x1080), anti-glare, LED backlight, 220 nits, 16:9 aspect ratio							Security	Power-on password, hard disk password, supervisor password	
Multi-touch	None							Security chip	Firmware TPM 2.0 integrated in chipset	
Storage	Up to 2 drives (one HDD and one M.2 SSD): • HDD / SATA 6.0Gb/s, 2.5" wide, 7mm high • M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 2 • M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4							Fingerprint reader	None	
Optical	None							Battery	Integrated Li-ion 30Wh or 35Wh battery	
Ethernet	None							Max battery life	MobileMark® 2014: 5 hr (30Wh) or 6 hr (35Wh) * Battery life varies significantly with hardware configurations, settings, usage, & other factors.	
WLAN	802.11ac 2x2 Wi-Fi + Bluetooth 5.0, M.2 Card							AC adapter	65W round tip AC adapter	
Bluetooth™	Bluetooth 5.0 wireless, integrated in Wi-Fi + Bluetooth combo adapter							Preload (opt)	Preloaded operating system • Windows 10® Home 64 • Windows 10 Pro 64 Preloaded applications (only some listed) • Microsoft Office 365 Home • Microsoft Office 365 Personal • Microsoft Office Trial (with 30-day license) • Microsoft Office Home and Student 2019 • Microsoft Office Home and Business 2019 • Microsoft Office Professional 2019	
Note: The specifications above may not be available in all regions.								Limited warranty	One of the following, configurable by model: • 1-year depot repair service • 2-year/1-yr battery depot repair service	
								Environment	ErP lot3; RoHS-compliant	

Lenovo™

Lenovo V15 ADA

