



SPECIFICATIONS

Panel Size	29.5"
Panel Resolution	2560 x 1080 (WFHD)
Refresh Rate	200Hz
Response time	1ms(MPRT)
DYNAMIC REFRESH RATE TECHNOLOGY	FreeSync Premium
Panel Type	VA
Brightness (nits)	300
Viewing Angle	178°(H) / 178°(V)
Aspect Ratio	21:9
Curvature	1500R
Contrast Ratio	3000:1
DCR	1000000:1
Active Display Area (mm)	690.432 (H) x 291.276 (V)
Pixel Pitch (H x V)	0.2697 (H) x 0.2697 (V)
Surface Treatment	Anti-glare
Display Colors	1.07B[8bit+FRC]
DCI-P3 / sRGB	82% / 103%
Video ports	1x Display Port (1.2) 2x HDMI (2.0) 1x Type C (DP alt.)
USB ports	2x USB 3.2 Gen1 Type A 1x USB 3.2 Gen1 Type B
Audio ports	1 x Earphone out
Kensington Lock	Yes
VESA Mounting	75 x 75 mm
Power Type	External Adaptor 19V 4.74A
Power Input	19V 4.74A
Power consumption	90W
Signal Frequency	66 to 250.7KHz (H) 48 to 200Hz(V)
Adjustment (Tilt)	-5° ~ 20°
Adjustment (Swivel)	-30° ~ 30°
Adjustment (Pivot)	-90° ~ 90°
Adjustment (Height)	0 - 110mm
Dimension (W x H x D)	703 x 287 x 512 mm / 27.68 x 11.3 x 20.16 inch
Carton Dimension (W X H X D)	785 x 197 x 452 mm / 30.91 x 7.76 x 17.8 inch

FEATURES



Weight (NW / GW)	5.8 kg / 8.21 kg 12.79 lbs/ 18.1 lbs
Frameless Design	Yes
Note	Display Port: 2560 x 1080(Up to 200Hz) Type C: 2560 x 1080(Up to 200Hz) HDMI: 2560 x 1080 (Up to 180Hz) DCI-P3 and sRGB follow CIE1976 Standard

CONNECTIONS



1. 1x HDMI 1.4
2. 1x HDMI 2.0
3. 1x Display Port 1.2a
4. 1x DC Jack
5. 1x Earphone out
- 6.