Samsung **Hospitality Displays** HT670U Series (NA)

Highlights

- Elevate content to UHD resolution through upscaling technology
- Improve picture clarity and detail with HDR10+ refinement
- Quickly create and share personalized and promotional messaging
- Allow guests to manage in-room settings within an intuitive home menu
- Gauge and address maintenance needs in anticipation of guest requests
- Build compatible web applications within the powerful TIZEN OS



crystal Display Crisp and vivid color expression

Crystal Display ensures optimized color expression so guests can experience every subtle detail, immersing themselves in any content with a wider range of colors.



UHD-quality content delivery




Samsung's hospitality displays offer hotel guests the vivid picture quality of home entertainment systems. Through UHD upscaling technology, these refined displays showcase all content at UHD resolution (3,840 x 2,160), with four times the pixels of the FHD standard.

Refined picture quality



Beyond consistent UHD quality, Samsung's displays bring the power of High Dynamic Range (HDR10+) picture refinement to any hotel room. Using dynamic metadata that fine-tunes each frame within a given program, HDR10+ technology delivers an optimal, detail-rich and memorable viewing experience.

A tailored home menu



Each Samsung hospitality display includes an intuitive, customizable home menu that streamlines content exchange between hotels and quests. Content managers can easily incorporate images, logos and feature icons specific to guest needs while reinforcing special offers and hotel brandinwg.

Powerful performance, enhanced security



Backed by the powerful TIZEN operating system, Samsung hospitality displays ensure secure content delivery across the application, platform and system layers.

Centralized, real-time management



Compatible with existing LAN, Wi-Fi and coaxial infrastructures, Samsung's LYNK REACH 4.0 content platform centralizes and streamlines overall hotel maintenance. Hotel managers now can remedy issues across single displays or display groups before they escalate.

End-to-end personalized service



Hotels additionally can use LYNK REACH 4.0 to deliver customized quest messaging. Upon arrival, quests can receive a personalized greeting along with information about promotions or on-site amenities relevant to their stay. LYNK REACH 4.0 also provides express check-out for added convenience.

Additional features








Specifications


	Model	HG43NT670UFXZA	HG50NT670UFXZA	HG55NT670UFXZA	HG65NT670UFXZA
	Backlight	LED	LED	LED	LED
Display	Screen Size	43	50	55	65
	Resolution	3,840 x 2,160	3,840 x 2,160	3,840 x 2,160	3,840 x 2,160
	Picture Engine	UHD Mastering Engine	UHD Mastering Engine	UHD Mastering Engine	UHD Mastering Engine
	Auto Motion Plus	Yes	Yes	Yes	Yes
	Film Mode	Yes	Yes	Yes	Yes
	Natural Mode Support	Yes	Yes	Yes	Yes
	Motion Rate	120	120	120	120
	PQI (Picture Quality Index)	1300	1300	1300	1300
Video	HDR(High Dynamic Range)	HDR	HDR	HDR	HDR
	HDR10+	Yes	Yes	Yes	Yes
	HLG (Hybrid Log Gamma)	Yes	Yes	Yes	Yes
	Contrast	Mega Contrast	Mega Contrast	Mega Contrast	Mega Contrast
	Color	PurColor	PurColor	PurColor	PurColor
	Viewing Angle (H/V)	178/178	178/178	178/178	178/178
	Contrast Enhancer	Yes	Yes	Yes	Yes
	Dolby Digital Plus	Yes	Yes	Yes	Yes
Audio	WSound Output (RMS)	20W	20W	20W	20W
	Speaker Type	2CH	2CH	2CH	2CH
	VESA Mount	200 x 200 mm	200 x 200 mm	200 x 200 mm	400 x 300 mm
VESA	VESA Screw Size	M8	M8	M8	M8
	VESA Screw Depth	20-22	20-22	20-22	20-22
	Accessibility	US English	US English	US English	US English
	Digital Clean View	Yes	Yes	Yes	Yes
	Auto Channel Search	Yes	Yes	Yes	Yes
	Auto Power Off	Yes	Yes	Yes	Yes
General Feature	Caption (Subtitle)	Yes	Yes	Yes	Yes
	Caption (Subtitle) Connect Share™ (HDD)	Yes	Yes	Yes	Yes
	Connect Share™ (HDD) ConnectShare™ (USB 2.0)	Yes Yes	Yes Yes	Yes	Yes Yes
	EPG Camp Mode	Yes	Yes	Yes	Yes
	Game Mode	Yes	Yes	Yes	Yes
	OSD Language	English, Spanish, F Serbian	rench, Estonian, Finnish, German, Greek, Hungariar n, Slovak, Swedish, Bulgarian, Croatian, Czech, Danis	ı, ıtatıan, Latvian, Lithuanian, Norwegian, Polish, Po sh, Dutch, Slovenian. Albanian . Macedonian . Rosni:	ortuguese, komanian, an, Korean
	USB HID Support	Yes	Yes	Yes	Yes
	V-Chip	Yes	Yes	Yes	Yes
	Digital Broadcasting	ATSC/ClearQAM	ATSC/ClearQAM	ATSC/ClearQAM	ATSC/ClearQAM
System	Analog Tuner	Yes	Yes Yes	Yes	Yes
	Anatog Tuner Samsung LYNK™ REACH (RF)	REACH 4.0	REACH 4.0	REACH 4.0	REACH 4.0
	Hospitality Home Menu	Home Menu 2017	Home Menu 2017	Home Menu 2017	Home Menu 2017
	Hospitality Home Menu Hospitality Plug&Play (Easy Set-up)	Yes	Yes	Yes	Home Menu 2017 Yes
	Auto Source Mode	Yes	Yes	Yes	Yes
	Auto Source Mode Power On Mode	yes Yes	Yes Yes	Yes	Yes
	Hotel Channel List	Yes	Yes	Yes	Yes
	Channel Menu Display	Yes	Yes	Yes	Yes
	Mixed Channel List (ATSC, DVB-T/T2/C/S2, Analog)	Yes	Yes	Yes	Yes
	My Channel	Yes	Yes	Yes	Yes
	Energy Saving Mode (BLU Control)	Yes	Yes	Yes	Yes
	Logo Display with Time Out Setting (BMP/Movie)	Yes	Yes	Yes	Yes
	Welcome Message	Yes	Yes	Yes	Yes
	-				
	RJ12/IR Pass Through	Yes	Yes	Yes	Yes
	External Clock Compatibility	No 	No 	No 	No
	Clock Back Up Supply	Yes	Yes	Yes	Yes
	External Clock Dimming Control	No	No	No	No
	Multi Code Remote Control	Yes	Yes	Yes	Yes
	Screwed Remote Battery Cover	Yes	Yes	Yes	Yes
	Soundbar Compatibility	Yes	Yes	Yes	Yes
	Music Mode (Input: PC/AV/Component/HDMI)	Yes	Yes	Yes	Yes
	TTX Clock Update (Analogue)	No	No	No	No
	USB Cloning	Yes	Yes	Yes	Yes
	Smoovie Compatibility	Yes	Yes	Yes	Yes
	On/Off Timer (Schedule)	Yes	Yes	Yes	Yes
	Wake-up Timer (Alarm)	Yes	Yes	Yes	Yes
	Samsung LYNK™ DRM	Yes	Yes	Yes	Yes
	blan	No	No	No No	No
	Security Mode	Yes	Yes	Yes	Yes
	S/W EPG (Solution EPG)	Yes	Yes	Yes	Yes
	IP Over Coax	No Yes	No No	No No	No No
	HDMI (Side/Rear)	No 3/0	No 3/0	No 3/0	3/0
Input & Output		3/0 2	3/0		3/0
	USB (Side/Rear)			2	
	RF In (Terrestrial / Cable input) (Side/Rear)	1/1(Common Use for Terrestrial)/0	1/1(Common Use for Terrestrial)/0	1/1(Common Use for Terrestrial)/0	1/1(Common Use for Terrestrial)/
	Ex-Link (RS-232C)	1	1	1	1
	HDMI A / Return Ch. Support	Yes	Yes	Yes	Yes
	Anynet+ (HDMI-CEC)	Yes	Yes	Yes	Yes
	Pillow Speaker Jack (Side/Rear)	No	No	No	No
	RJ12 (Side/Rear)	0/1	0/1	0/1	0/1
	RJP (Remote Jackpack) (Side/Rear)	0/1	0/1	0/1	0/1
	Door-Eye Control (Side/Rear)	No	No	No	No
	Door-Eye Video In (Side/Rear)	No	No	No	No
	PC In (D-sub) (Side./Rear)	No	No	No	No
	PC/DVI Audio In (Mini Jack) (Side./Rear)	No	No	No	No
	Front Color	BLACK	BLACK	BLACK	BLACK
Design Eco Power	Stand Type	SQUARE	SQUARE	SQUARE	SLIM FEET
	Bezel Type	3 Bezel-less	3 Bezel-less	3 Bezel-less	3 Bezel-less
	ENERGY STAR (Latest effective version)	Yes	Yes	Yes	Yes
	Eco Sensor	Yes	Yes	Yes	Yes
	Power Supply (V)	AC110-120V 50/60Hz	AC110-120V 50/60Hz	AC110-120V 50/60Hz	AC110-120V 50/60Hz
		105 W	135 W	135 W	ACTIO-120V 50/60HZ 190 W
	Power Consumption (Max)				
	Power Consumption (Stand-by)	0.5 W	0.5 W	0.5 W	0.5 W
	Power Consumption (Typical)	51 W	61 W	62 W	80 W
Dimension	Set Dimension without Stand (WxHxD)	963.9 x 558.9 x 59.6 mm	1116.8 x 644.2 x 59.9 mm	1230.5 x 707.2 x 59.9 mm	1449.4 x 830.3 x 59.9 mm
	Set Dimension with Stand (WxHxD)	963.9 x 610.9 x 226.5 mm	1116.8 x 696.8 x 226.5 mm	1230.5 x 759.8 x 226.5 mm	1449.4 x 906.6 x 282.1 mm
	Package Dimension (WxHxD)	1183 x 670 x 143 mm	1357 x 780 x 152 mm	1467 x 843 x 158 mm	1606 x 963 x 184 mm
	Set Weight without Stand	8.6 kg	11.9 kg	14.3 kg	21.1 kg
Weight	Set Weight with Stand	11.8 kg	15.1 kg	17.5 kg	21.4 kg
,	Package Weight	15.0 kg	19.3 kg	22.8 kg	29.5 kg
	Remote Controller Model	TM1240A	TM1240A	TM1240A	77.5 kg
	Batteries (for Remote Control)	Yes	Yes	Yes	Yes
	Mini Wall Mount Supported	Yes	Yes	Yes	Yes
	Vesa Wall Mount Supported	Yes	Yes	Yes	Yes
		Yes	Yes	Yes	Yes
	Power Cable Power Cable			Yes	Yes
Accessory	Power Cable Quick Install Guide	Yes	Yes	162	103
Accessory		Yes Yes	Yes Yes	Yes	Yes
Accessory	Quick Install Guide				
Accessory	Quick Install Guide Data Cable	Yes	Yes	Yes	Yes
Accessory	Quick Install Guide Data Cable Stand Mount Kit	Yes Yes	Yes Yes	Yes Yes	Yes Yes

Specifications

43"



Specifications



Connectors

- 1. EX-LINK
- 2. USB (5V 0.5A)
- 3. USB (HDD 5V 1A)
- 4. DIGITAL AUDIO OUT (OPTICAL)
- 5. HDMI IN 3 (ARC)
- 6. HDMI IN 2
- 7. HDMI IN 1
- 8. ANT IN
- 9. DATA

About Samsung Electronics Co., Ltd.

Samsung Electronics Co., Ltd. inspires the world and shapes the future with transformative ideas and technologies. The company is redefining the worlds of TVs, smartphones, wearable devices, tablets, cameras, digital appliances, medical equipment, network systems, and semiconductor and LED solutions. For the latest news, please visit Samsung Newsroom at http://news.samsung.com

Hospitality Display

For more information about Samsung Hospitality Displays, visit www.samsung.com/business or www.samsung.com/displaysolutions

Copyright © 2020 Samsung Electronics Co. Ltd. All rights reserved. Samsung is a registered trademark of Samsung Electronics Co. Ltd. Specifications and designs are subject to change without notice. Non-metric weights and measurements are approximate. All data were deemed correct at time of creation. Samsung is not liable for errors or omissions. All brand, product, service names and logos are trademarks and/or registered trademarks of their respective owners and are hereby recognized and acknowledged.

Samsung Electronics Co., Ltd. 416, Maetan 3-dong, Yeongtong-gu, Suwon-si, Gyeonggi-do 443-772, Korea

