



The on-the-go monitor that's ready to work in any light

Double down on your productivity with the HP E14 G4 Portable Monitor. Remove from the soft sleeve, stand up on the kickstand, and connect with the simplicity of just one USB-C™ cable.^[1] Enjoy a great view indoors or outdoors from an extra-bright screen.



Work anywhere

Get a clear view wherever the day takes you—inside or out—with an ultra-bright, anti-glare, 400-nit screen that delivers equally sharp visuals in dark rooms or direct sunlight.

Portable dual-screen productivity

Expand your laptop's visual workspace and boost your productivity with a slim, lightweight Full HD monitor that weighs just 640 g and is less than 4.75 mm thick, so you can slide it into your carrying case with your device without weighing you down.

Conserve your laptop's battery life

Work without interruption with a monitor that requires half the power of its predecessor. An integrated 65W power pass-through powers your monitor from your laptop's USB-C™ while it charges from its power brick at the same time.

Featuring

Easy USB-C™ efficiency

Set up quickly with just one USB-C™ cable that transfers video and powers your monitor from your laptop.^[1]

Share-worthy visuals

Slide the monitor out of the sleeve to reveal the 14" diagonal IPS glass panel screen with 1920 x 1080 resolution, a 16:9 aspect ratio, and fast 5 ms response time—perfect for single and group viewing.^[2]

Form meets function

Carry a display that sets a style standard with an aesthetic that complements HP PCs. The soft, easy-to-carry sleeve helps protect the display when you're on the move. Find a comfortable viewing position with the adjustable kickstand on the back.

Customize your settings

Control brightness, contrast, and response time, and activate HP Low Blue Light mode to filter blue light emission and shift colors to a warmer spectrum for more comfortable viewing, all from the intuitive OSD.

Global reassurance

Rest assured that your IT investment is supported by a three-year standard limited warranty. To extend your protection, select an optional HP Care service.^[3]

Specifications

Display size (diagonal)	14"
Panel technology	IPS
Display size (diagonal)	35.56 cm (14")
Aspect ratio	16:9 ^[1]
Native resolution	FHD (1920 x 1080) ^[1]
Resolutions supported	1024 x 768; 1280 x 1024; 1280 x 720; 1440 x 900; 1600 x 900; 1680 x 1050; 1920 x 1080; 640 x 480; 720 x 400; 800 x 600
Pixel pitch	0.161 mm
Brightness	400 nits ^[1]
Contrast ratio	800:1 static ^[1]
Response time (typical)	5ms GtG (with overdrive) ^[1]
Dimensions With Stand (W x D x H)	32.14 x 1.52 x 21 cm
Weight	0.64 kg
Weight	1.41 lb
Display features	On-screen controls; Low blue light mode; Anti-glare
Display Input Type	2 SuperSpeed USB Type-C® 5Gbps signaling rate (Alt mode DisplayPort™ 1.2)
Onscreen controls	Brightness; Exit; Information; Management; Power control; Input control; Menu control; Image; Color
Display scan frequency (horizontal)	30-80 KHz
Display scan frequency (vertical)	59-60 Hz
Power	PD Power 5v
Power consumption	7.5 W (maximum), 6 W (typical), 0.3 W (standby)
Operating temperature range	5 to 35°C
Operating humidity range	20 to 80% RH
Sustainable impact specifications	Arsenic-free display glass; Low halogen; Mercury-free display backlights
Certifications and compliances	BIS; BSMI; CB; CCC; CE; cTUVus; EAC; ENERGY STAR®; FCC; ICES; ISE for Cambodia; ISO 9241-307; KC/KCC; NOM; SEPA; Taiwan Green Mark; TUV/GS; VCCI; Vietnam MEPS; WEEE; ISC; WW application; UAE
UPC number	(AB1) 194850687785; (AB2) 194850687808; (ABA) 194850333804; (ABB) 195122635008; (ABG) 195122771492; (ABM) 195122417208; (ABT) 194850710292; (AC3) 194850333811; (ACJ) 194850687792; (AR6) 195122417215
What's in the box	Monitor; Documentation; USB Type-C™ cable; QSP; Sleeve

Top Recommended Displays, Accessories and Services

No Top Recommended Displays, Accessories and Services

Messaging Footnotes

[1] Cable included. 5v@3A from the connected device required for power to the display. Video over USB-C™ requires a device with USB-C™ DisplayPort™ Alt mode or Thunderbolt™ 3.

[2] All performance specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

[3] HP Care Packs sold separately. Service levels and response times for HP Care Packs may vary depending on your geographic location. Service starts on date of hardware purchase. Restrictions and limitations apply. For details, visit www.hp.com/go/cpc. HP Services are governed by the applicable HP terms and conditions of service provided or indicated to Customer at the time of purchase. Customer may have additional statutory rights according to applicable local laws, and such rights are not in any way affected by the HP terms and conditions of service or the HP Limited Warranty provided with your HP Product.

Technical Specifications Footnotes

[1] All specifications represent the typical specifications provided by HP's component manufacturers; actual performance may vary either higher or lower.

© Copyright 2020 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

USB Type-C™ and USB-C™ are trademarks of USB Implementers Forum. DisplayPort™ and the DisplayPort™ logo are trademarks owned by the Video Electronics Standards Association (VESA®) in the United States and other countries. Thunderbolt is a trademark of Intel Corporation or its subsidiaries in the U.S. and/or other countries.

