


## Key Features

TWO MONITORS IN A SINGLE PACKAGE | ACCURATE FROM ALL ANGLES: SUPERCLEAR™ IPS TECHNOLOGY | FRAMELESS DESIGN | VERSATILE CONNECTIVITY | FULL HD 1080P RESOLUTION



## Product Description

The ViewSonic™ VA2256-mhd\_H2 dual monitor pack delivers an efficient end-to-end enterprise experience. From easy installation, to recycling, to long-term reliability, this dual monitor solution reduces the total cost of ownership beyond the initial purchase price. Sold as a dual pack of monitors without monitor stands, the VA2256-mhd\_H2 ships in biodegradable packaging to minimize recycling costs and waste. Standard VESA-compatible mounting offers easy dual-screen installation, while a 3-sided thin bezel design provides a seamless viewing experience for multi-monitor setups. SuperClear™ IPS panel technology delivers wide-angle viewing and incredibly vivid colors. Extensive connectivity options include VGA, HDMI, and DisplayPort so that you can connect to a variety of HD and analog devices – today and tomorrow.



1. Menu Controls
2. VESA Compatible Wall Mount - 100 x 100 mm
3. DisplayPort In

4. HDMI
5. Internal Speakers
6. Kensington® Lock Slot
7. Audio In




8. Audio Out
9. VGA



22" DISPLAY



IPS PANEL



1920 x 1080 RESOLUTION

### Contact Sales

- call: 888.881.8781
- email: [salesinfo@viewsonic.com](mailto:salesinfo@viewsonic.com)
- visit: [viewsonic.com](http://viewsonic.com)

Display:	
Display Size (in.):	22
Viewable Area (in.):	21.5
Panel Type:	IPS
Resolution:	1920 x 1080
Resolution type:	Full HD (1920x1080)
Static Contrast Ratio:	1,000:1
Dynamic Contrast Ratio:	50,000,000:1
Light Source:	LED
Brightness:	250 cd/m <sup>2</sup>
Colors:	16.7M
Aspect Ratio:	16:9
Response Time (Typical @ 60Hz):	5ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30,000
Panel Surface:	Anti-glare

Compatibility:	
PC Resolution (max):	1920x1080
Mac® Resolution (max):	1920x1080

Connector:	
3.5mm Audio In(1), 3.5mm Audio Out(1), HDMI In(1), VGA(1)	

Audio:	
Internal Speakers:	7W (x2)

Power:	
Eco Mode (Conserve):	18W
Eco Mode (Optimized):	22W
Consumption (typical):	23W
Consumption (max):	31W
Voltage:	100-240 VAC, 50-60Hz
Stand-by:	0.5W
Power Supply:	Internal

Controls:	
Physical Controls:	Key 1 (favorite), Key 2, Key 3, Key 4, Key 5, Key 6 (power)
On Screen Display:	Input Select, Audio Adjust, View Mode, Color Adjust, Manual Image Adjust, Setup Menu

Operating Conditions:	
Temperature:	32-104° F (0 - 40° C)
Humidity (non-condensing):	20-90%

Weight (imperial):	
Net Without Stand (lbs):	12.8
Gross (lbs):	18.5

Weight (metric):	
Net Without Stand (kg):	5.8
Gross (kg):	8.4

Dimensions (imperial) (WxHxD):	
Packaging (in.):	21.4 x 15.7 x 7.1
Physical Without Stand (in.):	19.3 x 11.7 x 1.9

Dimensions (metric) (WxHxD):	
Packaging (mm):	544.0 x 400.0 x 180.0
Physical Without Stand (mm):	490.0 x 297.0 x 48.0

General:	
Regulations:	eUlus FCC-B, ICES003, Energy Star Certified, EPEAT Certified, MX-CeC, Mexico Energy
Packaging Contents:	VA2256-MHD_H x2, 3-pin Plug (IEC C13 / CFF22) x2, HDMI Cable (v1.4: Male-Male) x1, DisplayPort Cable (v1.2: Male-Male) x1, Quick Start Guide x2
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Warranty:	Three-year limited warranty on parts, labor and backlight
UPC:	766907009873

Accessories:	
CB-00008948, CB-00010555, CB-00010684, CB-00010958, ICID-CAB1H-001, ICID-CMK-001, ICID-IDMA-001, ICID-IDMA-002, ICID-WMK-001, cb-00011486	