

# ThinkBook 14s Yoga ITL 20WE0014US

**Product**

ThinkBook 14s Yoga ITL

**Region**

NA

**Country/Region**

USA

**Machine Type**

20WE

**TopSeller**

TopSeller

**Processor**

Intel Core i5-1135G7 (4C / 8T, 2.4 / 4.2GHz, 8MB)

**Graphics**

Integrated Intel Iris Xe Graphics

**Chipset**

Intel SoC Platform

**Memory**

8GB Soldered DDR4-3200

**Storage**

256GB SSD M.2 2242 PCIe 3.0x4 NVMe

**Display**

14" FHD (1920x1080) IPS 300nits Glossy, Glass, 100% sRGB, Touch

**Touchscreen**

10-point Multi-touch

**Pen**

ThinkBook Yoga Integrated Smart Pen without Battery

**Optical**

None

**Card Reader**

MicroSD Card Reader

**Ethernet**

None

**WLAN + Bluetooth**

Intel AX201 11ax, 2x2 + BT5.1

**Camera**

720p with ThinkShutter

**Microphone**

2x, Array

**Case Color**

Mineral Grey

**Surface Treatment**

Anodizing sandblasting

**Case Material**

Aluminium (Top), Aluminium (Bottom)

**Keyboard**

Backlit, English (US)

**Fingerprint Reader**

Touch Style

**Security Chip**

Discrete TPM 2.0

**Battery**

Integrated 60Wh

**Power Adapter**

65W USB-C

**Operating System**

Windows 10 Pro 64, English

**Bundled Software**

Office Trial

**Base Warranty**

1-year, Depot

**Bundled Service**

None

**EAN / UPC / JAN**

195348295314

**End of Support**

2027-05-30

**Announce Date**

2020-09-21

**Recommended Services****Best**

3Y Lenovo Protect (Premier Support + Keep Your Drive + Accidental Damage Protection) (5PS0N73156)

**Better**

3Y Lenovo Support (Premier Support + Keep Your Drive) (5PS0N73153)

**Good**

3Y Premier Support Upgrade from 1Y Depot/CCI (5WS0T36151)

**Notes:****California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

**L** [WWW.LENOVO.COM](http://WWW.LENOVO.COM)

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2020. All rights reserved.



# ThinkBook 14s Yoga ITL Platform Specifications

Product Specifications Reference (PSREF)

Processor	11th Generation Intel® Core™ i5 / i7 Processor									Media reader Ports	MicroSD card reader One Thunderbolt 4 / USB4 40Gbps (with the function of PD 3.0 and DP 1.4), one USB-C 3.2 Gen 2 (with the function of PD 3.0 and DP 1.4), two USB 3.2 Gen 1 (one Always On), HDMI 1.4, MicroSD card reader, headphone / microphone combo jack, security keyhole <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i>	
	Processor Number	# of Cores	# of Threads	Base Frequency	Max Turbo Frequency	Cache	Memory Types	Processor Graphics				
	i5-1135G7	4	8	2.4 GHz	4.2 GHz	8MB	DDR4-3200	Intel Iris® Xe Graphics				
i7-1165G7	2.8 GHz			4.7 GHz	12MB							
Graphics	Intel Iris Xe Graphics in processor; supports up to 4 independent displays via native display and 3 external monitors; supports external monitors via HDMI (up to 4096x2304 @30Hz), USB Type-C (up to 5120x3200 @60Hz) or Thunderbolt™ (up to 7680x4320 @30Hz)									Camera	HD720p camera with ThinkShutter, fixed focus, integrated dual array digital microphone	
Chipset	Intel SoC (System on Chip) platform									Audio support	HD Audio, Realtek® ALC3287 codec, HARMAN speakers, 2W x 2, Dolby Audio™, dual array digital microphone, headphone / microphone combo jack	
Memory	40GB max / 3200MHz DDR4, dual-channel capable, 8GB memory soldered to systemboard, one DDR4 SO-DIMM slot									Keyboard	6-row, spill-resistant, multimedia Fn keys, LED backlight	
Display	Size	Resolution	Surface	Touch	Type	Brightness	Aspect Ratio	Contrast Ratio	Color Gamut	Viewing Angle	Touchpad	Buttonless Mylar surface multi-touch touchpad, supports Precision TouchPad
	14.0"	FHD (1920x1080) Dolby Vision™	Glossy	Multi-touch	IPS	300 nits	16:9	1200:1	100% sRGB	170°	Security	Power-on password, hard disk password, supervisor password, Kensington Nano security slot
											Security chip	Discrete TPM 2.0, TCG Certified
Multi-touch	OGM with OCA direct bonding, capacitive-type multi-touch, supports 10-finger gesture, Corning® Gorilla® Glass, Anti-Fingerprint (AF) coating									Fingerprint reader	Touch style fingerprint reader on side power button	
Hinge	Yoga hinge, 360 degree									Battery	Integrated Li-Polymer 60Wh battery, supports rapid charge (charge up to 80% in 1hr)	
Convertible mode	Laptop, tent, stand and tablet									Max battery life	<i>MobileMark® 2018: 8.4 hr</i> <i>* Battery life varies significantly with hardware configurations, settings, usage, &amp; other factors</i>	
Pen	ThinkBook Yoga Integrated Smart Pen (battery need to be purchased separately)									AC adapter	65W USB-C AC adapter	
Storage	Up to two drives • M.2 2242 SSD / PCIe NVMe, PCIe 3.0 x 4 • M.2 2280 SSD / PCIe NVMe, PCIe 3.0 x 4									Preload (optional)	<i>Preloaded operating system</i> • Windows® 10 Home 64 • Windows 10 Pro 64 <i>Preloaded applications (only some listed)</i> • Microsoft® 365 Personal • Microsoft 365 Family • Microsoft Office Home and Business 2019 • Microsoft Office Home and Student 2019 • Microsoft Office Professional 2019 • Microsoft Office Personal 2019 • Microsoft Office Trial (with 30-day license)	
Optical	None									Limited warranty	<i>One of the following, configurable by model:</i> • 1-year depot repair service • 1-year depot with 2-year system board repair service • 2-year/1-yr battery depot repair service	
Ethernet	None									Mil-Spec test	Work in progress	
WLAN + Bluetooth™	One of the following, configurable by model: • 802.11ac 2x2 Wi-Fi + Bluetooth 5.0, M.2 card • Intel Wi-Fi 6 AX201, Wi-Fi 2x2 802.11ax + Bluetooth 5.1, M.2 card <i>* Intel WiFi 6 full features might be limited by country level restrictions</i> <i>* BT5.1 is supported on Windows 10 version 2004 or above (limited to BT5.0 on earlier version)</i>									Environment	ENERGY STAR® 8.0; ErP lot3; TUV Low Blue Light certified; RoHS-compliant	
Dimensions	WxDxH: 12.60" x 8.62" x 0.67"; 320mm x 216mm x 16.9mm											
Weight	Starting at 3.31 lbs / 1.5 kg											
Case color	Mineral grey or abyss blue, dual tone design											
Case material	Top cover: Aluminum Bottom: Aluminum											

The specifications above may not be available in all regions and might change by regions

Lenovo  
November 2020



# ThinkBook 14s Yoga ITL

Lenovo™

