

4-Port DisplayPort/USB KVM Switch - 4K 60 Hz, HDR, HDCP 2.2, IR, DP 1.4, USB Sharing

MODEL NUMBER: B005-DPUA4



Controls 4 DisplayPort-enabled desktop or notebook computers using one centralized DisplayPort or HDMI monitor and USB keyboard/mouse.

Features

Connects 4 DisplayPort-Enabled Devices to a Single Monitor, Keyboard and MouseThis KVM switch lets you access, control, boot and reboot four computers with DisplayPort connectors and switch between them. In addition to desktop and notebook computers, the switch also connects up to four media centers, video game systems, Blu-ray and DVD players, cable and satellite boxes, DVRs and other DisplayPort-enabled devices. All computers share one monitor, USB keyboard and USB mouse, which saves space on your desk or workspace.

Supports DisplayPort++ for Connecting an HDMI or DisplayPort MonitorThe B005-DPUA4 supports DP++, allowing incoming DisplayPort signals to be converted to HDMI. It features one DisplayPort output and one HDMI output, though only one monitor may be used at a time.

Switching Between Computers Is Fast and EasyUse the front-panel push buttons, hotkey commands, mouse movement or the included IR remote control for quick and easy toggling between computers. You can also use the Auto Scan feature to scan all connected computers in five-second intervals automatically. LEDs indicate which computer is currently selected. Please note: The included IR remote requires a battery in order to work.

USB Hub Lets You Share Peripherals between ComputersTwo USB 3.0 hub ports allow you to share USB peripherals, such as printers, hard drives, scanners, webcams and flash drives, between both connected computers. The ports support USB 3.0 data transfer speeds up to 5 Gbps and are backward compatible with earlier USB generations.

Transmits Crystal-Clear True 4K Video with HDR and 4:4:4 Color The B005-DPUA4 supports Ultra HD resolutions up to 4096 x 2160 (4K x 2K) at 60 Hz, as well as HDR video, providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This KVM switch also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

Designed for Convenient Mounting with Included BracketsThe heavy-duty metal housing comes with mounting brackets for permanent installation on a wall or beneath a desk with user-supplied hardware. The included DC power supply connects to any standard AC power source.

Highlights

- Supports UHD resolutions up to 4K @ 60 Hz (4:4:4) for crystalclear video
- Carries High Dynamic Range (HDR) signals for expanded color accuracy
- Dual-mode DisplayPort (DP++) support allows connection of a local HDMI display
- Dual USB 3.0 hub ports let you share USB peripherals among connected computers
- Push buttons, hotkeys and included IR remote allow easy toggling between computers

Applications

- Share a keyboard, mouse and screen with up to 4 computers
- Connect up to 4 gaming consoles, media centers or other A/V devices for a home theater system with 4K resolution
- Save money and space by sharing USB peripherals, such as a printer and external hard drive, among 4 connected computers

System Requirements

- Console with DisplayPort or HDMI monitor, USB keyboard/mouse and (optional) speakers with 3.5 mm connectors
- Computers with DisplayPort connector, USB-A port and (optional) 3.5 mm audio jack
- Windows, macOS or Linux operating system

Package Includes

- B005-DPUA4 4-Port DisplayPort/USB KVM Switch
- IR extender
- IR remote control
- External power supply (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V 3A)
- Mounting brackets
- Owner's manual



Specifications

OVERVIEW		
UPC Code	037332255020	
Technology	DisplayPort; HDMI; Stereo Audio	
VIDEO		
Max Supported Video Resolution	4K x 2K (4096 x 2160) @ 60 Hz (HDMI and DisplayPort)	
Max Supported Color Depth	36-bit Deep Color	
HDR Support	Yes	
3D Video Supported	Yes	
Chroma Sub Sampling	4:2:0; 4:2:2; 4:4:4	
AUDIO		
Audio Specification	7.1 Surround Sound	
INPUT		
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240	
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 5-15P North America	
Bus Powered	No	
POWER		
External Power Supply Input Specs (V / Hz / A)	100-240V; 50/60Hz; 0.6A	
External Power Supply Output Specs (V / A)	5.0V, 3.0A	
External Power Supply Cord Length (ft.)	3.5	
DC Barrel Plug	OD: 5.5 x 2.5 x 16.5mm, Positive Pin, Negative Sleeve	
External Power Supply Certifications	CCC; UL; cUL	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	White (KVM Port LED's) = Port in use; White (Power LED) = Power On; Green = Online	
PHYSICAL		
Color	Black	
Material of Construction	Metal	
Rackmountable	No	



Tripp Lite 1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

Unit Dimensions (hwd / in.)	1.02 x 9.57 x 2.95	
Unit Dimensions (hwd / mm)	26 x 243 x 75	
Unit Packaging Type	Box	
Unit Weight (kg)	0.50	
Unit Weight (Ibs.)	1.11	
ENVIRONMENTAL		
Operating Temperature Range	32 to 113°F (0 to 45°C)	
Storage Temperature Range	14 to 176°F (-10 to 80°C)	
Power Consumption (Watts)	11.75	
Operating Humidity Range	10% to 85% RH (No Condensation)	
Storage Humidity Range	5% to 90% RH (No Condensation)	
ESD Protection	+/- 8kV (air-gap discharge); +/- 4kV (contact discharge)	
COMMUNICATIONS		
Hotkey	Yes	
IP Remote Access	No	
IR Remote Extension Support	Yes	
CONNECTIONS		
Ports	4	
PC/Server Connections	DisplayPort; HDMI	
Side A - Connector 1	(3) 3.5MM (FEMALE)	
Side A - Connector 2	(2) USB 3.0 A (FEMALE)	
Side B - Connector 1	(2) USB A (FEMALE)	
Side B - Connector 2	HDMI (FEMALE)	
Side B - Connector 3	(4) USB 3.0 B (FEMALE)	
Side B - Connector 4	(5) DISPLAYPORT (FEMALE)	
Side B - Connector 5	(10) 3.5MM (FEMALE)	
Side B - Connector 6	3.5mm x 1.35mm (5V DC Barrel)	
Computer Keyboard and Mouse Interface	USB	
Computer Monitor Interface	Displayport; HDMI	
Console Keyboard and Mouse Interface	USB	
Console Monitor Interface	Displayport	
FEATURES & SPECIFICATIONS		



Autoscan (Y,N)	Υ	
Autoscan Duration	5 to 999 seconds	
Number of Users	1	
NIAP-Certified Secure	No	
On-Screen Display (OSD)	No	
Port Selection	Hotkey; Mouse; Pushbutton; Remote Selector	
Displayport Specification	1.4	
HDCP Specification	1.4; 2.2	
USB Hub Ports	Yes	
Number of USB Hub Ports	4	
USB Specification	USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)	
Driver Required	No	
Common Access Card (CAC) Support	No	
Cat5 KVM Switch	No	
STANDARDS & COMPLIANCE		
Certifications	CE, FCC, RoHS, REACH	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: https://www.tripplite.com/products/product-certification-agencies