

Tripp Lite

1111 W. 35th Street Chicago, IL 60609 USA Telephone: 773.869.1234 www.tripplite.com

# 4-Port HDMI/USB KVM Switch - 4K 60 Hz, HDR, HDCP 2.2, IR, USB Sharing

### MODEL NUMBER: B005-HUA4











Controls 4 HDMI-enabled desktop or notebook computers using one centralized HDMI monitor and USB keyboard/mouse.

#### **Features**

Connects 4 HDMI-Enabled Devices to a Single HDMI Monitor, Keyboard and Mouse This KVM switch lets you access, control, boot and reboot four computers with HDMI ports and switch between them. In addition to desktop and notebook computers, the switch also connects up to four media centers, video game systems, Blu-ray and DVD players, cable and satellite boxes, DVRs and other HDMI-enabled devices. All computers share one HDMI monitor, USB keyboard and USB mouse, which saves space on your desk or workspace.

**Switching Between Computers Is Fast and Easy**Use the front-panel push buttons, hotkey commands, mouse movement or the included IR remote control for quick and easy toggling between computers. You can also use the Auto Scan feature to scan all connected computers in five-second intervals automatically. LEDs indicate which computer is currently selected.

**USB Hub Lets You Share Peripherals Between Computers**Two USB 3.0 hub ports allow you to share USB peripherals, such as printers, hard drives, scanners, webcams and flash drives, between all connected computers. The hub is backward compatible with USB 1.1 devices.

Transmits Crystal-Clear True 4K Video with HDR and 4:4:4 ColorThe B005-HUA4 supports Ultra HD resolutions up to 4096 x 2160 (4K x 2K) at 60 Hz, as well as 7.1-channel surround sound and HDR video, providing a wide range of vibrant colors with richer contrast, brighter whites and deeper blacks that pop on your 4K display. HDCP 2.2 compliance allows you to stream 4K Amazon and Netflix content with no complications. This KVM switch also supports 4:4:4 chroma subsampling for top-level PC gaming or using your HDTV as a PC monitor.

**Designed for Convenient Mounting with Included Brackets**The heavy-duty metal housing comes with mounting brackets for permanent installation on a wall or beneath a desk with user-supplied hardware. The included DC power supply connects to any standard AC power source. The plug-and-play B005-HUA4 requires no drivers, so you can connect and use it immediately. It works with all major operating systems, including Windows, macOS and Linux.

#### **Highlights**

- Supports UHD resolutions up to true 4K @ 60 Hz (4:4:4) for crystal-clear video
- Carries High Dynamic Range (HDR) signals for expanded color accuracy
- Dual USB 3.0 hub ports let you share USB peripherals among connected computers
- Push buttons, hotkeys and included IR remote allow easy toggling between computers
- Works with all major operating systems, including Windows, macOS and Linux

#### **Applications**

- Share a keyboard, mouse and HDMI display with 4 computers
- Connect 4 gaming consoles, media centers or other A/V devices for a home theater system with true 4K resolution
- Save money and space by sharing USB peripherals, such as a printer and external hard drive, between 4 connected computers

#### **System Requirements**

- Console with HDMI monitor, USB keyboard/mouse and (optional) speakers with 3.5 mm connectors
- Computer with HDMI port, USB-A port and (optional) 3.5 mm audio jack
- Windows, macOS or Linux operating system

#### **Package Includes**

- B005-HUA4 4-Port HDMI/USB KVM Switch
- IR extender
- IR remote control
- External power supply (Input: 100–240V, 50/60 Hz, 0.5A; Output: 5V 3A)
- Mounting brackets
- Owner's manual

## **Specifications**





OVERVIEW		
UPC Code	037332254900	
Technology	HDMI; USB 2.0 (High Speed)	
VIDEO		
Max Supported Video Resolution	4K x 2K (4096 x 2160) @ 60 Hz	
Max Supported Color Depth	36-bit Deep Color	
HDR Support	Yes	
3D Video Supported	Yes	
Chroma Sub Sampling	4:2:0; 4:2:2; 4:4:4	
AUDIO		
Audio Specification	7.1 Surround Sound	
INPUT		
Voltage Compatibility (VAC)	100; 110; 120; 125; 127; 200; 208; 220; 230; 240	
External Power Supply Plug(s)	AS/NZS 3112 Australia; BS 1363 UK; CEE 7/16 Schuko; NEMA 5-15P North America	
Bus Powered	No	
POWER		
External Power Supply Input Specs (V / Hz / A)	100-240V, 50/60Hz, 0.6A	
External Power Supply Output Specs (V / A)	5V/3A	
External Power Supply Cord Length (ft.)	4	
DC Barrel Plug	OD: 5.5 x 2.5 x 16.5mm, Positive Pin, Negative Sleeve	
External Power Supply Certifications	CCC; UL; cUL	
USER INTERFACE, ALERTS & CONTROLS		
LED Indicators	White (KVM Port LED's) = Port in use; White (Power LED) = Power On; Green = Online	
PHYSICAL		
Color	Black	
Material of Construction	Metal	
Rackmountable	No	
Unit Dimensions (hwd / in.)	1.02 x 9.57 x 2.95	
Unit Dimensions (hwd / mm)	26 x 243 x 75	
Unit Packaging Type	Вох	



ENVIRONMENTAL		
Operating Temperature Range	32 to 113°F (0 to 45°C)	
Storage Temperature Range	14 to 176°F (-10 to 80°C)	
Power Consumption (Watts)	12.15	
Operating Humidity Range	10% to 85% RH (No Condensation)	
Storage Humidity Range	5% to 90% RH (No Condensation)	
ESD Protection	+/- 8kV (air-gap discharge) & +/- 4kV (contact discharge)	
COMMUNICATIONS		
Hotkey	Yes	
IP Remote Access	No	
IR Remote Extension Support	Yes	
CONNECTIONS		
Ports	4	
PC/Server Connections	НОМІ	
Side A - Connector 1	(3) 3.5MM (FEMALE)	
Side A - Connector 2	(2) USB 3.0 A (FEMALE)	
Side B - Connector 1	(2) USB A (FEMALE)	
Side B - Connector 2	(5) HDMI (FEMALE)	
Side B - Connector 3	(4) USB 3.0 B (FEMALE)	
Side B - Connector 4	(10) 3.5MM (FEMALE)	
Side B - Connector 5	3.5mm x 1.35mm (5V DC Barrel)	
Computer Keyboard and Mouse Interface	USB	
Computer Monitor Interface	HDMI	
Console Keyboard and Mouse Interface	USB	
Console Monitor Interface	НОМІ	
FEATURES & SPECIFICATIONS		
Autoscan (Y,N)	Y	
Autoscan Duration	5 to 999 seconds	
Number of Users	1	
NIAP-Certified Secure	No	
Port Selection	Hotkey; Mouse; Pushbutton; Remote Selector	
HDCP Specification	1.4; 2.2	



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USB Hub Ports	Yes	
Number of USB Hub Ports	4	
USB Specification	USB 2.0 (up to 480 Mbps); USB 3.0 (up to 5 Gbps); USB 3.1 Gen 1 (up to 5 Gbps)	
Driver Required	No	
Common Access Card (CAC) Support	No	
Cat5 KVM Switch	No	
STANDARDS & COMPLIANCE		
Certifications	CE, FCC, RoHS, REACH	
WARRANTY		
Product Warranty Period (Worldwide)	3-year limited warranty	

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <a href="https://www.tripplite.com/products/product-certification-agencies">https://www.tripplite.com/products/product-certification-agencies</a>