



Solid State Drive Desktop & Laptop SATA Connection

FEATURES

- 76800GB Unformatted - 1GB = 1 billion bytes - Formatted capacity is less based on OS and configuration
- S.M.A.R.T. support
- DEVSLP support
- SATA 3.2 Compliant SATA 6Gb/s – backwards compatible with SATA 3Gb/s and 1.5Gb/s
- ATA/ATAPI-8-ACS3 command set compliant
- Industry-standard 512 byte sector support
- Temperature sensor
- RoHS-compliant package
- 3D TLC NAND

WARRANTY

- 3 Year Limited
- Lifetime US-Based Technical Support
www.VisionTek.com
1-866-883-5411

The VisionTek 8TB TLC 7mm 2.5" SSD is designed to bring ultra-fast, reliable storage to system users. The 8TB Class SSD has 7.68TB user accessible raw space, formatted space will be less depending on OS and configuration. With the shift from the hard disk drive to the solid state drive, our TLC Series SSDs are a drop-in replacement option for a hard disk drive (HDD). They deliver superior reliability, durability, power efficiency and performance - keeping your system working reliably in the toughest of conditions.

Conforming to the industry standard SATA connector specification, these SSDs integrate easily into existing storage infrastructures. The VisionTek TLC Series SSDs provide high bandwidth and IOPS while efficiently managing write amplification. Employing SSD technology in a system enables faster boot times, quicker application load times, lower power consumption, and enhanced reliability.



Speed & Performance

Start your system in seconds, load files almost instantly, and accelerate the most demanding applications with the VisionTek TLC SSD drives. Our Dynamic Write Acceleration technology uses an adaptable pool of high-speed, single-level cell flash memory to generate blistering speeds.



Install with confidence

For many people, opening a computer and transferring data seems terrifying. That's why we've made it easy in the step-by-step SSD Install Guide. Check it out before you buy, then install your own SSD quickly with everything transferred over successfully and hassle-free.

8TB Class with 7.680TB User Accessible Space

Save massive amounts of photos, music, and videos comfortably and securely. With fast access to your media, creations, and designs, you're ready to share at the speed of life.





Endurance

- TBW: Up to 14826TB
- DWPD: 0.1 (3 Years)

Security

- User selectable ATA password support
- Secure Erase support

Reliability

- MTBF: 1.5 million device hours*
- End-to-End Data Protection
- Built-in LDPC ECC provides the most-powerful data correction level in use today
- Static and dynamic wear leveling
- Uncorrectable Bit Error Rate: ≤ 1 sector per 10^{17} bits read

Electrical/Mechanical

- +5VDC ($\pm 5\%$) power supply
- Power Consumption: up to 4.7W (Active), 1.8W (Idle)
- 2.5-inch form factor: 100 x 69.85 x 7mm
- Weight: 60g

Environmental

- Operating temperature: 0-70°C
- Non-Operating temperature: -40-85°C
- Operating humidity: 5-95% relative
- Shock: 1500G/0.5ms
- Vibration: 20-80Hz, 1.52mm | 80-2000Hz, 20G

Capacity	VisionTek Part Number	UPC	Max Sequential Read (up to)	Max Sequential Write (up to)	Max 4K Random Sequential Read (up to)	Max 4k Random Sequential Write (up to)	Access Time
8TB	901414	784090040879	550 MB/s	520 MB/s	80K IOPS	72K IOPS	<0.1ms

*7680GB (7.68TB) Unformatted. 1 GB = 1 billion bytes. Formatted capacity will be less depending on OS and configuration

V 11.11.2020

All specifications are subject to change without notice. Products may not be available in all markets. The VisionTek name and design are registered trademarks of VisionTek Products, LLC. All other registered and unregistered trademarks are the property of their respective owners.

FOR MORE INFORMATION CONTACT: 1-866-883-5411 | sales@visiontek.com