

Key Features

Wide Quad HD Resolution | 144Hz Refresh Rate | Ultra-Fast

Response Time | AMD FreeSync™ Premium | SuperClear

IPS Technology



Product Description

The ViewSonic® VX2768-2KP-MHD is a 27" WQHD IPS gaming monitor built for gaming and entertainment. Featuring a 144Hz refresh rate and AMD FreeSync Premium technology, this monitor virtually eliminates screen tearing and stuttering for fluid game play during fast-paced action scenes. An ultra-fast 1ms (MPRT) response time also provides smooth screen performance free from blurring or ghosting. For a game-winning competitive edge, Game Mode hot keys optimize gameplay for FPS, RTS and MOBA game genres. With a sleek frameless design, the VX2768-2KP-MHD provides a seamless viewing experience for multi-monitor gaming setups. Flexible connectivity options such as DisplayPort and HDMI allow you to connect to your dedicated graphics card and gaming console. The VX2768-2KP-MHD features all the perks needed to dominate your gaming and entertainment quests.



1. VESA Compatible Mount 100 x 100mm
2. Menu Controls
3. AC In


4. Kensington® Lock Slot
5. 3.5mm Audio Out
6. DisplayPort In
7. HDMI 2.0 (x2)



27" DISPLAY



IPS PANEL



2560 x 1440 RESOLUTION

Contact Sales

- call: 888.881.8781
- email: salesinfo@viewsonic.com
- visit: viewsonic.com

Display:	
Display Size (in.):	27
Viewable Area (in.):	27
Panel Type:	IPS
Resolution:	2560 x 1440
Resolution type:	WQHD (2560x1440)
Static Contrast Ratio:	1,000:1
Dynamic Contrast Ratio:	80,000,000:1
Brightness:	350 cd/m ²
Colors:	1.07B
Color Space Support:	10 bit (8 bit + 1 RC)
Aspect Ratio:	16:9
Response Time (Typical @ 60):	3ms
Response Time (MPRT):	1ms
Viewing Angles:	178° horizontal, 178° vertical
Backlight Life (Hours):	30,000
Panel Surface:	Anti-Glare type, Hard-coating (3H), Haze 25%
Refresh Rate (Hz):	144
Adaptive Sync:	AMD FreeSync™ Premium

Compatibility:	
PC Resolution (max):	2560 x 1440
Mac® Resolution (max):	2560 x 1440

Connector:	
3.5mm Audio Out(1), HDMI 2.0 In(2), DisplayPort(1)	

Audio:	
Internal Speakers:	2W (x2)

Power:	
Eco Mode (Conserve):	25W
Eco Mode (Optimized):	32W
Consumption (typical):	38W
Consumption (max):	55W
Voltage:	AC: 100-240V (universal), 50-60Hz
Stand-by:	0.5W
Power Supply:	Internal

Additional Hardware:	
Kensington Lock Slot:	1

Controls:	
Physical Controls:	Key 1 (favorite), Key 2, Key 3, Key 4, Key 5, Key 6 (power)
On-Screen Display:	Input Select, Audio Adjust, View Mode, Color Adjust, Manual Image Adjust, Setup Menu

Operating Conditions:	
Temperature:	32-104° F (0 - 40° C)
Humidity (non-condensing):	20-90%

Mount:	
VESA Compatible:	100 x 100 mm

Video Signal:	
Frequency Horizontal:	15 - 255 KHz
Frequency Vertical:	48 - 144 Hz

Ergonomics:	
Tilt (Forward/Back):	3° / 21°

Weight (imperial):	
Net (lbs):	11.5
Net Without Stand (lbs):	9.7
Gross (lbs):	15.2

Weight (metric):	
Net (kg):	5.2
Net Without Stand (kg):	4.4
Gross (kg):	6.9

Dimensions (imperial) (WxHxD):	
Packaging (in.):	26.7 x 20.5 x 6.0
Physical (in.):	24.1 x 17.7 x 7.9
Physical Without Stand (in.):	24.1 x 14.5 x 7.2

Dimensions (metric) (WxHxD):	
Packaging (mm):	677.0 x 520.0 x 152.0
Physical (mm):	613.0 x 451.0 x 200.0
Physical Without Stand (mm):	613.0 x 368.0 x 55.0

General:	
Regulations:	eU/VvUs, I.C.C.-B, ICES003, C.F.C., MX-CoC, Mexico Energy
PACKAGE CONTENTS:	VX2768-2KP-MHD, Power Cable, HDMI Cable, Quick Start Guide
Recycle/Disposal:	Please dispose of in accordance with local, state or federal laws.
Warranty:	Three-year limited warranty on parts, labor and backlight

UPC:	766907010534
------	--------------

Accessories:	
CB-00008948, CB-00009950, CB-00010555, CB-00010684, CB-00010958, IC-IDMA-007, I-CID-WMK-001	