



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	Installation guide Rack mounting brackets Safety guide
--------------------	--

### Physical

Cable length	3.05 m
Colour	Black
Depth	4.6 cm
Height	182.9 cm
Net weight	8.5 kg
Width	5.5 cm

### Input

[In] rated current	24 A
Max line current	30 A
Communication port protocol	SNMP Redfish
Input current limits	30 A
Load capacity	4992 VA
Network frequency	50/60 Hz
Plug standard	NEMA L6-30P
Input voltage	208 V 200 V

### Output

Number of power socket outlets	21 C13/C15 3 C19/C21
--------------------------------	-------------------------

## Conformance

Product certifications	CUL listed FCC part 15 class A PSE
Standards	ICES-003

## Environmental

Ambient air temperature for operation	-5...60 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage altitude	0.00...15240.00 m

## Batteries & Runtime

Communication network type	10/100/1000BASE-T Wi-Fi (optional)
----------------------------	---------------------------------------

## Packing Units

Package 1 Weight	10 kg
Package 1 Height	204 cm
Package 1 width	16.5 cm
Package 1 Length	12.4 cm
Number of Units in Package 3	48

## Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------