



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	Installation guide Rack mounting brackets Safety guide Serial configuration cable
--------------------	--

Physical

Cable length	3.05 m
Colour	Black
Depth	4.6 cm
Height	182.9 cm
Net weight	7.34 kg
Width	5.6 cm

Input

Permissible voltage	220...240 V
Max line current	32 A
Communication port protocol	SNMP Redfish
Input current limits	32 A
Load capacity	7400 VA
Network frequency	50/60 Hz
Plug standard	IEC 60309 32 A 2P + E
Input voltage	200 V 208 V

Output

Number of power socket outlets	21 IEC 60320 C13 3 IEC 60320 C19
--------------------------------	-------------------------------------

Conformance

Product certifications	VDE EAC RCM
Standards	EN 55022 class A EN 55024 EN 61000-3-2 EN 61000-3-3

Environmental

Ambient air temperature for operation	-5...45 °C
Relative humidity	5...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	5...95 %
Storage altitude	0.00...15240.00 m

Batteries & Runtime

Communication network type	10/100/1000BASE-T Wi-Fi (optional)
----------------------------	---------------------------------------

Packing Units

Package 1 Weight	9.95 kg
Package 1 Height	204 cm
Package 1 width	16.5 cm
Package 1 Length	12.4 cm
Number of Units in Package 3	48

Contractual warranty

Warranty	3 years repair or replace
----------	---------------------------