

IMPACT 100 Series

IMPACT SC 30 / SC 60
IMPACT SC 45 USB MS / SC 75 USB MS

Let's start talking

Enjoy more natural-sounding conversations and great quality audio with headsets designed for enterprises introducing Unified Communications. Experience the difference unique EPOS technology can make to your efficiency and well-being. Easy call-handling via in-line call control makes this solution easy and convenient for your entire workforce. In addition, the IMPACT 100 Series provides EPOS Voice™ technology and noise-cancelling microphone for clear communication that boosts productivity.

See more at eposaudio.com/impact-100



Key benefits & features

EPOS Audio technology

For a more natural listening experience and quality sound

EPOS Voice™ technology for speech clarity

Noise-cancelling microphone that filters out ambient noise

Great comfort

Ultra-lightweight headset with comfortable ear pads

Easy Disconnect plug

Simple quick-release mechanism for increased flexibility

Bendable boom arm

For optimal microphone position all day long

EPOS ActiveGard® technology

Protects against sudden sound bursts



IMPACT 100 Series

Product data

General

Product description	IMPACT SC 30 / SC 60: Single or double-sided headset with Easy Disconnect plug
Wearing style	IMPACT SC 30 / SC 60: Headband IMPACT SC 45 USB MS / SC 75 USB MS: Headband – single and double-sided variants.
Color	IMPACT SC 30 / SC 60: Black with silver IMPACT SC 45 USB MS / SC 75 USB MS: Black leatherette padding on headband and ear pad/s cover/s
Headset weight	IMPACT SC 30 / SC 60: Single-sided: 42 g / 1.48 oz Double-sided: 66 g / 2.33 oz IMPACT SC 45 USB MS / SC 75 USB MS: Single-sided: 102 g / 3.6 oz Double-sided: 130 g / 4.59 oz
Warranty	2 years

Audio

EPOS Voice™ technology	IMPACT SC 30 / SC 60: For a clear and natural listening experience
Microphone	Noise-cancelling microphone for optimal speech transmission
Microphone frequency response	IMPACT SC 30 / SC 60: 100 – 10,000 Hz IMPACT SC 45 USB MS / SC 75 USB MS: 150 – 6,800 Hz (Wideband)

Speaker type	IMPACT SC 30 / SC 60: Neodymium magnet speaker IMPACT SC 45 USB MS / SC 75 USB MS: High-quality neodymium magnet speaker
Speaker frequency response	IMPACT SC 30 / SC 60: 50 – 10,000 Hz IMPACT SC 45 USB MS / SC 75 USB MS: 60 – 16,000 Hz (Wideband)
Sound pressure	IMPACT SC 30 / SC 60: Limited by EPOS ActiveGard®: SC 30 – Max 117 dB SC 60 – Max 113 dB IMPACT SC 30 USB ML / SC 60 USB ML: Max 113 dB limited by EPOS ActiveGard® on USB interface Max 118 dB limited by EPOS ActiveGard® on 3.5 mm interface
Optimized for communication & multimedia*	Sound enhancement profiles adjust automatically for optimal communication or multimedia

Call management

In-line call control	Answer/end call, volume up/down, microphone mute and redial last outgoing call
----------------------	--

Hearing Protection

EPOS ActiveGard® technology	Protects users against acoustic injury caused by sudden sound burst on the line
EU Noise at Work limiter**	Enhanced audio protection preventing listening fatigue, average 85 dB over a work day

IMPACT 100 Series

Product data

Content of delivery

What's in the box-headset	IMPACT SC 30 / SC 60: Headset, quick guide, safety guide IMPACT SC 45 USB MS / SC 75 USB MS: Headset with 3.5 mm jack, foam ear pad/s and leatherette cover/s, detachable USB cable with in-line call control, carry pouch, printed quick guide, printed safety guide
---------------------------	--

Software

EPOS Connect	Remote call control, firmware updates and settings: eposaudio.com/software-epos-connect
PC Software	For other relevant PC software, please check: eposaudio.com/software
EPOS Manager	Manage, update and configure your EPOS audio devices from one location: eposaudio.com/software-epos-manager
UC compatible	Yes. For more information please go to: eposaudio.com/compatibility

* Available when the headset is connected via USB

** Noise at Work: The EU's "Noise at Work Directive" (2003/10/EC) sets limits for two types of noise in the workplace: Acoustic burst and Sustained Noise.

IMPACT 100 Series

Additional benefits & features

Optimized for communication and multimedia

With automatic sound-enhancement profiles

Optimal speech transmission

Bendable boom arm ensures optimal microphone position

Protects your hearing

From acoustic shock with EPOS ActiveGard® technology




Switchable Noise at Work limiter

In compliance with EU Noise at Work Directive
(Directive 2003/10/EC)

Easy to store and transport

With protective carry pouch

Product overview

Connects to	Product	Description	Details	EAN / UPC code
Desk phone 	SC 30 Art. no. 1000550	Single-sided headset w. Easy Disconnect plug		EAN: 57 14708 00351 9 UPC: 8 40064 40351 1
	SC 60 Art. no. 1000551	Double-sided headset w. Easy Disconnect plug		EAN: 57 14708 00352 6 UPC: 8 40064 40352 8
PC via USB Smartphone & tablet via 3.5 mm jack  	SC 45 USB MS Art. no. 1000634	Single-sided, 3.5 mm jack and USB	Microsoft Teams Certified*	EAN: 57 14708 00435 6 UPC: 8 40064 40435 8
	SC 75 USB MS Art. no. 1000635	Double-sided, 3.5 mm jack and USB	Microsoft Teams Certified*	EAN: 57 14708 00436 3 UPC: 8 40064 40436 5

* The Microsoft Teams certified products in the IMPACT SC 40/70 series require installation of EPOS Connect
- download the software from our website: eposaudio.com/epos-connect

