

## MB2236i

### Small. Easy to use. Great value.

With monochrome output up to 36 pages per minute\* and standard two-sided printing, the Lexmark MB2236i offers impressive performance and valuable extras. Standard Wi-Fi enhances connectivity, front-panel USB makes printing easier, and touch screen with Cloud Connector lets users integrate their printing and scanning with popular cloud services.



### Get more done

- ▶ Print up to 36 pages per minute\*, and scan up to 25 pages per minute.
- ▶ Tackle your printing workload with the power of a 1-GHz processor and 512 MB of memory.
- ▶ Unison™ Toner replacement cartridges deliver up to 6,000 pages\*\* of high-quality printing.
- ▶ Load and print up to 250 pages without refilling, or manual-feed single sheets.
- ▶ Send and receive faxes with available cloud fax\*\*\*.
- ▶ Use media sizes from A6 to legal in the paper tray, plus smaller media and envelopes in the multipurpose feeder.

### The right fit

- ▶ Compact dimensions of only 16.4 inches wide, 14.2 inches deep, and 13.9 inches tall (41.5 cm wide x 36 cm deep x 35.2 cm tall) helps it fit almost anywhere.
- ▶ Standard Wi-Fi supports desktop and mobile devices, and complements the MFP's ethernet and USB connections.

- ▶ Bright 2.8-inch (7.2-cm) color touch screen adds convenience and offers embedded workflow capabilities, including Lexmark's own Cloud Connector.
- ▶ Direct-print front-panel USB port makes it even easier to get things done.

### Robust, built-in security

- ▶ Lexmark's full-spectrum security architecture helps keep your information safe—on the document, the device, over the network, and everywhere in between.
- ▶ A range of embedded features harden device against attacks.

### Built for planet earth

- ▶ Energy management features reduce power consumption in active use or sleep mode.
- ▶ Standard two-sided printing saves paper.
- ▶ Recycle cartridges through the award-winning Lexmark Cartridge Collection Program (LCCP).



\* Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: [www.lexmark.com/ISOspeeds](http://www.lexmark.com/ISOspeeds).

\*\* Average continuous mono declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19752. Actual yield will vary considerably based upon many factors. See [www.lexmark.com/yields](http://www.lexmark.com/yields) for more information.

\*\*\* Subject to subscription with etherFAX®. A trial package (up to 3 months or 300 pages, whichever comes first) is included free of subscription charge; other fees, such as telecommunication charges, may apply. Contact etherFAX ([www.etherfax.net](http://www.etherfax.net)) for details. Trial may be withdrawn without notice. Service may not be available in all locations. Analog faxing via phone line is not supported by this device.

Product Specifications		Lexmark MB2236i
<b>Printing</b>		
Display	2.8 inch (7.2 cm) LCD touch panel	
Print Speed	Up to: Black: 36 ppm <sup>1</sup> (Letter)	
Time to First Page	As fast as: Black: 7.9 seconds	
Print Resolution	Black: 2400 IQ (2400 x 600 dpi), 300 x 300 dpi, 600 x 600 dpi, 1200 IQ (1200 x 600 dpi)	
Memory	Standard: 512 MB / Maximum: 512 MB	
Hard Disk	Not Available	
Recommended Monthly Page Volume	250 - 2500 pages <sup>2</sup>	
Maximum Monthly Duty Cycle	Up to: 30000 pages per month <sup>3</sup>	
<b>Copying</b>		
Copy Speed	Up to: Black: 36 cpm <sup>1</sup> (Letter)	
Time to First Copy	As fast as: Black: 8.5 seconds	
<b>Scanning</b>		
Scanner Type / ADF Scan	Flatbed scanner with ADF / Simplex	
A4/Ltr Simplex Scan Speed	Up to: Black: 23 / 25 sides per minute / Color: 7 / 8 sides per minute	
ADF Paper Input Capacity	Up to: 50 pages 20 lb or 75 gsm bond	
<b>Supplies<sup>4</sup></b>		
Laser Cartridge Yields	up to: 1,200 <sup>5</sup> -page Cartridge / up to: 3,000 <sup>5</sup> -page High Yield Cartridge / up to: 6,000 <sup>5</sup> -page Extra High Yield Cartridge	
Imaging Unit Estimated Yield	Up to: 12000 pages, based on 3 average letter/A4-size pages per print job and ~ 5% coverage <sup>6</sup>	
Cartridge(s) Shipping with Product	700 <sup>5</sup> -page Black Return Program Toner Cartridges	
<b>Paper Handling</b>		
Included Paper Handling	Integrated Duplex, Single-Sheet Manual Feed, 150-Sheet Output Bin, 250-Sheet Input	
Paper Input Capacity	Up to: Standard: 251 pages 20 lb or 75 gsm bond / Maximum: 251 pages 20 lb or 75 gsm bond	
Paper Output Capacity	Up to: Standard: 150 pages 20 lb or 75 gsm bond / Maximum: 150 pages 20 lb or 75 gsm bond	
Media Types Supported	Paper Labels, Card Stock, Plain Paper, Envelopes, Refer to the Paper & Specialty Media Guide	
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope	
<b>General Information<sup>7</sup></b>		
Standard Ports	Front USB 2.0 Specification Hi-Speed Certified port (Type A), 802.11b/g/n Wireless, USB 2.0 Specification Hi-Speed Certified (Type B), Ethernet 10/100BaseTX (RJ-45)	
Noise Level	Operating: 52 dBA (Print) / 55 dBA (Copy) / 52 dBA (Scan)	
Specified Operating Environment	Temperature: 10 to 32°C (50 to 90°F) / Altitude: 0 - 2896 Meters (9,500 Feet) / Humidity: 15 to 80% Relative Humidity	
Limited Warranty	See Statement of Limited Warranty: 1-Year Advanced Exchange	
Size / Weight	H x W x D: 13.9 x 16.4 x 14.2 in. / 22 lb.	
ENERGY STAR Typical Electricity Consumption	TEC: 0.53 kilowatt-hours per week	

All information is subject to change without notice. Lexmark is not liable for any errors or omissions.

<sup>1</sup> Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: [www.lexmark.com/ISOspeeds](http://www.lexmark.com/ISOspeeds).

<sup>2</sup> "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. <sup>3</sup> "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. <sup>4</sup> Product functions only with replacement cartridges designed for use in a specific geographical region. See [www.lexmark.com/regions](http://www.lexmark.com/regions) for more details. <sup>5</sup> Average standard page yield value declared in accordance with ISO/IEC 19752. <sup>6</sup> Actual Yield may vary based on other factors such as device speed, paper size and feed orientation, toner coverage, tray source, percentage of black-only printing and average print job complexity. <sup>7</sup> Printers are sold subject to certain license/agreement conditions. See [www.lexmark.com/printerlicense](http://www.lexmark.com/printerlicense) for details.

© 2021 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. AirPrint and the AirPrint Logo are trademarks of Apple, Inc. Mopria®, the Mopria® Logo™ and the Mopria® Alliance logos are registered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. All other trademarks are the property of their respective owners. This product includes software developed by the OpenSSL Project for use in the Open SSL Toolkit (<http://www.openssl.org/>).

