



V7 Bluetooth® Wireless Mono Headset

HB605M

SKU: 7FL291

Enjoy superior wireless connectivity with V7's H605M Bluetooth® Wireless Mono Headset. With a range of up to 30 meters or 100 feet, you can walk away from your desk without the hassle for dropped connections. Wirelessly connect the H605M via Bluetooth (Includes a USB dongle for PC connectivity) to your PC or smartphone to experience amazing clarity for conference calls with Microsoft Teams, Zoom, Google Meet and other popular conferencing programs. Our mono headset is lightweight, built for all-day comfort, includes on-headset controls and an impressive 30-meter (100') range, V7's wireless headsets are perfect choice to enhance your workplace efficiency.

- Bluetooth v5.0
- Up to 18 Hours Talk-time; 175 Hours Standby
- Detachable Boom Microphone
- Includes V7 Link Audio Bluetooth v5.0 USB Dongle
- USB-C Connector for Charging
- Designed for Windows 10, macOS, iOS and Android devices
- Optional Charging Cradle Available

General

Sku: 7FL291
 Model: HB605M
 EAN: 0662919107722
 Warranty: 2 years
 Compliance: BQB, CE, FCC, RoHS
 Country Of Origin: China
 Package Type: 4 Color Box
 Package Includes: Headset, Detachable Boom Mic, USB Dongle, USB Charging Cable, 3.5mm AUX Cable, Storage Bag, User's Guide, Warranty and Compliance document

Color

Color: Black
 Accent Color: Gray

Design

Audio Segment: Bluetooth Wireless
 Headset Form Factor: On Ear
 Controls: Power, Pairing, Volume, Mute, Call Answer, End

Package Dimensions

Package Dimensions (L/W/H): 206 x 186 x 55mm
 (8.11 x 7.32 x 2.17")
 Package Weight: 296.7g (10.5 oz)

Product Dimensions

Product Dim (L/W/H): 158.8 x 186.7 x 71.1mm (6.25 x 7.35 x 2.8")
 Product Weight: 144.3g (5.09 oz)

California Prop 65

No warning required

Technical

Connectivity: Bluetooth
 Decibels: 101 dB ±3
 Impedance: 32 ohms
 Driver Size: 30mm
 Mic Sensitivity: -42 db ±3



Specifications

Battery type: Lithium Polymer (350mAh)

Speaker sensitivity: 99dB±3dB

Speaker max input power: 80mW

Speaker frequency range: 20Hz-20000Hz

Speaker bandwidth-Music mode: 20Hz-20000Hz

Speaker bandwidth-Speak mode: 100Hz-10000Hz

Microphone type: Omnidirectional Microphone

Microphone frequency range: 100Hz-10000Hz

Audio Codecs supported: SBC

Music time: Up to 18 hours

Talk time: Up to 18 hours

Charging time: About 3 hours

Power consumption: 310mA

Connection: Bluetooth, Bluetooth Dongle, 3.5 Analog AUX

Bluetooth version: V5.0

Bluetooth profiles: A2DPv1.3.1, AVRCPv1.6, HFPv1.7, HSPv1.2, SPP v1.2, DID v1.3, HID v1.1, PXP v1.0.1, FMP v1.0, BAS v1.0

Operating range: Up to 30m line of site

Bluetooth pairing list: 8

Simultaneous Bluetooth connections: 2