



V7 Wireless Bluetooth Stereo Active Noise Cancelling Headphones

HB800ANC

SKU: CA60866

Clear away the noise and distractions with V7's Bluetooth Wireless headphones. Our noise cancelling technology improves enjoyment of music, allows for deeper concentration of work, or whatever needs your focus. That's the benefit of the HB800 Bluetooth Wireless headphones, they're designed with hybrid ANC technology to continuously monitor and measure outside noise and reduce it with an opposing signal. You can also adjust the noise cancellation level to better fit your environment so you can work and concentrate without distraction.

- Hybrid Digital Active Noise Cancelling Technology
- Bluetooth Version 5.0
- Clear, balanced audio performance at any volume, and includes a noise-cancelling microphone for your important calls
- Up to 26 hours operating time; 23 hours (BT + ANC)
- Supports Mobile Voice Assistants with a touch of a button
- Soft, luxurious headband and earpads for comfortable all-day use
- Foldable for easy transport & storage

General

Sku: CA60866
 Model: HB800ANC
 EAN: 0662919111545
 Warranty: 2 years
 Compliance: BQB, CE, FCC, RoHS
 Country Of Origin: China
 Package Type: 4 Color Box
 SAP: 5047799

Package Includes: Headphones, AUX audio cable, USB-C charging cable, Storage bag, User's guide, Warranty & compliance documents

Color

Color: Black

Design

Headset Form Factor: Over the Ear
 Controls: Volume, ANC, Power, Call Answer/End, Track Advance/Repeat, Pause

Package Dimensions

Package Dimensions (L/W/H): 230 x 195 x 70mm
 (9.06" x 7.67" x 2.76")
 Package Weight: 550g (19.4 oz)

Product Dimensions

Product Dim (L/W/H): 155 x 80 x 205mm (6.1 x 3.15 x 8.07")
 Product Weight: 280g (9.88 oz)

Technical

Connectivity: Bluetooth
 Decibels: 120 ± 3 dB @ 1KHz
 Impedance: 32Ω +/- 15%
 Driver Size: 40mm



Specifications

Bluetooth

Version v5.0

Operating distance 15m (49")

Transmission Range (Hz) 2402-2480 MHz

Active Noise Cancellation (ANC)

ANC effect: 30 +/- 2 dB

Sensitivity -35 +/- 1 dB

Speaker

Diameter Φ 40 +/- 0.3 mm

Frequency Response 20Hz-20KHz

Rated Power 10mW

Battery

Type ReChargeable Li-ion Battery

Capacity 500 mAh

Operating time 26 hours (Bluetooth @ 85% volume) 23 hours (Bluetooth and ANC @ 85% volume)

Charge time 0.8-1 hours

Charge current 1.5A, 5V

Charging Cable

USB type Type C connector

Length 0.8 m (31.5")

Audio Cable

Type 3.5mm TRS Stereo cable

Length 1.2 m (47.2")