

CHERRY STREAM DESKTOP



Wireless Desktop



Image: STREAM DESKTOP – JD-8500EU-0



Image: STREAM DESKTOP – JD-8500EU-2



Models may vary from the image shown

The best STREAM ever - now with wireless freedom and mouse

The STREAM DESKTOP is the logical next step in the evolution of the STREAM family: It combines all the features of the popular STREAM KEYBOARD with wireless 2.4 GHz freedom and a perfectly matched six-button mouse.

The in-house SX scissor technology means that the STREAM DESKTOP is precise and quiet when you type, properties we kept in mind when designing the mouse. Just like the super silent strokes of the keyboard, the mouse will inspire you with its almost inaudibly quiet buttons. That is why the newest member of the STREAM family is the perfect addition to your quiet workspace.

Visually, the popular STREAM KEYBOARD and the new wireless version are cut from the same cloth. Why change something that is already perfect? The simple, yet elegant design means that there is something for everyone - both in the office and at home. And the mouse is the ideal companion. Its shape and size are designed for optimal comfort in both medium and large hands.

If you value ease of use, STREAM DESKTOP is right for you. The mouse and keyboard are ideally matched. The forward and back buttons on the side of the mouse prove to be indispensable in any number of daily tasks. And this dynamic duo can be perfectly adapted to your needs: The mouse resolution has three settings up to 2,400 dpi, and the keyboard has ten office and multimedia keys.

The only way you can have more flexibility is by using the free CHERRY KEYS software. You can download them from www.cherry.de. With CHERRY KEYS, in just a few clicks you can configure your keyboard and mouse to perfectly suit your individual needs.

And nothing beats the convenience of the LEDs built into various keys. They let you know when the Caps Lock, Scroll Lock or Num Lock keys on the keyboard have been activated. In addition, the LEDs flash when you need to change batteries. However, this is a rare occurrence with the STREAM DESKTOP. With up to 36 months of battery life, this set is particularly tenacious.

We took great care to ensure maximum stability in the wireless set. The keyboard has eight rubber pads on the back, rubberized feet and an integrated metal plate. And the mouse feels sturdy and secure in your hand. Thanks to its optimized sliding characteristics, even the most demanding users will get their money's worth.

In working environments in particular, it is of the utmost importance to comply with guidelines, quality standards and environmental goals. The desktop set bears the GS seal "Tested Safety," which means it complies with all relevant European directives and regulations on safety and ergonomics. With the "Blauer Engel" award, the STREAM DESKTOP makes a positive contribution and offers a responsible approach to our environment.

The STREAM DESKTOP is a versatile addition to your workspace – it is solid, resilient, adaptable, durable and stylish. It unites all the beloved features of the STREAM in a 2.4 GHz wireless desktop and is the perfect choice for both professional and home use.

Key benefits

Maximum productivity:

- Extremely quiet keystrokes
- CHERRY SX scissor mechanism
- Quiet mouse buttons
- 3-level adjustable mouse sensor with up to 2400 dpi

Highest quality:

- Rubberized feet for perfect slip resistance
- Integrated metal plate for maximum torsional rigidity
- „Blauer Engel“ ecolabel
- Durable key lettering
- Keyboard with AES-128 encryption

Optimum operating comfort:

- Battery life up to 36 months (keyboard: 36 months, mouse: 12 months)
- Status LEDs show low battery charge and mouse resolution
- Keyboard with integrated status LEDs for the CAPS LOCK, NUM and SCROLL keys
- Keyboard with 10 office & multimedia keys
- 6 mouse buttons and scroll wheel

Very latest design:

- Flat overall height
- GS approval (full size layout)
- Perfectly coordinated design

Technical Data

Layout (country or language):

Product dependant, see table "Models"

Housing color:

Product dependant, see table "Models"

Weight (product):

Keyboard: approx. 925 g / 2.04 lb (with Batterie)

Mouse: approx. 115 g / 0.25 lb (with Batterie)

Receiver: approx. 3 g

Total weight (with packaging):

approx. 1.360 g / 3.00 lb

Transmission range:

approx. 10 m / 10.94 yd

Frequency range:

2.400 GHz - 2.4835 GHz (frequency)

Effective radiated power: max. 10 mW [EIRP]

Storage temperature:

--20 °C to 60 °C / -4° F to 140° F, max. 85 % humidity

Operating temperature:

0 °C to 40 °C / 32° F to 104° F, max. 85 % humidity

Current consumption:

Keyboard: max. 20 mA

Mouse: max. 20 mA

Receiver: max. 20 mA

Interface:

USB

Reliability:

MTBF > 80.000 hours

Product approvals:

- CE
- UKCA
- FCC
- cULus
- Blauer Engel (only for keyboard)
- VDE-GS
- Windows Hardware Compatibility

System requirements:

- USB port (Type A)
- Windows 7, 8, 10, 11

Delivery volume:

- Keyboard
- Mouse
- Batteries for Keyboard (2 x AA) and Mouse (1 X AA)
- Nano-USB-Receiver
- Operating instruction
- Warranty

Technical Data (continued)

Dimensions product:

Keyboard:

approx. 462,2 x 162,2 x 23,1 mm / 18.20 x 6.39 x 0.90 in

approx. 462,2 x 165,8 x 34,1 mm / 18.20 x 6.53 x 1.34 in (with feet up)

Mouse: approx. 116 x 64,7 x 37,7 mm / 4.57 x .55 x 1.48 in

Receiver: approx. 19 x 14,5 x 6,5 mm / 0.75 x 0.58 x 0.26 in

Packaging dimensions:

Single carton: approx. 560 x 186 x 48 mm / 22.05 x 7.32 x 1.89 in

Master carton: 585 x 490 x 210 mm / 23.03 x 19.29 x 8,27 in

Mouse:

- Design: symmetrical
- Scanning: Optical Sensor (PixArt)
- Resolution: 1000 dpi / 1600 dpi / 2400 dpi (adjustable)
- Number of buttons: 6
- Model of buttons: Silent click
- Function buttons: Right/Left-click, Scroll wheel; Browser forward; Browser back, DPI-switch
- Mouse wheel design: Scroll wheel with key function
- Status LED: DPI, battery status
- Housing color: Product dependant, see table "Models"
- Key color: Product dependant, see table "Models"

Keyboard:

- Fullsize layout with numeric pad
- Key technology: CHERRY SX scissor mechanism
- Service life, standard key: > 20 million key operations
- Anti-slip feet 8 pieces (18 x 4 mm / 0.71 x 0.16 in)
- Status-LED: Caps Lock, scroll- and Num-key
Battery status (via Status LED in the scroll key)
- Number of additional keys: 10
- Additional keys function: Volume up, Mute, Volume down, Previous title, Next title, Play/pause, Windows Lock, Browser, E-Mail program, Calculator
- Housing color: Product dependant, see table "Models"
- Key color: Product dependant, see table "Models"

Packaging Unit:

Number of products in the master carton: 10

Number of master packages per pallet: 12

Warranty

We put a lot of dedication and hard work into the development of our products and we are proud of their quality. This is why, in addition to the statutory guarantee mentioned in the operating instructions, we are granting an expanded manufacturer's guarantee that is subject to the conditions stated below.

For the first two years after delivery, the statutory warranty applies. In the third year after delivery, CHERRY voluntarily grants an additional warranty according to the following conditions ("extended warranty"). In the event of a defect, please contact the seller of your CHERRY product. Do not carry out any repairs on your own and do not open the product. There is no warranty if unauthorized changes to the product cause a defect.

Conditions for the extended warranty

In the case of a defect after the first 2 years after delivery of the CHERRY product, CHERRY grants its customers for the additional period of one year the right to assert claims for cure, i.e. demand that the defect is remedied or a thing free of defects is supplied. The extended warranty is to be asserted against the seller of the CHERRY product upon presentation of the original invoice, proof of purchase or a comparable proof of the time of purchase.

CHERRY, and the seller of the CHERRY product, where applicable, shall remedy the defect in the event the customer has justified claims for cure under the terms of the extended warranty.

Excluded from the extended warranty are damages caused by improper use, in particular by the effects of chemical substances, other damages caused by external influences, as well as normal wear and tear and optical changes, in particular discoloration or abrasion of shiny areas. Also excluded from the extended warranty are accessories and other parts which are not an integral part of the purchased item.

Errors, technical changes and delivery possibilities excepted.
Technical information refers only to the specifications of the products. Features may differ from the information provided.

CHERRY STREAM DESKTOP

Wireless Desktop



Models:

(possible country/layout versions, others available on request)



Image: STREAM DESKTOP – JD-8500GB-0

JD-8500xx-0 (pale grey)

	Product name	Order number	EAN code	Layout (country or language)	Keyboard Housing color	Number of keys	Mouse Housing color
1	CHERRY STREAM DESKTOP	JD-8500BE-0	4025112090899	Belgium	pale grey	105 + 10	pale grey
2	CHERRY STREAM DESKTOP	JD-8500CH-0	4025112090837	Switzerland	pale grey	105 + 10	pale grey
3	CHERRY STREAM DESKTOP	JD-8500DE-0	4025112090738	Germany	pale grey	105 + 10	pale grey
4	CHERRY STREAM DESKTOP	JD-8500ES-0	4025112090813	Spain	pale grey	105 + 10	pale grey
5	CHERRY STREAM DESKTOP	JD-8500EU-0	4025112090790	US English with EURO symbol	pale grey	104 + 10	pale grey
6	CHERRY STREAM DESKTOP	JD-8500FR-0	4025112090752	France	pale grey	105 + 10	pale grey
7	CHERRY STREAM DESKTOP	JD-8500GB-0	4025112090776	UK	pale grey	105 + 10	pale grey
8	CHERRY STREAM DESKTOP	JD-8500IT-0	4025112090875	Italy	pale grey	105 + 10	pale grey
9	CHERRY STREAM DESKTOP	JD-8500PN-0	4025112090851	Pan-Nordic	pale grey	105 + 10	pale grey
10	CHERRY STREAM DESKTOP	JD-8500CN-0	4025112096372	US/CN-Layout	pale grey	104 + 10	pale grey

Please contact your local CHERRY service and support teams or sales partners for layouts available in your country.

CHERRY STREAM DESKTOP

Wireless Desktop



Models:

(possible country/layout versions, others available on request)



Image: STREAM DESKTOP – JD-8500GB-2

JD-8500xx-2 (black)

	Product name	Order number	EAN code	Layout (country or language)	Keyboard Housing color	Number of keys	Mouse Housing color
1	CHERRY STREAM DESKTOP	JD-8500BE-2	4025112090905	Belgium	Black	105 + 10	Black
2	CHERRY STREAM DESKTOP	JD-8500CH-2	4025112090844	Switzerland	Black	105 + 10	Black
3	CHERRY STREAM DESKTOP	JD-8500DE-2	4025112090745	Germany	Black	105 + 10	Black
4	CHERRY STREAM DESKTOP	JD-8500ES-2	4025112090820	Spain	Black	105 + 10	Black
5	CHERRY STREAM DESKTOP	JD-8500EU-2	4025112090806	US English with EURO symbol	Black	104 + 10	Black
6	CHERRY STREAM DESKTOP	JD-8500FR-2	4025112090769	France	Black	105 + 10	Black
7	CHERRY STREAM DESKTOP	JD-8500GB-2	4025112090783	UK	Black	105 + 10	Black
8	CHERRY STREAM DESKTOP	JD-8500IT-2	4025112090882	Italy	Black	105 + 10	Black
9	CHERRY STREAM DESKTOP	JD-8500PN-2	4025112090868	Pan-Nordic	Black	105 + 10	Black
10	CHERRY STREAM DESKTOP	JD-8500CN-2	4025112096396	US/CN-Layout	Black	104 + 10	Black

Please contact your local CHERRY service and support teams or sales partners for layouts available in your country.