

Lexmark MC3224i

Small. Dependable. Secure.

Compact and lightweight, the Lexmark MC3224i multifunction brings color printing, scanning, copying, available cloud faxing* and touch-screen convenience to small workgroups. It offers color output at up to 24 pages per minute** in a package that fits almost anywhere. There's Wi-Fi to support mobile users and Lexmark full-spectrum security is built in.



Compact color versatility

- ▶ Get color output at up to 24 pages per minute**, plus automatic-feed single-side scanning and available cloud faxing*.
- ▶ Tackle your printing workload with the power of a 1-GHz processor and 512 MB of memory.
- ▶ Connect via standard Wi-Fi, ethernet and USB.
- ▶ Simplify mobile printing via Lexmark Mobile Print app, as well as Mopria® and AirPrint technologies.
- ▶ 2.8-inch (7.2 cm) touch screen offers built-in workflow capabilities like scan to network, scan to email and Lexmark's own Cloud Connector.

Easy to set up, easy to keep going

- ▶ Compact dimensions of 13.6 inches high x 16.2 inches wide x 15.5 inches deep (344.4 mm high x 411.2 mm wide x 394.1 mm deep) helps it fit almost anywhere.

- ▶ Unison™ Toner replacement cartridges deliver up to 1500 pages*** of high-quality output.
- ▶ Steel frame and lifetime imaging components mean long life and minimal maintenance.

Robust, built-in security

- ▶ Lexmark's full-spectrum security architecture helps keep your information safe—on the document, the device, over the network, and everywhere in between.

Built for planet earth

- ▶ Built-in energy-saving mode goes from sleep to print to sleep with nothing to set.
- ▶ Printer is rated EPEAT® Silver**** and is ENERGY STAR® certified.
- ▶ Recycle cartridges through the award-winning Lexmark Cartridge Collection Program (LCCP).



* Subject to subscription with etherFAX®. A trial package (up to 3 months or 300 pages, whichever comes first) is included free of subscription charge; other fees, such as telecommunication charges, may apply. Contact etherFAX (www.etherfax.net) for details. Trial may be withdrawn without notice. Service may not be available in all locations. Analog faxing via phone line is not supported by this device.

** Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds.

*** Average continuous black or continuous composite color (CMY) declared yield in one-sided (simplex) mode up to this number of pages in accordance with ISO/IEC 19798. Actual yield will vary considerably based upon many factors. See www.lexmark.com/yields for more information.

**** EPEAT ratings may vary by location See www.epeat.net for registration status by country.

Product Specifications		Lexmark MC3224i
Printing		
Display	2.8 inch (7.2 cm) LCD touch panel	
Print Speed	Up to: Black: 24 ppm ¹ (Letter) / Color: 24 ppm ¹ (Letter)	
Time to First Page	As fast as: Black: 11 seconds / Color: 11 seconds	
Print Resolution	Black: 4800 CQ (2400 x 600 dpi), 600 x 600 dpi / Color: 600 x 600 dpi, 4800 CQ (2400 x 600 dpi)	
Memory	Standard: 512 MB / Maximum: 512 MB	
Hard Disk	Not Available	
Recommended Monthly Page Volume	600 - 1500 pages ²	
Maximum Monthly Duty Cycle	Up to: 30000 pages per month ³	
Copying		
Copy Speed	Up to: Black: 24 cpm ¹ (Letter) / Color: 24 cpm ¹ (Letter)	
Time to First Copy	As fast as: Black: 11.2 seconds / Color: 11.2 seconds	
Scanning		
Scanner Type	Flatbed scanner	
Supplies⁴		
Laser Cartridge Yields	up to: 1,500 ⁵ -page Black and Color (CMYK) Cartridges	
Cartridge(s) Shipping with Product	750 ⁵ -page Black Return Program Toner Cartridge, 500 ⁵ -page Color (CMY) Return Program Toner Cartridge	
Paper Handling		
Included Paper Handling	100-Sheet Output Bin, Integrated Duplex, Single-Sheet Manual Feed, 250-Sheet Input	
Paper Input Capacity	Up to: Standard: 250+1 pages 20 lb or 75 gsm bond / Maximum: 250+1 pages 20 lb or 75 gsm bond	
Paper Output Capacity	Up to: Standard: 100 pages 20 lb or 75 gsm bond / Maximum: 100 pages 20 lb or 75 gsm bond	
Media Types Supported	Hagaki Card, Paper Labels, Card Stock, Plain Paper, Glossy Paper, Refer to the Paper & Specialty Media Guide	
Media Sizes Supported	A6, Oficio, 7 3/4 Envelope, 9 Envelope, JIS-B5, A4, Legal, A5, Hagaki Card, Letter, B5 Envelope, Statement, C5 Envelope, Executive, Universal, DL Envelope, Folio, 10 Envelope	
General Information⁶		
Standard Ports	802.11b/g/n Wireless, USB 2.0 Specification Hi-Speed Certified (Type B), Ethernet 10/100BaseTX (RJ-45)	
Noise Level	Operating: 49 dBA (Print) / 49 dBA (Copy) / 40 dBA (Scan)	
Specified Operating Environment	Humidity: 8 to 80% Relative Humidity / Altitude: 0 - 3048 Meters (10,000 Feet) / Temperature: 10 to 32°C (50 to 90°F)	
Limited Warranty	See Statement of Limited Warranty: 1- Year Onsite Repair, Next Business Day	
Size / Weight	H x W x D: 12.1 x 16.2 x 15.5 in. / 40.2 lb.	
ENERGY STAR Typical Electricity Consumption	TEC: 0.34 kilowatt-hours per week	

All information is subject to change without notice. Lexmark is not liable for any errors or omissions.

¹ Print and copy speeds measured in accordance with ISO/IEC 24734 and ISO/IEC 24735 respectively (ESAT). For more information see: www.lexmark.com/ISOspeeds.

² "Recommended Monthly Page Volume" is a range of pages that helps customers evaluate Lexmark's product offerings based on the average number of pages customers plan to print on the device each month. Lexmark recommends that the number of pages per month be within the stated range for optimum device performance, based on factors including: supplies replacement intervals, paper loading intervals, speed, and typical customer usage. ³ "Maximum Monthly Duty Cycle" is defined as the maximum number of pages a device could deliver in a month using a multishift operation. This metric provides a comparison of robustness in relation to other Lexmark printers and MFPs. ⁴ Product functions only with replacement cartridges designed for use in a specific geographical region. See www.lexmark.com/regions for more details. ⁵ Average continuous cartridge yield is stated number of standard pages as listed. Declared yield value in accordance with ISO/IEC 19798. ⁶ Printers are sold subject to certain license/agreement conditions. See www.lexmark.com/printerlicense for details.

© 2021 Lexmark. All rights reserved.

Lexmark, the Lexmark logo and Unison are trademarks of Lexmark International, Inc., registered in the United States and/or other countries. AirPrint and the AirPrint Logo are trademarks of Apple, Inc. Mopria®, the Mopria® Logo™ and the Mopria® Alliance logos are registered trademarks and service marks of Mopria Alliance, Inc. in the United States and other countries. Unauthorized use is strictly prohibited. All other trademarks are the property of their respective owners. This product includes software developed by the OpenSSL Project for use in the Open SSL Toolkit (<http://www.openssl.org/>).

