


CyberTrack C100

4K Ultra HD Conference Webcam with Built-In 5W Speaker and Dual Microphone, Adjustable Viewing Angle 90-150 Degree, Mount Adapter and Remote Control



Adesso's CyberTrack C100 is a 4K Ultra HD conference webcam with 4X zoom, adjustable viewing angles and manual focus. The 4K True Color High-Definition video processing allows you to record and share vivid Ultra HD quality video. This webcam includes integrated dual microphones that let your voice be heard loud and clear, whether you are chatting with loved ones or conducting a business video conference. The CyberTrack C100 also features a tripod-ready clip for additional placement options.



■ 4K Ultra High Definition Video Resolution

The CyberTrack C100 lets your audience feel like they are in the room with you with 4K True Color Ultra HD Video. Equipped with conferencing camera for business meetings, you'll feel like you're face-to-face in the same room.

■ 8 MP CMOS Sensor with Manual Focus

This webcam features a true 8MP CMOS image sensor that provides crisp, colorful and clear HD quality video and 30FPS at maximum resolution.

■ Infrared Remote Control

Includes a highly sensitive infrared remote control.

■ Multiple Mounting Positions

The C100 webcam can be mounted to the wall, TV and display monitor. Also comes with a tripod-ready clip, for additional placement options.

Specifications:

Interface:	USB
Image Sensor:	8 MP CMOS Sensor
Resolution:	3840 x 2160
Focus:	Manual Focus
Max Frame Rate:	30 FPS
Speaker :	5W
Optical Zoom :	4X
Viewangle:	90°/105°/120°/135°/150°
Data Format:	UY2, MJPG
Dynamic Range:	HDR
Features:	Saturation, Contrast, Acutance, White Balance, Exposure
Dimensions:	5.9x3.15x2.56 " (150 x 80 x 65mm)
Weight :	9.6 oz (270g)

Requirements:

Operating System	Windows® 10/8/7/Vista Mac® OS X 10.6 Android
Connectivity Interface	USB port

Includes:

Adesso CyberTrack C100

Shipping Information:

Item	UPC Code	Package Dimensions	Package Weight	Qty/Carton
CyberTrack C100	783750011068	7.0" x 6.0" x 2.25"	0.18 lb.	20/80

