

ThinkVision S24e-20 62AEKAR2US

Product

ThinkVision S24e-20

Machine Type

62AE

Region

NA, LA

Display Size

23.8"

View Area

527.04x296.46 mm

Panel

Vertical Alignment

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.2745x0.2745 mm

Dot / Pixel Per Inch

93 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

4 ms (Extreme mode) / 6 ms (normal mode)

Refresh Rate

60 Hz

Brightness

250 nits

Contrast Ratio

3000:1

Color Gamut

72% NTSC

Multiple Input

HDMI, VGA

USB Port

None

Camera

None

Speaker

None

Power Consumption (Typical / Maximum)

17.5W / 23.5W

Power Adapter

Integrated

Stand

Tilt Stand

Color

Raven Black

Side Bezel Width

2.5 mm

Dimensions with Stand (HxWxD)

434.5x540.4x173.1 mm

Weight (Including Stand)

8.42 lb / 3.82kg

Monitor Cable

HDMI

ENERGY STAR

Yes

TCO

TCO 8.0

EPEAT

Silver

Low Blue Light / Eye Comfort / Eyesafe Display

Eye Comfort

Base Warranty

3-year

Operating System Support

Support Windows 7, Windows 10

Sync Technology

AMD FreeSync

CPU / Platform

None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

EAN / UPC / JAN

0195348151344

Announce Date

2021-01-14

 WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors.

Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2021. All rights reserved.



Lenovo™

ThinkVision S24e-20

DISPLAY

Panel Size

23.8-inch

Screen Dimensions

531.73 mm x 340.80 mm

Panel Type

3-side NearEdgeless, VA

Active Area

527.04 mm x 296.46 mm

Backlight

WLED

Aspect Ratio

16:9

Resolution

1920 x 1080

Pixel Pitch

0.2745 x 0.2745 mm

Dot/Pixel Per Inch (DPI/PPI)

93

Viewing Angle (H x V @ CR 10:1)

178° / 178°

Response Time

4ms (Extreme Mode)

6ms (Normal Mode)

Refresh Rate

60 Hz

Brightness (typical)

250 cd/m²

Contrast Ratio (typical)

3000:1

Dynamic Contrast Ratio (typical)

3M:1

Color Gamut

72% NTSC (CIE 1931)

Color Support (typical)

16.7 Million

Anti-Glare

Yes

CONNECTIVITY

Video Signal

1 x HDMI 1.4

1 x VGA

Audio Signal

1 x Audio Out (3.5 mm)

MULTIMEDIA

Optional Soundbar Support

Yes (PN number: OA36190)

SPECIAL FEATURES

Sync Technology

AMD FreeSync™**

POWER

Power Consumption (typical/max)

17.5W / 23.5W

Power Consumption Sleep/Off Mode

< 0.5W

Power Consumption Switch-off Mode

< 0.5W

Energystar Power Consumption

(P_{on}/E_{TEC})

12W / 36 kWh

Power Supply

Internal

Voltage Required

AC 100 to 240V (50–60 Hz)

MECHANICAL

Tilt Angle (front/back)

-5° / 22°

VESA Mount Capability

Yes (100 x 100 mm)

ThinkCentre M Series Tiny Support

Yes, by Tiny VESA mount II

(PN: 4XFON03161)

ThinkCentre M Series Nano Support

Yes, by Nano VESA mount

(PN: 4XF0V81630)

Kensington Lock Slot

Yes

Cable Management

Yes

Bezel Color

Raven Black

Bezel Width (side)

2.5 mm

Bezel Width (top/bottom)

2.5 / 22.4 mm

DIMENSIONS

Size Packed (D x H x W, mm/inch)

624.0 x 124.0 x 415.0 mm

24.57 x 4.88 x 16.34 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)

173.1 x 434.5 x 540.4 mm

6.81 x 17.10 x 21.28 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position)

173.1 x 434.5 x 540.4 mm

6.81 x 17.10 x 21.28 inches

Size Unpacked w/o stand (Head Only) (D x H x W)(mm/inch)

45.5 x 327.2 x 540.4 mm

1.79 x 12.88 x 21.28 inches

Weight Packed (kg/lbs.)

5.42 kg / 11.95 lbs.

Weight Unpacked (kg/lbs.)

3.82 kg / 8.42 lbs.

Weight (Monitor Head Only) (kg/lbs.)

3.02 kg / 6.66 lbs.

WHAT'S IN THE BOX

Monitor with stand

1 x Power cable (1.8 m)

1 x HDMI cable (1.8 m)

Quick setup guide

CERTIFICATION

ENERGY STAR Certification

Yes

CCC

Yes

TCO

8.0

TCO Edge

2.0

RoHS (EU 2002/95/EC)

Yes

EPEAT

Silver

Windows Certification

Windows 7, Windows 10

China Energy Efficiency Standard

Tier 1

TÜV Rheinland Eye Comfort

Yes



*AMD FreeSync™ is enabled for AMD Radeon™ Series graphics cards.

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2021 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive.

Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, U.S.A., Attn: Dept. ZPYA/B600.

Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

ThinkVision S24e-20

