

W400LVe

Bright projection









- Bright WXGA projector 4,000 ANSI lumens
- Easy connectivity HDMI, VGA, USB Power
- Clear, powerful audio 10W speaker
- Lightweight and portable

Project bright vibrant presentations effortlessly any time of day in HD. Enhance meeting rooms and classrooms with the W400LVe, boasting amazing color, long lamp life and energy-saving features to provide you with a low overall cost of ownership.



Specifications

Specifications	
Display/image	
Display technology	DLP
Resolution	WXGA (1280x800)
Brightness	4,000 lumens
Contrast ratio	25,000:1
Native aspect ratio	16:10
Aspect ratio - compatible	4:3,16:9
Keystone correction -	+/-40°
vertical	
Horizontal scan rate	15.38 ~ 91.15Khz
Vertical scan rate	50 ~ 85(120 for 3D)Hz
Uniformity	75%
Screen size	32.24" ~ 299.53" diagonal
Lamp info	
Light source type	Lamp
Lamp watts	203
Lamp life hours (up to)	6000 (Bright), 12000 (Dynamic), 10000 (Eco), 15000 (Eco+)
Optical	
Throw ratio	1.55:1 ~ 1.73:1
Projection distance	39.37" - 472.44"
Zoom	1.1
	I.I Manual
Zoom type	
Focal length (mm)	21.85 mm~24mm/0.86"~0.945"
Native offset	112%
Connectivity	
Connections	Inputs 1 x HDMI 1.4a 3D support, 1 x VGA (YPbPr/RGB),
	1 x Composite video, 1 x Audio 3.5mm
	Outputs 1 x VGA, 1 x Audio 3.5mm, 1 x USB-A power 1A
	Control 1 x RS232
General	
Noise level (typical)	27dB
Noise level (max)	29dB
, ,	
PC compatibility	FHD, UXGA, SXGA, WXGA, HD, XGA, SVGA, VGA, Mac
2D compatibility	NTSC M/J, 3.58MHz, 4.43MHz PAL B/D/G/H/I/M/N, 4,43MHz SECAM B/D/G/K/K1/L, 4.25/4.4MHz 480i/p,
	576i/p, 720p(50/60Hz), 1080i(50/60Hz), 1080p(50/60Hz)
3D compatibility	Side-by-Side:1080i50 / 60, 720p50 / 60 Frame-pack:
3D Compatibility	1080p24, 720p50 / 60 Over-Under: 1080p24, 720p50 / 60
3D	Full 3D
Security	Security bar, Kensington Lock, Password protected interface
OSD / display languages	25 languages: Arabic, Czech, Danish, Dutch, English, Farsi, Finnish, French, German, Greek, Hungarian, Indonesian,
	Italian, Japanese, Norwegian, Polish, Portuguese, Romanian,
	Russian, Chinese (simplified), Spanish, Swedish, Chinese
	(traditional), Turkish, Vietnamese
Operating conditions	5°C~40°C/41°F~104°F, max altitude 3000M/9843ft, max
aparaming containents	humidity 85%
Remote control	Card style
Speaker count	1
Watts per speaker	10W
In the box	AC power cord
III UIG DUX	Remote control
	Battery
	Basic user manual
Optional wireless models	HDCast Pro, QuickCast Bundle, QuickCast starter kit,
	WHD200
Power	
Power supply	100 ~ 240V, 50 ~ 60Hz
Power consumption	0.5W
(standby)	0.000
Power consumption (min)	187W
	225W
Power consumption (max)	ZZOVV
Weight and dimensions	10.4410.0414.051.
Dimensions (W x D x H)	12.44" x 9.61" x 4.25"

9.7 lbs 6.61 lbs

Gross weight Net weight



