

Lenovo G27-20 66C2GCC1US

Product

Lenovo G27-20

Machine Type

66C2

Region

NA

Display Size

27"

View Area

597.89x336.31 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution

1920x1080

Pixel Pitch

0.3114x0.3114 mm

Dot / Pixel Per Inch

82 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

1 ms (MPRT) / 4 ms (Extreme mode) / 6 ms (Typical mode) / 14 ms (Off mode)

Refresh Rate

144 Hz

Brightness

400 nits

Contrast Ratio

1000:1

Color Gamut

99% sRGB

Anti-glare

Yes

Multiple Input

HDMI, DP

USB Port

None

Camera

None

Microphone

None

Speaker

None

Power Consumption (Typical / Maximum)

22W / 32W

Power Adapter

Integrated

Stand

Tilt, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

522.8x612.4x260 mm / 20.58x24.11x10.24 inches

Weight (Including Stand)

5.94 kg / 13.10 lbs.

Monitor cable

DP

ENERGY STAR

None

TCO

None

EPEAT

None

TÜV Rheinland Low Blue Light

Low Blue Light

TÜV Rheinland Eye Comfort

None

TÜV Rheinland Eyesafe Display

None

TÜV Rheinland Flicker Free

Yes

Base Warranty

1-year

Operating System Support

Support Windows 7, Windows 10

Sync Technology

NVIDIA G-SYNC Compatible, AMD Radeon FreeSync Premium Compatible

Tiny Support / CPU / Platform

None / None / None

Ethernet / Bluetooth / Wireless

None / None / None

Touch Screen / Digitizer Pen / Battery

None / None / None

Display Ram / Storage / Card Slot

None / None / None

EAN / UPC / JAN

0195348268387

Announce Date

2020-11-23

Notes:**California Electronic Waste Recycling Fee**

In California, per state law, Lenovo charges an electronic waste recycling fee on this covered device at the time of sale of the product. For more information, go to: <https://www.calrecycle.ca.gov/Electronics/Consumer>

L WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product specifications Reference.

© Lenovo, 2021. All rights reserved.



Lenovo G27-20 Monitor

DISPLAY

Panel Size
27-inch

Screen Dimensions
612.42 mm x 367.03 mm

Panel Type
3-side NearEdgeless
In-Plane Switching

Active Area
597.89 mm x 336.31 mm

Backlight
WLED

Aspect Ratio
16:9

Resolution
1920 x 1080

Pixel Pitch
0.3114 x 0.3114 mm

Dot/Pixel Per Inch (DPI/PPI)
82

Viewing Angle (H x V @ CR 10:1)
178° / 178°

Response Time
3ms (Extreme Mode)
5ms (Normal Mode)
1ms (with MPRT²)

Refresh Rate
144 Hz

Brightness (typical)
400 cd/m²

Contrast Ratio (typical)
1000:1

Dynamic Contrast Ratio (typical)
3M:1

Color Gamut
99% sRGB

Color Support (typical)
16.7 Million

Color Depth
True 8-bit

Anti-glare
Yes

HDR Decoding
Yes

CONNECTIVITY

Video Signal
1 x HDMI 1.4
1 x DP 1.2

Audio Signal
1 x Audio Out (3.5 mm)

SPECIAL FEATURES

Software
Yes⁴ (Lenovo Artery,
Lenovo Display Control Center)

Sync Technology
NVIDIA® G-SYNC® Compatible³
AMD Radeon Freesync™ Premium
Compatible⁵

POWER

Power Consumption (typical/max)
22W / 32W

Power Consumption Sleep/Off Mode
< 0.5W

Power Consumption Switch-off Mode
< 0.3W

Power Supply
Internal

Voltage Required
AC 100 to 240 V (50-60 Hz)

MECHANICAL

Tilt Angle (front/back)
-5° / 22°

Lift (max range)
130 mm

VESA Mount Capability
Yes (100 x 100 mm)

Kensington Lock Slot
Yes

Cable Management
Yes

Bezel Color
Raven Black

Bezel Width (side)
2.0 mm

Bezel Width (top/bottom)
2.0 / 20.7 mm

DIMENSION

Size Packed (D x H x W, mm/inch)
159.0 x 478.0 x 868.0mm /
6.26 x 18.82 x 34.17 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (lowest position)
260.0 x 392.8 x 612.4mm /
10.24 x 15.46 x 24.11 inches

Size Unpacked w/ Stand (D x H x W, mm/inch) (highest position)
260.0 x 522.8 x 612.4mm /
10.24 x 20.58 x 24.11 inches

Size Unpacked w/o Stand (head only) (D x H x W)(mm/inch)
48.0 x 367.0 x 612.4mm /
1.80 x 14.45 x 24.11 inches

Weight Packed (kg/lb)
8.25 kg / 18.19 lbs.

Weight Unpacked (kg/lb)
5.94 kg / 13.10 lbs.

Weight Unpacked (monitor head only) (kg/lb)
3.68 kg / 8.11 lbs.

WHAT'S IN THE BOX

Monitor with stand
1 x Power cable (1.8m)
1 x DP cable (1.8m)
Warranty Booklet
Quick setup guide

CERTIFICATION

CCC
Yes

RoHS (EU 2002/95/EC)
Yes

Windows Certification
Window 7, Windows 10

China Energy Efficiency Standard
Tier 2

TÜV Rheinland Low Blue Light
Yes

TÜV Rheinland Flicker Free
Yes



¹Requires PC connected over HDMI.

²MPRT of 1ms is based on internal testing conditions. Actual Response Time may vary based on operating conditions.

³NVIDIA® G-SYNC® Compatible works only with Compatible NVIDIA® GeForce® graphics card

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: ~ 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2021 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Other company, product, and service names may be trademarks or service marks of others.

Specifications may vary depending upon region.

Lenovo G27-20

