Lenovo

Think Vision P24h-2L 62B2GAR1US

Product

ThinkVision P24h-2L

Machine Type

62B2

Region

NA, LA

Display Size

23.8"

View Area

535x313 mm

Panel

In-Plane Switching

Aspect Ratio

16:9

Resolution 2560x1440

Pixel Pitch

0.2058x0.2058 mm

Dot / Pixel Per Inch

123 dpi

View Angle (H / V)

178 / 178

Pixel Response Time

4 ms (Extreme mode) / 6 ms (Normal mode)

Refresh Rate

60 Hz

Brightness

300 nits

Contrast Ratio

1000:1

Color Gamut

99% sRGB, 99% BT.709, 83% DCI-P3

Multiple Input

HDMI, DP, DP-out, USB Type-C Gen1(DP1.2 Alt Mode)

4 x USB 3.2 Gen1 (1 x BC1.2)

Camera

None

Microphone

None

Speaker 1W x 2

Power Consumption (Typical / Maximum)

23W / 132W

Power Adapter

Integrated

Stand

Tilt, Swivel, Pivot, Height Adjust Stand

Color

Raven Black

Side Bezel Width

2 mm

Dimensions with Stand (HxWxD)

570x539.8x205 mm

Weight (Including Stand)

14.09lb / 6.39kg

Monitor Cable

DP, USB Type-C to Type-C, USB Type-C to Type-A

ENERGY STAR

Yes

TCO

TCO 8.0

EPEAT

Silver

Low Blue Light / Eye Comfort / Eyesafe Display

Low Blue Light / Eye Comfort / Eyesafe Display

Base Warrantv

3-year

Operating System Support

Support Windows 7, Windows 10

Sync Technology

None

CPU / Platform / Tiny Support

None / None / None

Display Ram / Storage / Card Slot

None / None / None

Wireless / Ethernet / Bluetooth

Ethernet (10M/100M/1000M)

Touch Screen / Digitizer Pen / Battery

None / None / None

EAN/UPC/JAN

0195348052245

Announce Date

2020-12-12

WWW.LENOVO.COM

Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area.

Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



https://psref.lenovo.com

Visit psref website for the latest version of Product specifications Reference. © Lenovo, 2021. All rights reserved.



ThinkVision P24h-2L

DISPLAY

Panel Size 23.8-inch

Screen Dimensions 535 mm x 313 mm

Panel Type 3-side NearEdgeless In-Plane Switching

Active Area 526.85 mm x 296.35 mm

Backlight WLED

Aspect Ratio 16:9

Resolution 2560 x 1440

Pixel Pitch 0.2058 x 0.2058 mm

Dot/Pixel Per Inch (DPI/PPI)

Viewing Angle (H x V @ CR 10:1) 178° / 178°

Response Time 4ms (Extreme Mode) 6ms (Normal Mode)

Refresh Rate 60 Hz

Brightness (typical) 300 cd/m²

Contrast Ratio (typical) 1000:1

Dynamic Contrast Ratio (typical)

Color Gamut 99% sRGB, 99% BT.709, 83% DCI-P3

Color Support (typical) 16.7 Million

Anti-glare Yes

CONNECTIVITY

Video Signal 1 x USB Type-C³ Gen1 (DP1.2 Alt Mode) 1 x HDMI 1.4 1 x DP 1.2 1 x DP 1.2 (Out)

Audio Signal 1 x Audio Out (3.5 mm)

USB Hub Yes

Ethernet Yes

USB Upstream 1 x USB 3.2 Gen1 (by USB Type-C Gen1)

USB Downstream 4 x USB 3.2 Gen1 (1 x BC1.2)

MUI TI-MEDIA

Optional Soundbar Support Yes (PN 0A36190)

SPECIAL FEATURES

Software

Lenovo ThinkColour (Lenovo Display Control Center)²

POWER

Power Consumption (typ./max.) 23W / 132W

Power Consumption Sleep/Off Mode ≤ 0.5W

Power Consumption Switch-off Mode ≤ 0.3W

ENERGY STAR Power Consumption (P_{op}/E_{TEC}) 18.1W / 57.4kWh

Power Supply Internal

USB Type-C Power Delivery (W) up to 75 W⁴

Smart Power¹

Voltage Required AC 100 to 240 V (47-63 Hz)

MECHANICAL

Tilt Angle (front/back) -5° / 35°

Swivel Angle (left/right) +45° / -45°

Lift (Max range) 150 mm

Pivot -90° / 90°

VESA Mount Capability Yes (100 x 100 mm)

ThinkCentre M Series Tiny Support

Yes, by Tiny/Nano monitor clamp II (PN: 4XH0Z42451) and Tiny VESA mount II (PN: 4XF0N03161)

ThinkCentre M Series Nano Support

Yes, by Tiny/Nano monitor clamp II (PN: 4XH0Z42451) and Nano VESA mount(PN: 4XF0V81630)

Kensington Lock Slot Yes

Cable Management Yes

Bezel Color Raven Black

Bezel Width (side) 2.0 mm

Bezel Width (top/bottom) 2.0 mm / 21.4 mm

DIMENSION

Size Packed (D x H x W. mm/inch) 620.0 x 423.0 x 149.0 mm 24.40 x 16.70 x 5.90 inches

Size Unpacked w/ Stand (D x H x W. mm/inch) (lowest position) 205.0 x 420.0 x 539.80 mm 8.07 x 16.53 x 21.25 inches

Size Unpacked w/ Stand (D x H x W. mm/inch) (highest position) 205.0 x 570.0 x 539.8 mm 8.07 x 22.44 x 21.25 inches

Size Unpacked w/o Stand (head only) (D x H x W, mm/inch) 46.6 x 325.7 x 539.8 mm 1.83 x 12.82 x 21.25 inches

Weight Packed (kg/lbs.) 8.46 kg / 18.65 lbs.

Weight Unpacked (kg/lbs.) 6.39 kg / 14.09 lbs.

Weight (monitor head only) (kg/lbs.) 4.10 kg / 9.04 lbs.

WHAT'S IN THE BOX

Monitor with stand 1 x Power cable (1.8 m) 1 x DP cable (1.8 m) (US & Canada only) 1 x USB Type-C to Type-C cable (1.8 m)

1 x USB Type-C to Type-A cable (1.8 m) (US & Canada only) Factory calibration report Quick setup guide

CERTIFICATION

ENERGY STAR Rating 8.0

CCC Yes TCO 8.0

TCO Edge 2.0

EPEAT Silver

RoHS (EU 2002/95/EC)

Windows Certification Windows 7, Windows 10

China Energy Efficiency Standard

TÜV Rheinland Eye Comfort

TÜV Low Blue Light (Hardware Solution)

Evesafe Display Certification Yes

















The Smart Power function intelligently detects overall power consumption and dynamically manages the power delivery to each device. ²This software can only be used with Windows 10

³USB Type-C* and USB-C* are registered trademarks of USB Implementers Forum.

4Up to 75 W power delivery to compatible devices by USB Type-C. Listed as maximum capacity of power delivery. Actual capacity of power delivery may vary depending upon devices connected or monitor configuration, and may decline with downstream USB ports connected or higher brightness setting

Depending on many factors such as the processing capability of peripheral devices, file attributes, and other factors related to system configuration and operating environments, the actual transfer rate using the various USB connectors on this device will vary and is typically slower than the data rates as defined by the respective USB specifications: - 5 Gbit/s for USB 3.1 Gen1; 10 Gbit/s for USB 3.1 Gen2 & 20 Gbit/s for USB 3.2.

© 2021 Lenovo. All rights reserved. These products are available while supplies last. Prices shown are subject to change without notice. For any questions concerning price, please contact your Lenovo Account Executive. Lenovo is not responsible for photographic or typographic errors. Warranty: For a copy of applicable warranties, write to: Warranty Information, 500 Park Offices Drive, RTP, NC 27709, Attn: Dept. ZPYA/B600. Lenovo makes no representation or warranty regarding third-party products or services. Trademarks: Lenovo, the Lenovo logo, Rescue and Recovery, ThinkPad, ThinkCentre, ThinkStation, ThinkVantage, and ThinkVision are trademarks or registered trademarks of Lenovo. Microsoft, Windows, and Vista are registered trademarks of Microsoft Corporation. Intel, the Intel logo, Intel Inside, Intel Core, and Core Inside are trademarks of Intel Corporation in the U.S. and/or other countries. Other company, product, and service names may be trademarks or service marks of others.











